

GCX Series 22mm Plastic Illuminated Pushbuttons


Mushroom-style illuminated pushbuttons

All pushbuttons include operator, support base, indicating bulb (if applicable) and contact block. They are shipped unassembled. Legend plate is not included and must be ordered separately. All switches in this series use replacement contact block ECX1030 (Red, NC) or ECX1040 (Green, N.O.), sold separately in packages of two or five.



GCX3221-24


Dimensions: mm [inches]



Part Number	Lamp Color	Price	Mushroom-style Illuminated Pushbuttons Description	Replacement Incandescent Bulb	Replacement LED Lamp
Incandescent					
GCX3221-24	Red	\$11.50	22mm plastic momentary pushbutton with incandescent illuminated 40mm mushroom actuator, 24VDC/VAC, one N.C. contact block	ECX1902-5 5/pk 80mA	ECX1911-2 2/pk, 26mA
GCX3221-120	Red	\$13.00	22mm plastic momentary pushbutton with incandescent illuminated 40mm mushroom actuator, 120VDC/VAC, one N.C. contact block	ECX1904-5 5/pk 20mA	ECX1921-2 2/pk, 5mA
GCX3226-24	Red	\$13.00	22mm plastic pushbutton with incandescent illuminated 40mm mushroom twist-to-release actuator, 24VDC/VAC, one N.C. contact block	ECX1902-5 5/pk 80mA	ECX1911-2 2/pk, 26mA
GCX3226-120	Red	\$14.50	22mm plastic pushbutton with incandescent illuminated 40mm mushroom twist-to-release actuator, 120VDC/VAC, one N.C. contact block	ECX1904-5 5/pk 20mA	ECX1921-2 2/pk, 5mA
LED					
GCX3221-24L	Red	\$16.00	22mm plastic momentary pushbutton with LED illuminated 40mm mushroom actuator, 24VDC/VAC, one N.C. contact block	ECX1902-5 5/pk 80mA	ECX1911-2 2/pk 26mA
GCX3221-120L	Red	\$17.50	22mm plastic momentary pushbutton with LED illuminated 40mm mushroom actuator, 120VDC/VAC, one N.C. contact block	ECX1904-5 5/pk 20mA	ECX1921-2 2/pk 5mA
GCX3226-24L	Red	\$18.00	22mm plastic pushbutton with LED illuminated 40mm mushroom twist-to-release actuator, 24VDC/VAC, one N.C. contact block	ECX1902-5 5/pk 80mA	ECX1911-2 2/pk 26mA
GCX3226-120L	Red	\$19.00	22mm plastic pushbutton with LED illuminated 40mm mushroom twist-to-release actuator, 120VDC/VAC, one N.C. contact block	ECX1904-5 5/pk 20mA	ECX1921-2 2/pk 5mA


Non-illuminated mushroom pushbuttons

Feature large 60mm dia. actuator and mount in standard 22mm hole.



GCX3137

Dimensions: mm [inches]



GCX3141
(key operated)

Note: Keyed switches come with two keys. All plastic 22mm keyed switches are keyed alike. Replacement keys are available. Order part no. ECX1067-2 (pkg. of 2).

Part Number	Color	Price	Description
GCX3131	Red	\$9.50	Twist-to-release actuator with one N.C. contact block, fits in 22mm dia. hole. Has large 40mm dia. mushroom-style actuator.
GCX3134	Black	\$7.75	Momentary action with one N.O. contact block, fits in 22mm dia. hole, has large 40mm dia. mushroom-style actuator.
GCX3135	Red	\$7.75	Momentary action with one N.C. contact block, fits in 22mm dia. hole, has large 40mm dia. mushroom-style actuator. EMERGENCY legend plate available (see Accessories).
GCX3136	Red	\$12.00	Twist-to-release actuator with one N.C. contact block, fits in 22mm dia. hole. 60mm dia. mushroom-style actuator.
GCX3137	Red	\$9.50	Momentary action with one N.C. contact block, fits in 22mm dia. hole, has large 60mm dia. mushroom-style. EMERGENCY legend plate available (see Accessories).
GCX3139	Yellow	\$7.75	Momentary action with one N.O. contact block, fits in 22mm dia. hole, has large 40mm dia. mushroom-style actuator.
GCX3141	Red	\$14.00	Key operated release with one N.C. contact block, fits in 22mm dia. hole, has large 40mm dia. mushroom-style actuator. EMERGENCY legend plate available (see Accessories).


For accessories, see 22mm Plastic Pilot Device Accessories in this section.

GCX Series 22mm Plastic Pilot Devices

Features

Any combination of contact blocks is allowed, up to a total of six (two blocks wide and three blocks deep)

Secure mounting method eliminates twisting in mounting hole





Operators are protected to IP 40 or IP65 (see specifications below)


Support base mounts into panels up to 6 mm thick

Fiberglass reinforced thermoplastic bezel


Easy installation



All indicators offer side wire entry with back screw terminals for easy wiring



Self-cleaning silver contacts provide reliable, low-energy switching



Pressure plate wiring terminals for easy, secure wiring, accepting up to 14 AWG wire

Contacts rated A300
(Refer to E22 Series mounting/contact rating section for details)

Clear contact block for illustration purposes. Clear contact blocks are not available for sale from AutomationDirect.

22mm Plastic Pilot Device Accessories

Replacement incandescent bulbs



ECX1902-5

Replacement Incandescent Bulbs				
Part Number	Quantity	Price	Rating	Description
ECX1900-5	Pkg of 5 bulbs	\$8.75	6V@ 200mA 1.2 watts	6V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4
ECX1902-5	Pkg of 5 bulbs	\$8.75	24V@ 80mA 2 watts	24V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4
ECX1904-5	Pkg of 5 bulbs	\$18.00	130V@20mA 2.6 watts	120V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4

Note: Bulb removal tool available. Order part number HT8LAMP TOOL.

Replacement LED lamps



ECX1915-2

Replacement LED Lamps					
Part Number	Color	Quantity	Price	Rating	Description
ECX1911-2	Red	Pkg of 2 LED lamps	\$16.00	24V@26mA 0.6 watts	LED replacement lamp for miniature bayonet bases Works with 22mm switches and indicators, but illumination will not be as even when used with the ECX 22mm indicators Note: Will not replace sealed Cutler-Hammer monoblock LED indicators.
ECX1912-2	Green		\$20.00		
ECX1913-2	Yellow		\$16.00		
ECX1914-2	Blue		\$21.50		
ECX1915-2	White		\$25.00		
ECX1921-2	Red		\$16.00	120V@5mA 0.6 watts	
ECX1922-2	Green		\$20.00		
ECX1923-2	Yellow		\$16.00		
ECX1924-2	Blue		\$21.50		
ECX1925-2	White		\$25.00		

Note: LED modules have very low current draw and should not be used with triac output devices like PLC triac output modules. It is recommended that dry contact outputs be used to switch 120 volt AC LED modules.

Hole plug



ECX1490

Hole Plug			
Part Number	Color	Price	Description
ECX1490	Black	\$2.75	Plastic hole plug for 22.5 mm openings in panels and enclosures; supplied with O-ring and mounting screw. Two plugs per package.

Protective covers for pushbuttons



ECX1703-5

Protective Covers for Pushbuttons				
Part Number	Color	Quantity	Price	Description
ECX1700-5	Black	Pkg of 5 protective caps	\$6.75	Silicone protective covers for use with 22mm standard-size flush pushbuttons. Will not work with Cutler-Hammer pushbuttons, 22mm plastic illuminated or extended pushbuttons, or 22mm plastic pushbuttons with 40mm actuator face.
ECX1701-5	Red		\$6.75	
ECX1702-5	Green		\$6.75	
ECX1703-5	Yellow		\$6.75	
ECX1704-5	Blue		\$6.75	
ECX1705-5	Clear		\$6.75	
ECX1706-5	Clear		\$12.00	

Knockout Punches



109225

Ruko's knockout punch hole-cutting tool includes punch, die and draw bolt (without ball bearing). Use for sheet steel, stainless-steel sheets, non-ferrous and light metals, and plastics up to 0.16" (8 ga.) thick. Replacement bolts are offered in three of the most popular sizes. See the Tools section of the catalog for details.

Note: Part number 109225 is recommended when punching holes for 22mm pilot devices.

Replacement keys




ECX1067-2

Replacement Keys			
Part Number	Quantity	Price	Description
ECX1067-2	Pkg of 2	\$6.00	Replacement key for GCX series key-actuated selector switches, pack of 2 sets (2 keys each). NOTE: Will not work with Cutler-Hammer 22mm switches.


Note: All key-actuated 22mm plastic selector switches are keyed alike.

22mm Plastic Pilot Device Accessories

Replacement 22mm support base




ECX3029-2





Dimensions: mm [inches]

Replacement 22mm Support Base			
Part Number	Quantity	Price	Description
ECX3029-2	Pkg of 1	\$1.75	22mm plastic support base Note: This item is supplied as a replacement part and is not required with any switch assembly. Will not work with Cutler-Hammer 22mm switches sold by AUTOMATIONDIRECT

Replacement contact blocks



ECX1030-2



Dimensions: mm [inches]

Replacement Contact Blocks				
Part Number	Quantity	Price	Contacts	Description
ECX1030-2	Pkg of 2	\$6.50	Red, normally-closed (N.C.)	Replacement contact block for 22mm pushbuttons and selector switches. Tightening Torque, terminal screw: 0.8 N-m max mounting screw: 0.5 N-m max
ECX1030-5	Pkg of 5	\$15.50		
ECX1040-2	Pkg of 2	\$6.50	Green, normally-open (N.O.)	Note: Will not work with Cutler-Hammer 22mm switches sold by AUTOMATIONDIRECT
ECX1040-5	Pkg of 5	\$15.50		
ECX1042-2	Pkg of 2	\$6.50	Brown, normally-open (N.O.), push-push	Use on lighted Push-push button only

Note: See electrical specifications on GCX Series 22mm Plastic Pilot Devices Specifications page at beginning of this section.

EMERGENCY STOP legend plate



ECX1651

EMERGENCY STOP Legend Plate			
Part Number	Quantity	Price	Description
ECX1651	pkg. of 1	\$2.75	Oversize yellow circular EMERGENCY STOP legend plate for 22mm E-stop type mushroom pushbuttons, 60mm outside diameter.

Two-position short lever operator



GR1172PR-5

Short Lever Replacement Operator				
Part Number	Lamp Color	Price	2-Position	Use with
GR1172PR-5	Red	\$15.00	22mm 2-position selector switch illuminated short lever replacement operator, 5/pkg	Part numbers starting with GCX124, GCX125, GCX324, GCX325
GR1172PV-5	Green	\$15.00	22mm 2-position selector switch illuminated short lever replacement operator, 5/pkg	
GR1172PG-5	Yellow	\$15.00	22mm 2-position selector switch illuminated short lever replacement operator, 5/pkg	
GR1172PB-5	Blue	\$15.00	22mm 2-position selector switch illuminated short lever replacement operator, 5/pkg	
GR1172PN-5	Clear	\$15.00	22mm 2-position selector switch illuminated short lever replacement operator, 5/pkg	

22mm Plastic Pilot Device Accessories

Three-position short lever operator



GR1288PR-5

Short Lever Replacement Operator				
Part Number	Lamp Color	Price	3-Position	Use with
GR1288PR-5	Red	\$15.00	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	Part numbers starting with GCX126, GCX128 GCX326, GVX328
GR1288PV-5	Green	\$15.00	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
GR1288PG-5	Yellow	\$15.00	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
GR1288PB-5	Blue	\$15.00	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
GR1288PN-5	Clear	\$15.00	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	

Mushroom switch replacement operator



PL1298P-5

Mushroom Switch Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
PL1171PR-5	Red	\$6.50	22mm, illuminated momentary Mushroom switch replacement operator, red, 5/pk	Part numbers starting with GCX1221, GCX3221 mushroom-style illuminated pushbuttons
PL1298P-5	Red	\$6.50	22mm illuminated twist-to-release mushroom switch replacement operator, red, 5/pk	Part numbers starting with GCX1226, GCX3226 mushroom-style illuminated pushbuttons

Flush pushbutton replacement operator



GR1168PR-5

Flush Pushbutton Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
GR1168PR-5	Red	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	Part numbers starting with GCX119, GCX120 GCX319, GCX320
GR1168PV-5	Green	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	
GR1168PG-5	Yellow	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	
GR1168PB-5	Blue	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	
GR1168PN-5	Clear	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	
GR1168PW-5	White	\$8.25	22mm illuminated flush pushbutton replacement operator, 5/pk	

Extended pushbutton replacement operator



PL1308PR-5

Extended Pushbutton Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
PL1308PR-5	Red	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	Part numbers starting with GCX121, GCX321
PL1308PV-5	Green	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	
PL1308PG-5	Yellow	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	
PL1308PB-5	Blue	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	
PL1308PN-5	Clear	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	
PL1308PW-5	White	\$6.25	22mm illuminated extended pushbutton, replacement operator, 5/pk	

Note: All dimensions are in inches [millimeters].

22mm Plastic Pilot Device Accessories

Legend plates

Plastic legend plates for use with 22mm pilot devices. White engraved text on colored background. O-ring included.



ECX1670-B07




ECX1670-R03

Plastic Legend Plates			
Legend	Color of Field	Part Number	Price
AUTO OFF HAND	Black	ECX1670-B46	\$3.50
Blank Plate	Black	ECX1670-B	\$3.00
Blank Plate	Red	ECX1670-R	\$3.00
CLAMP	Black	ECX1670-B24	\$3.50
CLOSE	Black	ECX1670-B01	\$3.00
DOWN	Black	ECX1670-B02	\$3.00
EMERG. STOP	Red	ECX1670-R03	\$3.00
EXTEND	Black	ECX1670-B51	\$3.50
FEEDER OFF	Black	ECX1670-B26	\$3.50
FEEDER ON	Black	ECX1670-B25	\$3.50
FOR OFF REV	Black	ECX1670-B19	\$3.00
FOR-REV	Black	ECX1670-B13	\$3.00
FORWARD	Black	ECX1670-B04	\$3.00
GRIP	Black	ECX1670-B53	\$3.50
HAND-AUTO	Black	ECX1670-B14	\$3.00
HAND OFF AUTO	Black	ECX1670-B20	\$3.00
HIGH	Black	ECX1670-B27	\$3.50
HIGH LOW	Black	ECX1670-B43	\$3.50
IN	Black	ECX1670-B28	\$3.50
INCH	Black	ECX1670-B29	\$3.50
JOG	Black	ECX1670-B05	\$3.00
JOG FOR	Black	ECX1670-B30	\$3.50
JOG REV	Black	ECX1670-B31	\$3.50
JOG-RUN	Black	ECX1670-B15	\$3.00
LOW	Black	ECX1670-B32	\$3.50
LOWER	Black	ECX1670-B33	\$3.50

Plastic Legend Plates			
Legend	Color of Field	Catalog Number	Price
MAN AUTO	Black	ECX1670-B44	\$3.50
MAN OFF AUTO	Black	ECX1670-B47	\$3.50
MOTOR RUN	Black	ECX1670-B22	\$3.00
MOTOR STOP	Black	ECX1670-B23	\$3.00
OFF	Black	ECX1670-B34	\$3.50
OFF-ON	Black	ECX1670-B16	\$3.00
ON	Black	ECX1670-B06	\$3.00
OPEN	Black	ECX1670-B07	\$3.00
OPEN OFF CLOSE	Black	ECX1670-B48	\$3.50
OPEN-CLOSE	Black	ECX1670-B17	\$3.00
OUT	Black	ECX1670-B35	\$3.50
POWER ON	Black	ECX1670-B21	\$3.00
PULL ON PUSH OFF	Black	ECX1670-B50	\$3.50
RAISE	Black	ECX1670-B36	\$3.50
READY	Black	ECX1670-B37	\$3.50
RELEASE	Black	ECX1670-B54	\$3.50
RESET	Black	ECX1670-B38	\$3.50
RETRACT	Black	ECX1670-B52	\$3.50
REVERSE	Black	ECX1670-B08	\$3.00
RUN	Black	ECX1670-B09	\$3.00
SAFE RUN	Black	ECX1670-B45	\$3.50
START	Black	ECX1670-B10	\$3.00
STOP	Black	ECX1670-B11	\$3.00
STOP	Red	ECX1670-R11	\$3.00
TEST	Black	ECX1670-B39	\$3.50
TRANSFER	Black	ECX1670-B40	\$3.50
TRIP	Black	ECX1670-B41	\$3.50
UNCLAMP	Black	ECX1670-B42	\$3.50
UP	Black	ECX1670-B12	\$3.00
UP OFF DOWN	Black	ECX1670-B49	\$3.50
UP-DOWN	Black	ECX1670-B18	\$3.00

Note: Legend plate text is 3mm in height



Dimensions: mm [inches]

22mm Plastic Pilot Device Accessories




ECX1690-B16

Jumbo Plastic Legend Plates			
Legend	Color of Field	Part Number	Price
Blank Plate	Black	ECX1690-B	\$3.50
Blank Plate	Red	ECX1690-R	\$3.50
EMERG. STOP	Red	ECX1690-R03	\$3.50
HAND-OFF-AUTO	Black	ECX1690-B20	\$3.50
JOG	Black	ECX1690-B05	\$3.50
OFF-ON	Black	ECX1690-B16	\$3.50
OPEN-CLOSE	Black	ECX1690-B17	\$3.50
POWER ON	Black	ECX1690-B21	\$3.50
START	Black	ECX1690-B10	\$3.50
STOP	Red	ECX1690-R11	\$3.50

Note: Legend plate text is 3mm in height



ECX1690-R11




Dimensions: mm [inches]

GCX Series 22mm Plastic Pilot Devices Specifications


Assembly information

These pushbuttons and indicator lights are supplied with the appropriate contact blocks, unless otherwise indicated. Use these drawings as a guide to make sure there is adequate clearance behind the panel.


Pushbuttons and selector switches



Illuminated pushbuttons and selector switches/indicator lights




Mounting




This layout is suitable if all switches are 230V or less and the same polarity.

This layout is suitable if all switches are 400V or less and different polarity.



NOTE: Contact blocks can be arranged up to three deep by two wide.

Typical Wiring



Specifications

These specifications apply to all the GCX and ECX 22mm plastic pushbuttons and switches.

Physical Specifications		Electrical Specifications	
Standards Reference	CEI EN 60947-5-1, CSA C22-2 n.14	Rated Thermal Current (contact block)	A300, Q300 (Refer to E22 Series mounting/contact rating section for details)
Approvals	UL File E189258, IMQ (where specified)	Rated Insulation Voltage	Ui 660V according to CEI EN 60947-5-1, 300V according to CSA C22-2 n.14 and UL 508
Enclosure Material	Fiberglass reinforced thermoplastic	Dielectric Strength	3kV (1 second)
Contacts Material	Silver	Insulation Resistance	2MΩ min. (500VDC)
Protection Degree	IP 40 for GCX3151-24, GCX3151-120, GCX3153-24 and GCX3153-120. IP 65 for all others. (See Appendix of this catalog for explanation of IP ratings according to IEC 144 CEI 70-1.)	Initial Contact Resistance	≤25mΩ
Electric Shock Protection	IEC 536, Class II	Short-Circuit Protection*	Cartridge fuses gl 10 A-500V 10, 3x381 100 KA
Temperature Ratings	Storage: -40° to 80°C (-40° to 176° F) Operating: -25° to +70°C (-13° to 158° F)	Terminal Markings	According to CENELEC EN 50013
Working Positions	All working positions are allowed	Connections	Single screw with non-loosening plate clamp, 14AWG max., Tighten to 0.8Nm max
Mechanical Life	Pushbuttons, selector switches, joy stick switches: 1,000,000 operations Emergency mushrooms and push-push pushbuttons: 300,000 operations	Contacts Operation	Self-cleaning types EN01 (N.C.) EN 10 (N.O.) slow action, positive opening
Positive Opening Operation	(according to IEC 947-5-1) All functions incorporating an NC contact are positive opening operation	Operation Frequency	3600 operations per hour max.
		Utilization Category	AC15 (Control of AC electromagnetic loads) 24 volts AC at 10 amps 130 volts AC at 6.5 amps DC13 (Control of DC electromagnetic loads) 24 volts DC at 1.5 amps 110 volts DC at 0.5 amps

*Note: Recommended, not supplied

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.