

KSK Series Factor 1 Inductive Proximity Sensors

M18 (18mm)



- 4 models available
- Correction Factor (K-Factor) = 1
- Low cost/high performance
- Inductive sensor
- Metal thread M12 x 1 Connector
- Increased sensing range


- Gold-plated contacts
- Electromagnetic field immune
- Flush and Non-flush mounting
- Lifetime warranty



KSK Series M18 Inductive Prox Selection Chart									
Part Number	Price	Sensing Range	Mounting	Output State	Logic	Voltage	Connection	Wiring	Dimensions
KSK6-AP-3H	\$30.00	8mm (0.31 in)	Flush	N.O.	PNP	10 - 30 VDC	4-pin M12 quick-disconnect	Diagram 1	Figure 1
KSK6-AP-4H	\$30.00	12mm (0.47 in)	Non-flush						Figure 2
KSK-AP-3H	\$30.00	8mm (0.31 in)	Flush						
KSK-AP-4H	\$30.00	15mm (0.59 in)	Non-flush						

Wiring Diagrams

Diagram 1



Connector

4-pin M12 connector



Dimensions

mm [inches]

Figure 1





Figure 2



KSK Series Factor 1 Inductive Proximity Sensors

	M18 Specifications			
Model	KSK6-AP-3H	KSK6-AP-4H	KSK-AP-3H	KSK-AP-4H
Mounting Type	Flush	Non-flush	Flush	Non-flush
Nominal Sensing Distance (mm)	8mm (0.31in)	12mm (0.47 in)	8mm (0.31in)	15mm (0.59 in)
Operating Distance	0 - 6.48 mm	0 - 9.72 mm	0 - 6.48 mm	0 - 12.15 mm
Material Correction Factors	Correction Factor (K-Factor) = 1			
Output Type	N.O.			
Operating Voltage	10 to 30 VDC			
No-load Supply Current	< 20mA			
Operating (Load) Current	100mA			
Off-state Leakage Current	NA			
Voltage Drop	< 2.5 V			
Switching Frequency	2000Hz			
Differential Travel (% of Nominal Distance)	3 - 15			
Repeat Accuracy	NA			
Ripple	NA			
Time Delay Before Availability (tv)	NA			
Short Circuit Protection	Yes			
Operating Temperature	-40 — 85 °C [-40 — 185 °F]			
Protection Degree (DIN 40 050)	IP65 / IP66 / IP67 / IP68 / IP69K			
LED Indicators	Illuminated when energized			
Housing Material	stainless steel (316L); LED window: Polyetherimide (PEI)			
Sensing Face Material	active face: Liquid Crystal Polymer (LCP) white			
Shock/Vibration	See Proximity Sensor Terminology			
Weight	0.04 kg	0.035 kg	0.046 kg	0.042 kg
Connection	4-pin M12 quick-disconnect			
Agency Approvals	cULus E328811, CE			