

pro^{sense} Thermocouple and RTD Temperature Range

Thermocouple Temperature Range	
THMK-C06-04	32 to 2100°F (0 to 1149°C)
THMK-C12-04	
THMK-C18-04	
THMK-H06L01-03	
THMK-H12L01-03	
THMK-H18L01-03	32 to 2100°F (0 to 1149°C) lead wire transition rated to 204°C (400°F)
THMK-T06L06-03	
THMK-T12L06-03	
THMK-T18L06-03	
TTD25C-20-0300F-H	
TTD25N-20-0300F-H	0 to 300°F (-17.8 to 148.9°C)
THMJ-A01L04-01	32 to 900°F (0 to 482°C)
THMJ-A01L06-01	
THMJ-A01L10-01	
THMJ-A01L10-02	
THMJ-B01L06-01	
THMJ-B01L06-02	
THMJ-B02L06-01	
THMJ-B02L06-02	
THMJ-D08L04-01	
THMJ-D08L06-01	
THMJ-D08L10-01	
THMJ-D08L10-02	
THMK-A01L04-01	
THMK-A01L06-01	
THMK-A01L10-01	
THMK-A01L10-02	
THMK-B01L06-01	
THMK-B01L06-02	
THMK-D08L04-01	
THMK-D08L06-01	
THMK-D08L10-01	
THMK-D08L10-02	
THMJ-T06L06-01	
THMJ-T12L06-01	
THMJ-T18L06-01	
THMJ-P06-01	
THMJ-P12-01	
THMJ-P18-01	
THMJ-C04-03	
THMJ-C04R-03	
THMJ-C06-01	
THMJ-C06-02	
THMJ-C06-03	
THMJ-C06R-03	
THMJ-C12-01	
THMJ-C12-02	
THMJ-C12-03	
THMJ-C12R-03	
THMJ-C18-01	
THMJ-C18-02	
THMJ-H04L01-02	
THMJ-H06L01-01	
THMJ-H06L01-02	
THMJ-H12L01-01	
THMJ-H12L01-02	
THMJ-H18L01-01	

Thermocouple Temperature Range	
THMJ-T06L06-02	32 to 1330°F (0 to 720°C) lead wire transition rated to 400 °F (204 °C)
THMJ-T12L06-02	
THMJ-T18L06-02	
THMJ-P06-02	32 to 1330°F (0 to 720°C) plug rated to 400 °F (204 °C)
THMJ-P12-02	
THMJ-P18-02	
THMK-C04-03	32 to 1700°F (0 to 927°C)
THMK-C04R-03	
THMK-C06-01	
THMK-C06-02	
THMK-C06-03	
THMK-C06R-03	
THMK-C12-01	
THMK-C12-02	
THMK-C12-03	
THMK-C12R-03	
THMK-C18-01	
THMK-C18-02	
THMK-H04L01-02	
THMK-H06L01-01	
THMK-H06L01-02	
THMK-H12L01-01	
THMK-H12L01-02	
THMK-H18L01-01	
THMK-T06L06-01	
THMK-T06L06-02	
THMK-T12L06-01	
THMK-T12L06-02	
THMK-T18L06-01	
THMK-T18L06-02	
THMK-P06-01	
THMK-P06-02	
THMK-P12-01	
THMK-P12-02	
THMK-P18-01	
THMK-P18-02	
THMK-B02L06-01	
THMK-B02L06-02	
THMT-P06-01	
THMT-P12-01	
THMT-P18-01	
THMT-T06L06-01	
THMT-T12L06-01	
THMT-T18L06-01	
TTD25C-20-0100C-H	
TTD25N-20-0100C-H	
TSD25N-0P-0284-H	
TSD25N-AP-0284-H	

RTD Temperature Range	
RTD1-R01-01	40 to 185°F (-40 to 85°C)
RTD1-S04-01	-58 to 572°F (-50 to 300°C)
RTD1-S04-02	
RTD1-S04-03	
RTD1-S04-04	
RTD1-B01L06-01	
RTD1-B02L06-01	
RTD1-C04-03	
RTD1-C04R-03	
RTD1-C06-01	
RTD1-C06-03	
RTD1-C06R-03	
RTD1-C12-01	
RTD1-C12-02	
RTD1-C12-03	
RTD1-C12R-03	
RTD1-C18-01	
RTD1-C18-02	
RTD1-H04L01-02	
RTD1-H06L01-01	
RTD1-H06L01-02	
RTD1-H12L01-01	
RTD1-H12L01-02	
RTD1-H18L01-01	
RTD1-P06-01	-58 to 572°F (-50 to 300°C) Plug rated to 400°F (204°C)
RTD1-P12-01	
RTD1-P18-01	-58 to 572°F (-50 to 300°C), lead wire transition rated to 400°F (204°C)
RTD1-D08L10-01	
RTD1-T06L06-01	
RTD1-T12L06-01	
RTD1-T18L06-01	

J, K, & T Thermocouple Color Code

	White	+
J	Red	-
	Yellow	+
K	Red	-
	Blue	+
T	Blue	+
	Red	-