



# OKK Series Plinth Kits

## Description

Provides a mounting base and/or additional space for cable entry for OKK Series enclosures.

## Material

- 2.0 mm carbon steel

## Finish

- RAL 7024 graphite gray
- Textured powder coat finish

## Features

- ZAK0\* parts are plinth front/rear
- FLK\* are plinth sides
- Kits are available in 100mm [3.94 in] and 200mm [7.87 in] heights.
- Kits may be stacked to provide plinths over 200mm [7.87 in] high, if desired.



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

### Configuration Tool



View assembly guide with the link button or QR code below:

### Assembly Guide



## OKK Series Plinth Kits

Part Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
<a href="#">QTA-P010604C</a>	Retired	100 x 600 x 400 [3.94 x 23.62 x 15.75]	(1) ZAK061 and (1) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P010606C</a>	Retired	100 x 600 x 600 [3.94 x 23.62 x 23.62]	(1) ZAK061 and (1) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P010608C</a>	Retired	100 x 600 x 800 [3.94 x 23.62 x 31.50]	(1) ZAK061 and (1) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P010804C</a>	Retired	100 x 800 x 400 [3.94 x 31.50 x 15.75]	(1) ZAK081 and (1) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P010806C</a>	Retired	100 x 800 x 600 [3.94 x 31.50 x 23.62]	(1) ZAK081 and (1) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P010808C</a>	Retired	100 x 800 x 800 [3.94 x 31.50 x 31.50]	(1) ZAK081 and (1) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P011004C</a>	Retired	100 x 1000 x 400 [3.94 x 39.37 x 15.75]	(1) ZAK0A1 and (1) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P011006C</a>	Retired	100 x 1000 x 600 [3.94 x 39.37 x 23.62]	(1) ZAK0A1 and (1) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P011008C</a>	Retired	100 x 1000 x 800 [3.94 x 39.37 x 31.50]	(1) ZAK0A1 and (1) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P011204C</a>	Retired	100 x 1200 x 400 [3.94 x 47.24 x 15.75]	(1) ZAK0C1 and (1) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P011206C</a>	Retired	100 x 1200 x 600 [3.94 x 47.24 x 23.62]	(1) ZAK0C1 and (1) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P011208C</a>	Retired	100 x 1200 x 800 [3.94 x 47.24 x 31.50]	(1) ZAK0C1 and (1) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P020604C</a>	Retired	200 x 600 x 400 [7.87 x 23.62 x 15.75]	(1) ZAK062 and (2) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P020606C</a>	Retired	200 x 600 x 600 [7.87 x 23.62 x 23.62]	(1) ZAK062 and (2) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P020608C</a>	Retired	200 x 600 x 800 [7.87 x 23.62 x 31.50]	(1) ZAK062 and (2) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P020804C</a>	Retired	200 x 800 x 400 [7.87 x 31.50 x 15.75]	(1) ZAK082 and (2) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P020806C</a>	Retired	200 x 800 x 600 [7.87 x 31.50 x 23.62]	(1) ZAK082 and (2) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P020808C</a>	Retired	200 x 800 x 800 [7.87 x 31.50 x 31.50]	(1) ZAK082 and (2) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P021004C</a>	Retired	200 x 1000 x 400 [7.87 x 39.37 x 15.75]	(1) ZAK0A2 and (2) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P021006C</a>	Retired	200 x 1000 x 600 [7.87 x 39.37 x 23.62]	(1) ZAK0A2 and (2) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P021008C</a>	Retired	200 x 1000 x 800 [7.87 x 39.37 x 31.50]	(1) ZAK0A2 and (2) FLK18	<a href="#">PDF</a>
<a href="#">QTA-P021204C</a>	Retired	200 x 1200 x 400 [7.87 x 47.24 x 15.75]	(1) ZAK0C2 and (2) FLK14	<a href="#">PDF</a>
<a href="#">QTA-P021206C</a>	Retired	200 x 1200 x 600 [7.87 x 47.24 x 23.62]	(1) ZAK0C2 and (2) FLK16	<a href="#">PDF</a>
<a href="#">QTA-P021208C</a>	Retired	200 x 1200 x 800 [7.87 x 47.24 x 31.50]	(1) ZAK0C2 and (2) FLK18	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].