

OKK Series Side Exterior Panels



Application

Each exterior panel provides two side exterior surfaces for an OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Base and roof set
- Vertical frame rail set
- Door
- Exterior rear panel or additional door
- Subpanel

Multiple enclosure extensions bayed together can be sealed with a single set of side panels.

Material

- 1.5 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Package of two side panels
- Poured-in-place polyurethane gasket
- Includes mounting clips, screws, and gaskets (CLK013-KIT2F)

Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

Configuration Tool



Side Exterior Panels			
Part Number	Price	Fits Enclosure Size HxD	Drawing Link
DLK184	\$73.00	1800 x 400 [70.87 x 15.75]	PDF
DLK186	\$105.00	1800 x 600 [70.87 x 23.62]	PDF
DLK188	\$141.00	1800 x 800 [70.87 x 31.50]	PDF
DLK204	\$83.00	2000 x 400 [78.74 x 15.75]	PDF
DLK206	\$119.00	2000 x 600 [78.74 x 23.62]	PDF
DLK208	\$155.00	2000 x 800 [78.74 x 31.50]	PDF

Note: Dimensions in millimeters [inches].