

# OKK Series Swing Panels



## Application

Provides an interior mounting surface just behind the exterior door. Panel can swing open to allow access to the interior of the enclosure.

## Material

- 2.0 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Features

- Includes hinges, screws, and bolts
- Zinc alloy corner pieces.

## Listings

- IP44



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

### [Configuration Tool](#)



Swing Panels			
Part Number	Price	Fits Enclosure Size HxW	Drawing Link
<a href="#">DBI188</a>	\$241.00	1800 x 800 [70.87 x 31.50]	<a href="#">PDF</a>
<a href="#">DBI18A</a>	\$284.00	1800 x 1000 [70.87 x 39.37]	<a href="#">PDF</a>
<a href="#">DBI208</a>	\$278.00	2000 x 800 [78.74 x 31.50]	<a href="#">PDF</a>
<a href="#">DBI20A</a>	\$321.00	2000 x 1000 [78.74 x 39.37]	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].  
Swing panels kits consist of a panel and a mounting frame; each packaged separately.