

OKK Series Swing Panels



Application

Provides an interior mounting surface just behind the exterior door. Panel can swing open to allow access to the interior of the enclosure.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Features

- Includes hinges, screws, and bolts
- Zinc alloy corner pieces.

Listings

- IP44



Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

[Configuration Tool](#)



| Swing Panels | | | |
|---|----------|-----------------------------|---------------------|
| Part Number | Price | Fits Enclosure Size HxW | Drawing Link |
| DBI188 | \$259.00 | 1800 x 800 [70.87 x 31.50] | PDF |
| DBI18A | \$304.00 | 1800 x 1000 [70.87 x 39.37] | PDF |
| DBI208 | \$297.00 | 2000 x 800 [78.74 x 31.50] | PDF |
| DBI20A | \$344.00 | 2000 x 1000 [78.74 x 39.37] | PDF |
| Note: Dimensions in millimeters [inches]. Swing panels kits consist of a panel and a mounting frame; each packaged separately. | | | |