



# Tools – Pneumatic Die Grinder

## Pneumatic Die Grinder

The RUKO pneumatic grinder has a rubberized, non-slip handle that absorbs vibration and protects the users' hand from slipping while working. Speed is adjusted by a governor on top of the grinder. It has a tool adapter made of hardened steel. The exhaust port directs air backwards through the handle. It features an integrated air filter.



### RUKO Pneumatic Die Grinder Specifications

<b>Speed Range</b>	0 - 25,000 RPM
<b>Tool Adapter</b>	1/4 in, collet type
<b>Average Air Consumption</b>	4.00 cfm (113 liters/min)
<b>Air Inlet</b>	1/4 in
<b>Recommended Air Pressure</b>	90 psi (6.2 bar)
<b>Recommended Hose Size</b>	3/8 in
<b>Noise Level</b>	77 dB(A)
<b>Overall Length</b>	7.75 in (196.9 mm)
<b>Weight</b>	1.26 lb (570 g)

### RUKO Pneumatic Die Grinder

Part #	Price	Description
<b><u>116100US</u></b>	Retired	RUKO compact pneumatic grinder, 25,000 rpm, adjustable governor, rear exhaust, rubberized non-slip handle. 116101L coupling plug and (2) collet wrenches included.

### RUKO Pneumatic Die Grinder Kits

<b><u>116112US</u></b>	Retired	RUKO compact pneumatic grinder set, 14 pieces, includes 116100US compact pneumatic grinder, 116101L coupling plug, 116002US tungsten carbide rotary burr set and (2) collet wrenches.
<b><u>116113US</u></b>	Retired	RUKO compact pneumatic grinder set, 7 pieces, includes 116100US compact pneumatic grinder, 116101L coupling plug, 116001US tungsten carbide rotary burr set and (2) collet wrenches.

### Spare Parts

<b><u>116101L</u></b>	Retired	RUKO coupling plug, pneumatic, European, 1/4 inch nominal hose size, G1/4 male, steel (fits universal couplings)
<b><u>116119</u></b>	Retired	RUKO collet, 1/4 inch, replacement. For use with 116100US.



**116112US**



**116119**



**116101L**