

# RSCG Series NEMA 3R Wiring Trough



## Applications

These enclosures are designed to protect wiring against rain, sleet and snow in outdoor installations, or indoors against dripping water.

## Construction

- Trough and cover fabricated from 16 gauge carbon steel
- Drip shield top and smooth seamless sides, front and back, prevent rain, snow and sleet from entering the enclosure
- Embossed mounting holes are conveniently located on the back
- A slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are provided on bottom of enclosure

## Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces

## Listings

- UL 870
- UL File E32576
- CSA File LL66078
- Meets NEMA/EEMAC Types, 1 & 3R requirements


Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days

Color indicates shipping lead time in business days.

Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxDxL	Knockout Pattern
<b>RSCG040412</b>	\$46.50	16/16	4.06x4.06x12.13 (103x103x308)	B-A-C-D-A-B repeated
<b>RSCG040424</b>	\$66.00	16/16	4.06x4.06x24.13 (103x103x613)	B-A-C-D-A-B repeated
<b>RSCG040436</b>	\$86.00	16/16	4.06x4.06x36.13 (103x103x918)	B-A-C-D-A-B repeated
<b>RSCG040448</b>	\$105.00	16/16	4.06x4.06x48.13 (103x103x1222)	B-A-C-D-A-B repeated
<b>RSCG040460</b>	\$125.00	16/16	4.06x4.06x60.13 (103x103x1527)	B-A-C-D-A-B repeated
<b>RSCG060612</b>	\$57.00	16/16	6.06x6.06x12.13 (154x154x308)	B-A-C-D-A-B repeated
<b>RSCG060624</b>	\$90.00	16/16	6.06x6.06x24.13 (154x154x613)	B-A-C-D-A-B repeated
<b>RSCG060636</b>	\$119.00	16/16	6.06x6.06x36.13 (154x154x918)	B-A-C-D-A-B repeated
<b>RSCG060648</b>	\$148.00	16/16	6.06x6.06x48.13 (154x154x1222)	B-A-C-D-A-B repeated
<b>RSCG060660</b>	\$178.00	16/16	6.06x6.06x60.13 (154x154x1527)	B-A-C-D-A-B repeated
<b>RSCG060672</b>	\$207.00	16/16	6.06x6.06x72.13 (154x154x1832)	B-A-C-D-A-B repeated
<b>RSCG080824</b>	\$120.00	16/16	8.06x8.06x24.13 (205x205x613)	B-A-C-D-A-B repeated
<b>RSCG080836</b>	\$161.00	16/16	8.06x8.06x36.13 (205x205x918)	B-A-C-D-A-B repeated
<b>RSCG080848</b>	\$201.00	16/16	8.06x8.06x48.13 (205x205x1222)	B-A-C-D-A-B repeated
<b>RSCG080860</b>	\$242.00	16/16	8.06x8.06x60.13 (205x205x1527)	B-A-C-D-A-B repeated
<b>RSCG080872</b>	\$317.00	16/16	8.06x8.06x72.13 (205x205x1832)	B-A-C-D-A-B repeated

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

# RSCG Series NEMA 3R Wiring Trough



## KNOCKOUT SIZES

- B = 3/4" x 1" CONCENTRIC KO
- A = 1/2" x 3/4" CONCENTRIC KO
- C = 1" SOLID KO
- D = 1-1/4" SOLID KO

G19RSCG