

Tools – Hand Taps

Fractional and Metric Thread Hand Taps

High-speed steel fractional and metric size hand taps.



231100 shown

High-Speed Steel Fractional Size Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
	246080UNC3	1	\$9.75	8-32 UNC	1.77	2149029		246100UNF2	1	\$9.75	10-32 UNF	1.77	2149021
	246100UNC3	1	\$9.75	10-24 UNC	1.97	2149025		246014UNF2	1	\$6.50	1/4-28 UNF	1.97	2149003
	246014UNC3	1	\$5.75	1/4-20 UNC	1.97	2149007		246516UNF2	1	\$7.25	5/16-24 UNF	2.20	2149001
	246516UNC3	1	\$5.75	5/16-18 UNC	2.20	214900F							

High-Speed Steel Metric Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
	231030	1	\$4.00	M3x0.5	40.0	214025, 215025		235041-2	1	\$8.00	M4x0.5	45.0	214035, 215035
	231040	1	\$4.00	M4x0.7	45.0	214033, 215033		235050-2	1	\$8.50	M5x0.5	50.0	214045, 215045
	231050	1	\$4.00	M5x0.8	50.0	214042, 215042		235081-2	1	\$10.50	M8x1	56.0	214070, 215070
	231060	1	\$4.25	M6x1	50.0	214050, 215050		235122-2	1	\$11.00	M12x1	70.0	214110, 215110
	231080	1	\$4.75	M8x1.25	56.0	214068, 215068		235181-2	1	\$21.50	M18x1	80.0	17.0 mm
	231100	1	\$6.75	M10x1.5	70.0	214085, 215085		235301-2	1	\$44.50	M30x1.5	90.0	28.5 mm
	231120	1	\$8.25	M12x1.75	75.0	214102, 215102							

NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

High-Speed Steel NPT Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
231116NPT	1	\$15.00	1/16-27 NPT	2.56	214813, 250813T, 215813
231018NPT	1	\$13.50	1/8-27 NPT	2.56	214900R
231014NPT	1	\$14.75	1/4-18 NPT	2.76	214825, 250825T, 215825
231038NPT	1	\$20.75	3/8-18 NPT	2.95	37/64"
231012NPT	1	\$26.00	1/2-14 NPT	3.15	23/32"



231038NPT shown

Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

High-Speed Steel Conduit Thread Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
264009	1	\$20.50	PG-9	70.0	14.0 mm
264011	1	\$28.50	PG-11	80.0	17.25 mm
264016	1	\$40.50	PG-16	80.0	21.25 mm
264021	1	\$60.00	PG-21	90.0	26.75 mm
264029	1	\$92.00	PG-29	100.0	35.5 mm



RUKO Tools – Hand Taps



245004RO shown

Drill and Hand Tap Sets		
Part #	Price	Description
245004RO	\$72.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) metric size taps (M3, M4, M5, M6, M8, M10, M12), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.
245004USRO	\$85.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) SAE taps (8-32 UNC, 10-24 UNC, 10-32 UNF, 1/4-20 UNC, 1/4-28 UNF, 5/16-18 UNC, 5/16-24 UNF), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.
231004USRO	\$160.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (3) 1/8 x 27 NPT taps, (4) 1/4 x 18 NPT taps, (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.

RUKO Tools – Hand Tap Wrenches

Hand Tap Wrenches



241103 shown



241010 shown

Hand Tap Wrenches					
Part #	Pcs/Pkg	Price	Description	Construction Material	Use With
241010	1	\$25.50	Sliding T-handle ratcheting tap wrench	Chrome plated steel	M3 to M10, 1/8" to 3/8" taps
241020	1	\$29.00	Sliding T-handle ratcheting tap wrench	Chrome plated steel	M5 to M12, 7/32" to 1/2" taps
241103	1	\$14.50	Two-jaw chuck tap wrench	Die cast zinc housing, steel handles, hardened chuck jaws	M5 to M20, 1/4" to 3/4" taps
241112	1	\$7.50	Two-jaw chuck tap wrench	Die cast zinc housing, steel handles, hardened chuck jaws	M1 to M12, 1/8" to 1/2" taps