

# Tools – Hand Taps

## Fractional and Metric Thread Hand Taps

High-speed steel fractional and metric size hand taps.



**231100**

High-Speed Steel Fractional Size Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
	<a href="#">246080UNC3</a>	1	\$10.50	8-32 UNC	1.77	<a href="#">2149029</a>		<a href="#">246100UNF2</a>	1	\$10.50	10-32 UNF	1.77	<a href="#">2149021</a>
	<a href="#">246100UNC3</a>	1	\$10.50	10-24 UNC	1.97	<a href="#">2149025</a>		<a href="#">246014UNF2</a>	1	\$7.25	1/4-28 UNF	1.97	<a href="#">2149003</a>
	<a href="#">246014UNC3</a>	1	\$6.25	1/4-20 UNC	1.97	<a href="#">2149007</a>		<a href="#">246516UNF2</a>	1	\$8.00	5/16-24 UNF	2.20	<a href="#">2149001</a>
	<a href="#">246516UNC3</a>	1	\$6.25	5/16-18 UNC	2.20	<a href="#">214900F</a>							

High-Speed Steel Metric Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
	<a href="#">231030</a>	1	\$4.25	M3x0.5	40.0	<a href="#">214025</a> , <a href="#">215025</a>		<a href="#">235041-2</a>	1	\$8.50	M4x0.5	45.0	<a href="#">214035</a> , <a href="#">215035</a>
	<a href="#">231040</a>	1	\$4.25	M4x0.7	45.0	<a href="#">214033</a> , <a href="#">215033</a>		<a href="#">235050-2</a>	1	\$9.00	M5x0.5	50.0	<a href="#">214045</a> , <a href="#">215045</a>
	<a href="#">231050</a>	1	\$4.25	M5x0.8	50.0	<a href="#">214042</a> , <a href="#">215042</a>		<a href="#">235081-2</a>	1	\$11.00	M8x1	56.0	<a href="#">214070</a> , <a href="#">215070</a>
	<a href="#">231060</a>	1	\$4.50	M6X1	50.0	<a href="#">214050</a> , <a href="#">215050</a>		<a href="#">235122-2</a>	1	\$12.00	M12x1	70.0	<a href="#">214110</a> , <a href="#">215110</a>
	<a href="#">231080</a>	1	\$5.00	M8x1.25	56.0	<a href="#">214068</a> , <a href="#">215068</a>		<a href="#">235181-2</a>	1	\$23.50	M18x1	80.0	17.0 mm
	<a href="#">231100</a>	1	\$7.00	M10x1.5	70.0	<a href="#">214085</a> , <a href="#">215085</a>		<a href="#">235301-2</a>	1	\$48.50	M30x1.5	90.0	28.5 mm
	<a href="#">231120</a>	1	\$8.50	M12x1.75	75.0	<a href="#">214102</a> , <a href="#">215102</a>							

## NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

High-Speed Steel NPT Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
<a href="#">231116NPT</a>	1	\$16.00	1/16-27 NPT	2.56	<a href="#">214813</a> , <a href="#">250813T</a> , <a href="#">215813</a>
<a href="#">231018NPT</a>	1	\$14.50	1/8-27 NPT	2.56	<a href="#">214900R</a>
<a href="#">231014NPT</a>	1	\$15.50	1/4-18 NPT	2.76	<a href="#">214825</a> , <a href="#">250825T</a> , <a href="#">215825</a>
<a href="#">231038NPT</a>	1	\$22.00	3/8-18 NPT	2.95	37/64"
<a href="#">231012NPT</a>	1	\$27.00	1/2-14 NPT	3.15	23/32"



**231038NPT**

## Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

High-Speed Steel Conduit Thread Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
<a href="#">264009</a>	1	\$21.50	PG-9	70.0	14.0 mm
<a href="#">264011</a>	1	\$29.50	PG-11	80.0	17.25 mm
<a href="#">264016</a>	1	\$42.00	PG-16	80.0	21.25 mm
<a href="#">264021</a>	1	\$63.00	PG-21	90.0	26.75 mm
<a href="#">264029</a>	1	\$97.00	PG-29	100.0	35.5 mm



**264029**

# **RUKO** Tools – Hand Taps



**245004RO**

Drill and Hand Tap Sets		
Part #	Price	Description
<b>245004RO</b>	\$78.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) metric size taps (M3, M4, M5, M6, M8, M10, M12), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.
<b>245004USRO</b>	\$93.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) SAE taps (8-32 UNC, 10-24 UNC, 10-32 UNF, 1/4-20 UNC, 1/4-28 UNF, 5/16-18 UNC, 5/16-24 UNF), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.
<b>231004USRO</b>	\$170.00	RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (3) 1/8 x 27 NPT taps, (4) 1/4 x 18 NPT taps, (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.

# **RUKO** Tools – Hand Tap Wrenches

## Hand Tap Wrenches



**241103**



**241010**

Hand Tap Wrenches					
Part #	Pcs/Pkg	Price	Description	Construction Material	Use With
<b>241010</b>	1	\$26.00	Sliding T-handle ratcheting tap wrench	Chrome plated steel	M3 to M10, 1/8" to 3/8" taps
<b>241020</b>	1	\$29.50	Sliding T-handle ratcheting tap wrench	Chrome plated steel	M5 to M12, 7/32" to 1/2" taps
<b>241103</b>	1	\$14.50	Two-jaw chuck tap wrench	Die cast zinc housing, steel handles, hardened chuck jaws	M5 to M20, 1/4" to 3/4" taps
<b>241112</b>	1	\$7.50	Two-jaw chuck tap wrench	Die cast zinc housing, steel handles, hardened chuck jaws	M1 to M12, 1/8" to 1/2" taps