

# Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets



Your Enclosure Source®



## Applications

Designed to house electrical and electronic controls, instruments, and components. Provides protection from dust, dirt, oil and water. Consolets can be mounted on either of two sides to give a control surface inclined at 30° or 60°. Can be mounted on desks, machines, or pedestals.

## Construction

- 16 gauge carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Removable hinges.
- Poured-in-place oil- and water-resistant gasket.
- Standoffs provided for mounting optional sub-panels.
- Cable door stops included on SCE-12C\_, SCE-16C\_ and SCE-20C\_.
- Black mini 1/4-turn latches as required.
- Latches are opened or closed with a screwdriver.
- Ground studs on door and body.
- Mounting holes in back/bottom, depending on orientation.

## Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels power coated white

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

## Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-8C8ELJ</b>	\$122.00	7.44 x 8.00 x 7.09 [189 x 203 x 180]	<a href="#">PDF</a>	<b>SCE-8P8C</b>	\$7.00
<b>SCE-8C12ELJ</b>	\$134.00	7.44 x 12.00 x 7.09 [189 x 305 x 180]	<a href="#">PDF</a>	<b>SCE-8P12C</b>	\$11.00
<b>SCE-8C16ELJ</b>	\$149.00	7.44 x 16.00 x 7.09 [189 x 406 x 180]	<a href="#">PDF</a>	<b>SCE-8P16C</b>	\$15.25
<b>SCE-8C20ELJ</b>	\$161.00	7.44 x 20.00 x 7.09 [189 x 508 x 180]	<a href="#">PDF</a>	<b>SCE-8P20C</b>	\$19.25
<b>SCE-12C12ELJ</b>	\$158.00	10.91 x 12.00 x 9.09 [277 x 305 x 231]	<a href="#">PDF</a>	<b>SCE-12P12C</b>	\$17.50
<b>SCE-12C16ELJ</b>	\$176.00	10.91 x 16.00 x 9.09 [277 x 406 x 231]	<a href="#">PDF</a>	<b>SCE-12P16C</b>	\$24.00
<b>SCE-12C20ELJ</b>	\$194.00	10.91 x 20.00 x 9.09 [277 x 508 x 231]	<a href="#">PDF</a>	<b>SCE-12P20C</b>	\$30.50
<b>SCE-12C24ELJ</b>	\$208.00	10.91 x 24.00 x 9.09 [277 x 610 x 231]	<a href="#">PDF</a>	<b>SCE-12P24C</b>	\$37.00
<b>SCE-16C16ELJ</b>	\$206.00	14.38 x 16.00 x 11.09 [365 x 406 x 282]	<a href="#">PDF</a>	<b>SCE-16P14</b>	\$26.50
<b>SCE-16C20ELJ</b>	\$226.00	14.38 x 20.00 x 11.09 [365 x 508 x 282]	<a href="#">PDF</a>	<b>SCE-16P20C</b>	\$41.50
<b>SCE-16C24ELJ</b>	\$247.00	14.38 x 24.00 x 11.09 [365 x 610 x 282]	<a href="#">PDF</a>	<b>SCE-16P24C</b>	\$50.00
<b>SCE-16C30ELJ</b>	\$283.00	14.38 x 30.00 x 11.09 [365 x 762 x 282]	<a href="#">PDF</a>	<b>SCE-16P30C</b>	\$59.00
<b>SCE-20C20ELJ</b>	\$259.00	14.38 x 36.00 x 11.09 [365 x 914 x 282]	<a href="#">PDF</a>	<b>SCE-20P20C</b>	\$52.00
<b>SCE-20C24ELJ</b>	\$289.00	17.84 x 20.00 x 13.09 [453 x 508 x 332]	<a href="#">PDF</a>	<b>SCE-20P24C</b>	\$56.00
<b>SCE-20C30ELJ</b>	\$331.00	17.84 x 24.00 x 13.09 [453 x 610 x 332]	<a href="#">PDF</a>	<b>SCE-20P30C</b>	\$62.00

Note: Dimensions in inches [millimeters].