

Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instruments, and components. Provides protection from dust, dirt, oil and water. Consolets can be mounted on either of two sides to give a control surface inclined at 30° or 60°. Can be mounted on desks, machines, or pedestals.

Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Removable hinges
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Cable door stops included on SCE-12C_, SCE-16C_ and SCE-20C_
- Black, mini 1/4-turn latches as required.
- Latches are opened or closed with a screwdriver.
- Ground studs on door and body
- Mounting holes in back/bottom, depending on orientation

Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels are power coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 12 and 13 Operator Consolets

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-8C8ELJ	\$139.00	7.44 x 8.00 x 7.09 [189 x 203 x 180]	PDF	SCE-8P8C	\$7.75
SCE-8C12ELJ	\$152.00	7.44 x 12.00 x 7.09 [189 x 305 x 180]	PDF	SCE-8P12C	\$12.50
SCE-8C16ELJ	\$169.00	7.44 x 16.00 x 7.09 [189 x 406 x 180]	PDF	SCE-8P16C	\$17.00
SCE-8C20ELJ	\$183.00	7.44 x 20.00 x 7.09 [189 x 508 x 180]	PDF	SCE-8P20C	\$22.00
SCE-12C12ELJ	\$179.00	10.91 x 12.00 x 9.09 [277 x 305 x 231]	PDF	SCE-12P12C	\$19.75
SCE-12C16ELJ	\$200.00	10.91 x 16.00 x 9.09 [277 x 406 x 231]	PDF	SCE-12P16C	\$27.00
SCE-12C20ELJ	\$220.00	10.91 x 20.00 x 9.09 [277 x 508 x 231]	PDF	SCE-12P20C	\$34.50
SCE-12C24ELJ	\$237.00	10.91 x 24.00 x 9.09 [277 x 610 x 231]	PDF	SCE-12P24C	\$42.00
SCE-16C16ELJ	\$233.00	14.38 x 16.00 x 11.09 [365 x 406 x 282]	PDF	SCE-16P14	\$29.50
SCE-16C20ELJ	\$257.00	14.38 x 20.00 x 11.09 [365 x 508 x 282]	PDF	SCE-16P20C	\$46.50
SCE-16C24ELJ	\$281.00	14.38 x 24.00 x 11.09 [365 x 610 x 282]	PDF	SCE-16P24C	\$57.00
SCE-16C30ELJ	\$321.00	14.38 x 30.00 x 11.09 [365 x 762 x 282]	PDF	SCE-16P30C	\$67.00
SCE-20C20ELJ	\$294.00	14.38 x 36.00 x 11.09 [365 x 914 x 282]	PDF	SCE-20P20C	\$58.00
SCE-20C24ELJ	\$328.00	17.84 x 20.00 x 13.09 [453 x 508 x 332]	PDF	SCE-20P24C	\$63.00
SCE-20C30ELJ	\$375.00	17.84 x 24.00 x 13.09 [453 x 610 x 332]	PDF	SCE-20P30C	\$70.00

Note: Dimensions in inches [millimeters].