

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Operator



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instruments, and components. Provides a degree of protection from dust, dirt, oil and water. Consoles can be mounted on either of two sides to give a control surface inclined at 30° or 60°. Can be mounted on desks, machines, or pedestals.

- Construction
- 16 gauge stainless steel type 304 or 316L.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Removable hinges.
- Poured-in-place oil- and water-resistant gasket.
- Standoffs provided for mounting optional sub-panels.
- Cable door stops included on SCE-12C_, SCE-16C_ and SCE-20C_.
- Black mini 1/4-turn latches as required.
- Latches are opened or closed with a screwdriver.
- Ground studs on door and body.
- Mounting holes in back/bottom, depending on orientation.

Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels power coated white

Listings

- NEMA Type 3R, 4, 4X, 12 and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 304 Stainless Steel Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-8C8ELJSS	\$582.00	7.44 x 8.00 x 7.09 [189 x 203 x 180]	PDF	SCE-8P8C	\$7.00
SCE-8C12ELJSS	\$622.00	7.44 x 12.00 x 7.09 [189 x 305 x 180]	PDF	SCE-8P12C	\$11.00
SCE-8C16ELJSS	\$703.00	7.44 x 16.00 x 7.09 [189 x 406 x 180]	PDF	SCE-8P16C	\$15.25
SCE-8C20ELJSS	\$781.00	7.44 x 20.00 x 7.09 [189 x 508 x 180]	PDF	SCE-8P20C	\$19.25
SCE-12C12ELJSS	\$766.00	10.91 x 12.00 x 9.09 [277 x 305 x 231]	PDF	SCE-12P12C	\$17.50
SCE-12C16ELJSS	\$791.00	10.91 x 16.00 x 9.09 [277 x 406 x 231]	PDF	SCE-12P16C	\$24.00
SCE-12C20ELJSS	\$811.00	10.91 x 20.00 x 9.09 [277 x 508 x 231]	PDF	SCE-12P20C	\$30.50
SCE-12C24ELJSS	\$882.00	10.91 x 24.00 x 9.09 [277 x 610 x 231]	PDF	SCE-12P24C	\$37.00
SCE-16C16ELJSS	\$811.00	14.38 x 16.00 x 11.09 [365 x 406 x 282]	PDF	SCE-16P14	\$26.50
SCE-16C20ELJSS	\$882.00	14.38 x 20.00 x 11.09 [365 x 508 x 282]	PDF	SCE-16P20C	\$41.50
SCE-16C24ELJSS	\$950.00	14.38 x 24.00 x 11.09 [365 x 610 x 282]	PDF	SCE-16P24C	\$50.00
SCE-20C20ELJSS	\$950.00	14.38 x 36.00 x 11.09 [365 x 914 x 282]	PDF	SCE-20P20C	\$52.00
SCE-20C24ELJSS	\$1,092.00	17.84 x 20.00 x 13.09 [453 x 508 x 332]	PDF	SCE-20P24C	\$56.00
SCE-20C30ELJSS	\$1,310.00	17.84 x 24.00 x 13.09 [453 x 610 x 332]	PDF	SCE-20P30C	\$62.00

Note: Dimensions in inches [millimeters].

Enviroline Junction Series NEMA 3R, 4, 12, and 13 Operator Consolets



Your Enclosure Source®

Dimensions

