

# NEMA 3R, 12, and 13 Desk Consoles



## Applications

Intended for indoor use to provide a degree of protection to personnel against access to hazardous parts, also to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects and falling dirt, to provide a degree of protection with respect to harmful effects on the equipment due to the ingress of water, splashing water. Designed for use in a standing or sitting position with single or dual access and top that opens for easy accessibility.

## Construction

- 14 gauge carbon steel.
- Seams continuously welded and ground smooth.
- 25° sloped top.
- Door props on sloped door to hold in the open position.
- Poured-in-place oil- and water-resistant gasket.
- Flange trough collar around all sides of door opening.
- Concealed hinges.
- Removable doors.
- Removable print pocket.
- Ground studs on door and body.
- Rubber pads with provision for leveling pads on bottom of enclosure.
- Black 1/4-turn latches on top door.
- Keylocking black 3-point flush swing handle in front door of single access, front and rear doors on dual access.
- Mounting studs welded on interior back for mounting optional subpanels on single access console.
- Mounting channels welded on sides of interior body for mounting optional subpanels on dual access console.
- Mounting hardware included for one optional subpanel.

## Finish

- ANSI 61 gray powder coated inside and out.
- Optional panels are powder coated white.

## Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



# NEMA 3R, 12, and 13 Desk Consoles



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

## NEMA 3R, 12, and 13 Desk Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>Single-Access Single-Door</b>					
<b>SCE-403716SDC</b>	\$1,323.00	41.18 x 37.25 x 21.50 [1046 x 946 x 546]	<a href="#">PDF</a>	<b>SCE-36P30</b>	\$134.00
<b>SCE-463719SDC</b>	\$1,779.00	47.18 x 37.25 x 24.50 [1198 x 946 x 622]	<a href="#">PDF</a>	<b>SCE-36P36</b>	\$157.00
<b>Dual-Access Single-Door</b>					
<b>SCE-463719DC</b>	\$1,879.00	47.18 x 37.25 x 25.57 [1198 x 946 x 649]	<a href="#">PDF</a>	<b>SCE-36P36</b>	\$157.00
<b>Single-Access Overlapping Double-Door</b>					
<b>SCE-464919SDC</b>	\$2,058.00	47.18 x 49.25 x 24.50 [1198 x 1251 x 622]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$204.00
<b>SCE-466019SDC</b>	\$2,664.00	47.18 x 59.88 x 24.50 [1198 x 1521 x 622]	<a href="#">PDF</a>	<b>SCE-60PC36</b>	\$240.00
<b>Dual-Access Overlapping Double-Door</b>					
<b>SCE-464919DC</b>	\$2,164.00	47.18 x 49.25 x 25.57 [1198 x 1251 x 649]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$204.00
<b>SCE-466019DC</b>	\$2,877.00	47.18 x 59.88 x 25.57 [1198 x 1521 x 649]	<a href="#">PDF</a>	<b>SCE-60PC36</b>	\$240.00

Note: Dimensions in inches [millimeters].