NEMA 3R, 12, and 13 Operator Consoles

SAGINAW CONTROL & ENGINEERING
Your Enclosure Source ®

Applications

Designed for electronic controls and instruments. Equipment can be mounted on the sloping control panel door. Interior components mount to stationary panels. Provides protection from dirt, oil, dust and water.

Construction

- 14-gauge carbon steel
- Sloping control panel door is attached with concealed hinge on bottom edge.
- Door opens 90°
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Seams continuously welded and ground smooth
- Poured-in-place oil- and water-resistant gasket on door
- Interior print pocket
- Optional back and side panels are mounted on collar studs.
- Removable eyebolts
- Ground stud on door and body
- Hole plugs are provided to seal holes in bottom of enclosure.

Finish

- ANSI 61 Gray powder coated inside and out
- Optional subpanels are power coated white.

Listings

- NEMA Type 3R, 12 and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55

c UL us

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

NEMA 3R, 12, and 13 Operator Consoles							
Part Number	*Price*	*Size HxWxD*	*Drawing Link*	*Optional Back Subpanel*	*Price*	*Optional Side-Mount Panel*	*Price*
SCE-924B	$1,778.00	48.00 x 24.00 x 18.00 [1219 x 610 x 457]	PDF	***SCE-30P20***	$91.00	***SCE-30P20***	$91.00
SCE-936B	$2,184.00	48.00 x 36.00 x 18.00 [1219 x 914 x 457]	PDF	***SCE-30P30***	$91.00	***SCE-30P20***	$136.00
Note: Dimensions in inches [millimeters]. **Consoles can accommodate one back subpanel and two side-mount subpanels.**							

NEMA 3R, 12, and 13 Operator Consoles

SAGINAW CONTROL & ENGINEERING
Your Enclosure Source ®

Dimensions