

# Disconnect Handle Applications for Stainless Steel Disconnect Enclosures



## Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F\_SO\_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C.**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft).
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**

## Available at AutomationDirect.com

Disconnect Enclosure Series	AutomationDirect F_SO_C Series	Socomec 37299002 and 37299003	Fuji BW9F Series
<b>SCE-<u>HS</u>_SS_LP</b>	✓	✓	✓
<b>SCE-<u>XM</u>_SS_</b>	✓	✓	✓
<b>SCE-<u>XM</u>_EQ_SS_</b>	✓	✓	✓
<b>SCE-<u>XM</u>_EW_SS_</b>	✓	✓	✓

## Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators.
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers.
- General Electric** Type STDA flange handles and variable depth operating.
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers.
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers.
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

## Other Brands

Disconnect Enclosures Series	Square D 9422 Series	Allen-Bradley 1494F and 1494D Series	Allen-Bradley 1494V and 140U Series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
<b>SCE-<u>HS</u>_SS_LP</b>	✓	✗	✓	✓	✓	✓	✓
<b>SCE-<u>XM</u>_SS_</b>	✓	✗	✓	✓	✓	✓	✓
<b>SCE-<u>XM</u>_EQ_SS_</b>	✓	✗	✓	✓	✓	✓	✓
<b>SCE-<u>XM</u>_EW_SS_</b>	✓	✗	✓	✓	✓	✓	✓

Note: For more detail on compatible disconnects, see the "Other Documents" section of the enclosure's item page.

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Single-Door Wall-Mount Right-Flange Disconnect



Your Enclosure Source®



## Applications

Designed to house most standard disconnects. For outdoor applications a drip shield is recommended.

## Construction

- 14-gauge stainless steel Type 304 or 316L.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Poured-in-place oil- and water-resistant gasket.
- Collar studs provided for mounting optional sub-panels.
- Holes provided in body for mounting disconnect operating handle and operating mechanism.
- Stainless steel concealed hinges.
- Doors are interchangeable and easily removed by pulling hinge pin.
- 3-point latching mechanism.
- Latches are opened or closed with screwdriver (optional tamper-resistant inserts available).
- Mounting holes in back of enclosure.
- Mounting hardware, sealing washers and hole plugs included.
- Black 1/4-turn latches as required.
- Removable print pocket.
- Ground studs on door and body.
- Black zinc die cast coinproof/padlocking handle.
- Note: Disconnect switch (or circuit breaker) and operating mechanism are not furnished with this enclosure.

## Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, & 13
- cULus Listed Type 3R, 4, 4X, & 12 [File E69392]
- IEC 60529 IP66



# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Single-Door Wall-Mount Right-Flange Disconnect



Your Enclosure Source®

## Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount Right-Flange Disconnect

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-20XEL2108SSLP</b>	\$902.00	<b>SCE-20XEL2108SS6LP</b>	\$1,083.00	20.00 x 21.38 x 9.10 [508 x 543 x 231]	<a href="#">PDF</a>	<b>SCE-20P20</b>	\$47.00
<b>SCE-24XEL2108SSLP</b>	\$983.00	<b>SCE-24XEL2108SS6LP</b>	\$1,180.00	24.00 x 21.38 x 9.10 [610 x 543 x 231]	<a href="#">PDF</a>	<b>SCE-24P20</b>	\$60.00
<b>SCE-24XEL2508SSLP</b>	\$1,069.00	<b>SCE-24XEL2508SS6LP</b>	\$1,283.00	24.00 x 25.38 x 9.10 [610 x 645 x 231]	<a href="#">PDF</a>	<b>SCE-24P24</b>	\$70.00
<b>SCE-24XEL2510SSLP</b>	\$1,143.00	<b>SCE-24XEL2510SS6LP</b>	\$1,372.00	24.00 x 25.38 x 11.10 [610 x 645 x 282]	<a href="#">PDF</a>	<b>SCE-24P24</b>	\$70.00
<b>SCE-30XEL2508SSLP</b>	\$1,253.00	<b>SCE-30XEL2508SS6LP</b>	\$1,503.00	30.00 x 25.38 x 9.10 [762 x 645 x 231]	<a href="#">PDF</a>	<b>SCE-30P24</b>	\$84.00
<b>SCE-30XEL2510SSLP</b>	\$1,365.00	<b>SCE-30XEL2510SS6LP</b>	\$1,638.00	30.00 x 25.38 x 11.10 [762 x 645 x 282]	<a href="#">PDF</a>	<b>SCE-30P24</b>	\$84.00
<b>SCE-36XEL2508SSLP</b>	\$1,437.00	<b>SCE-36XEL2508SS6LP</b>	\$1,725.00	36.00 x 25.38 x 9.10 [914 x 645 x 231]	<a href="#">PDF</a>	<b>SCE-36P24</b>	\$100.00
<b>SCE-36XEL3110SSLP</b>	\$1,691.00	<b>SCE-36XEL3110SS6LP</b>	\$2,029.00	36.00 x 31.38 x 11.10 [914 x 797 x 282]	<a href="#">PDF</a>	<b>SCE-36P30</b>	\$134.00
<b>SCE-36XEL3112SSLP</b>	\$1,788.00	<b>SCE-36XEL3112SS6LP</b>	\$2,146.00	36.00 x 31.38 x 13.10 [914 x 797 x 333]	<a href="#">PDF</a>	<b>SCE-36P30</b>	\$134.00
<b>SCE-42XEL3110SSLP</b>	\$1,926.00	<b>SCE-42XEL3110SS6LP</b>	\$2,311.00	42.00 x 31.38 x 11.10 [1067 x 797 x 282]	<a href="#">PDF</a>	<b>SCE-42P30</b>	\$154.00
<b>SCE-42XEL3112SSLP</b>	\$2,034.00	<b>SCE-42XEL3112SS6LP</b>	\$2,440.00	42.00 x 31.38 x 13.10 [1067 x 797 x 333]	<a href="#">PDF</a>	<b>SCE-42P30</b>	\$154.00
<b>SCE-42XEL3712SSLP</b>	\$2,209.00	<b>SCE-42XEL3712SS6LP</b>	\$2,650.00	42.00 x 37.38 x 13.10 [1067 x 949 x 333]	<a href="#">PDF</a>	<b>SCE-42P36</b>	\$181.00
<b>SCE-42XEL3716SSLP</b>	\$2,471.00	<b>SCE-42XEL3716SS6LP</b>	\$2,966.00	42.00 x 37.38 x 17.10 [1067 x 949 x 434]	<a href="#">PDF</a>	<b>SCE-42P36</b>	\$181.00
<b>SCE-48XEL3710SSLP</b>	\$2,276.00	<b>SCE-48XEL3710SS6LP</b>	\$2,731.00	48.00 x 37.38 x 11.10 [1219 x 949 x 282]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$204.00
<b>SCE-48XEL3712SSLP</b>	\$2,404.00	<b>SCE-48XEL3712SS6LP</b>	\$2,885.00	48.00 x 37.38 x 13.10 [1219 x 949 x 333]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$204.00
<b>SCE-48XEL3716SSLP</b>	\$2,673.00	<b>SCE-48XEL3716SS6LP</b>	\$3,208.00	48.00 x 37.38 x 17.10 [1219 x 949 x 434]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$204.00
<b>SCE-60XEL3712SSLP</b>	\$3,001.00	<b>SCE-60XEL3712SS6LP</b>	\$3,601.00	60.00 x 37.38 x 13.10 [1524 x 949 x 333]	<a href="#">PDF</a>	<b>SCE-60P36</b>	\$251.00
<b>SCE-60XEL3716SSLP</b>	\$3,283.00	<b>SCE-60XEL3716SS6LP</b>	\$3,940.00	60.00 x 37.38 x 17.10 [1524 x 949 x 434]	<a href="#">PDF</a>	<b>SCE-60P36</b>	\$251.00

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Single-Door Wall-Mount Right-Flange Disconnect



## Dimensions

