

Disconnect Handle Applications for Carbon Steel Disconnect Enclosures

Designed to house the following available at AutomationDirect.com



- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_SO_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C.**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft).
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**

Disconnect Enclosure Series	Available at AutomationDirect.com		
	AutomationDirect F_SO_C Series	Socomec 37299002 and 37299003	Fuji BW9F Series
SCE-SA_LPPL Series	✓	✓	✓
SCE-HS_LP Series	✓	✓	✓
SCE-XVR_Series	✓	✓	✓
SCE-X_D_Series	✓	✓	✓
SCE-X_LP Series	✓	✓	✓
SCE-XM_Series	✓	✓	✓
SCE-XM_EQ_Series	✓	✓	✓
SCE-XM_EW_Series	✓	✓	✓
SCE-XD_Series	✓	✓	✓


Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators.
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers.
- General Electric** Type STDA flange handles and variable depth operating.
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers.
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers.
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Disconnect Enclosures Series	Other Brands						
	Square D 9422 Series	Allen-Bradley 1494F and 1494D Series	Allen-Bradley 1494V and 140U Series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
SCE-SA_LPPL Series	✓	✗	✓	✓	✓	✓	✓
SCE-HS_LP Series	✓	✗	✓	✓	✓	✓	✓
SCE-XVR_Series	✓	✗	✓	✓	✓	✓	✓
SCE-X_D_Series	✓	✗	✓	✓	✓	✓	✓
SCE-X_LP Series	✓	✗	✓	✓	✓	✓	✓
SCE-XM_Series	✓	✗	✓	✓	✓	✓	✓
SCE-XM_EQ_Series	✓	✗	✓	✓	✓	✓	✓
SCE-XM_EW_Series	✓	✗	✓	✓	✓	✓	✓
SCE-XD_Series	✓	✗	✓	✓	✓	✓	✓

Note: For more detail on compatible disconnects, see the "Other Documents" section of the enclosure's item page.

Heavy Duty Freestanding Enclosures with External Disconnect



Applications

Designed to house the main power supply in external enclosure on the right side of main enclosure, keeping the live side of the power supply separate from the primary electrical equipment. Provides protection from dirt, dust, oil and water and can house most standard type disconnects.

Construction

- 1/8 in [3mm]
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Body stiffeners in large enclosures for extra rigidity.
- Heavy duty lifting eyes anchor into reinforced top.
- Removable center posts permit easy subpanel installation.
- Concealed hinges.
- Black zinc die cast coinproof/padlocking handle on main door with black zinc die cast padlocking handle on slave doors.
- 3-point latching mechanism.
- Large removable print pockets.
- Poured-in-place oil- and water-resistant gasket.
- Removable subpanels mount on collar studs.
- Defeater on master door requires a screwdriver to open.
- Mechanical interlock activated by the External Disconnect prevents main door of the enclosure from being closed unless the EXD enclosure is first closed.
- Mechanical interlock activated by master door prevents slave doors from being opened first. Doors can be closed in any order.
- Hole plugs provided to seal holes in bottom of enclosure.
- Ground stud on door and body.
- Provisions for light kit.

Finish


- ANSI 61 gray powder coated inside and out.
- Included subpanels are powder coated white, or galvanized steel for part numbers ending in G.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



Heavy Duty Single-Door Freestanding Enclosures with External Disconnect



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Single-Door with Powder Coated Subpanel

Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel
SCE-72XD2818	\$3,541.00	72.00 x 27.50 x 19.07 [1829 x 699 x 484]	PDF	SCE-64P25
SCE-72XD3418	\$3,763.00	72.00 x 33.50 x 19.07 [1829 x 851 x 484]	PDF	SCE-64P31
SCE-72XD4018	\$3,986.00	72.00 x 39.50 x 19.07 [1829 x 1003 x 484]	PDF	SCE-64P37
SCE-84XD4018	\$4,265.00	84.00 x 39.50 x 19.07 [2134 x 1003 x 484]	PDF	SCE-76P37
SCE-90XD4018	\$4,463.00	90.00 x 39.50 x 19.07 [2286 x 1003 x 484]	PDF	SCE-82P37

Note: Dimensions in inches [millimeters].

Single-Door with Galvanized Subpanel


Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel
SCE-72XD2818G	\$3,575.00	72.00 x 27.50 x 19.07 [1829 x 699 x 484]	PDF	SCE-64P25GALV
SCE-72XD3418G	\$3,837.00	72.00 x 33.50 x 19.07 [1829 x 851 x 484]	PDF	SCE-64P31GALV
SCE-72XD4018G	\$4,025.00	72.00 x 39.50 x 19.07 [1829 x 1003 x 484]	PDF	SCE-64P37GALV
SCE-84XD4018G	\$4,319.00	84.00 x 39.50 x 19.07 [2134 x 1003 x 484]	PDF	SCE-76P37GALV
SCE-90XD4018G	\$4,517.00	90.00 x 39.50 x 19.07 [2286 x 1003 x 484]	PDF	SCE-82P37GALV

Note: Dimensions in inches [millimeters].

Heavy Duty Double-Door Freestanding Enclosures with External Disconnect



Your Enclosure Source®



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	


Double-Door with Powder Coated Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel
SCE-72XD5418	\$5,093.00	72.00 x 53.75 x 19.07 [1829 x 1365 x 484]	PDF	SCE-64P52
SCE-72XD6618	\$5,550.00	72.00 x 65.75 x 19.07 [1829 x 1670 x 484]	PDF	SCE-64P64
SCE-72XD7818	\$6,007.00	72.00 x 77.75 x 19.07 [1829 x 1975 x 484]	PDF	SCE-64P76
SCE-84XD7818	\$6,504.00	84.00 x 77.75 x 19.07 [2134 x 1975 x 484]	PDF	SCE-76P76
SCE-90XD7818	\$6,844.00	90.00 x 77.75 x 19.07 [2286 x 1975 x 484]	PDF	SCE-82P76

Note: Dimensions in inches [millimeters].

Double-Door with Galvanized Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel
SCE-72XD5418G	\$5,151.00	72.00 x 53.75 x 19.07 [1829 x 1365 x 484]	PDF	SCE-64P52GALV
SCE-72XD6618G	\$5,713.00	72.00 x 65.75 x 19.07 [1829 x 1670 x 484]	PDF	SCE-64P64GALV
SCE-72XD7818G	\$6,160.00	72.00 x 77.75 x 19.07 [1829 x 1975 x 484]	PDF	SCE-64P76GALV
SCE-84XD7818G	\$6,650.00	84.00 x 77.75 x 19.07 [2134 x 1975 x 484]	PDF	SCE-76P76GALV
SCE-90XD7818G	\$7,025.00	90.00 x 77.75 x 19.07 [2286 x 1975 x 484]	PDF	SCE-82P76GALV

Note: Dimensions in inches [millimeters].

Heavy Duty Three-Door Freestanding Enclosures with External Disconnect





Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Three-Door with Powder Coated Subpanel					
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel 1	Included Subpanel 2
SCE-72XD3EQ18	\$7,303.00	72.00 x 99.50 x 19.07 [1829 x 2527 x 484]	PDF	SCE-64P64*	SCE-64P31
SCE-72XD3EW18	\$8,022.00	72.00 x 117.50 x 19.07 [1829 x 2985 x 484]	PDF	SCE-64P76*	SCE-64P37
SCE-84XD3EW18	\$8,763.00	84.00 x 117.50 x 19.07 [2134 x 2985 x 484]	PDF	SCE-76P76*	SCE-76P37
Note: Dimensions in inches [millimeters]. * Two of this subpanel part included.					

Three-Door with Galvanized Subpanel					
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel 1	Included Subpanel 2
SCE-72XD3EQ18G	\$7,479.00	72.00 x 99.50 x 19.07 [1829 x 2527 x 484]	PDF	SCE-64P31GALV*	SCE-64P64GALV
SCE-72XD3EW18G	\$8,226.00	72.00 x 117.50 x 19.07 [1829 x 2985 x 484]	PDF	SCE-76P37GALV*	SCE-76P76GALV
SCE-84XD3EW18G	\$9,011.00	84.00 x 117.50 x 19.07 [2134 x 2985 x 484]	PDF	SCE-64P37GALV*	SCE-64P76GALV
Note: Dimensions in inches [millimeters]. * Two of this subpanel part included.					

Heavy Duty Four-Door Freestanding Enclosure with External Disconnect




Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Four-Door with Powder Coated Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanels
SCE-84XD4EW18	\$11,077.00	84.00 x 157.50 x 19.07 [2134 x 4001 x 484]	PDF	SCE-76P76*
SCE-90XD4EW18	\$11,447.00	90.00 x 157.50 x 19.07 [2286 x 4001 x 484]	PDF	SCE-82P76*
Note: Dimensions in inches [millimeters]. * Two of this subpanel part included.				

Four-Door with Galvanized Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanels
SCE-84XD4EW18G	\$11,451.00	84.00 x 157.50 x 19.07 [2134 x 4001 x 484]	PDF	SCE-76P76GALV*
SCE-90XD4EW18G	\$11,823.00	90.00 x 157.50 x 19.07 [2286 x 4001 x 484]	PDF	SCE-82P76GALV*
Note: Dimensions in inches [millimeters]. * Two of this subpanel part included.				

Heavy Duty Five-Door Freestanding Enclosure with External Disconnect



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Five-Door with Powder Coated Subpanel

Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel 1	Included Subpanel 2
SCE-84XD5EW18	\$13,676.00	84.00 x 196.75 x 19.05 [2134 x 4997 x 484]	PDF	SCE-76P76	SCE-76P37
SCE-90XD5EW18	\$14,214.00	90.00 x 196.75 x 19.05 [2286 x 4997 x 484]	PDF	SCE-82P76	SCE-82P37

Note: Dimensions in inches [millimeters].


Five-Door with Galvanized Subpanel

Part Number	Price	Size HxWxD	Drawing Link	Included Subpanel 1	Included Subpanel 2
SCE-84XD5EW18G	\$14,132.00	84.00 x 196.75 x 19.05 [2134 x 4997 x 484]	PDF	SCE-82P37GALV*	SCE-82P76GALV
SCE-90XD5EW18G	\$14,678.00	90.00 x 196.75 x 19.05 [2286 x 4997 x 484]	PDF	SCE-76P37GALV*	SCE-76P76GALV

Note: Dimensions in inches [millimeters].

* Two of this subpanel part included.

Heavy Duty Six-Door Freestanding Enclosure with External Disconnect



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Six-Door with Powder Coated Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanels
SCE-84XD6EW18	\$16,613.00	84.00 x 235.00 x 19.05 [2134 x 5969 x 484]	PDF	SCE-76P76**
SCE-90XD6EW18	\$17,169.00	90.00 x 252.00 x 19.05 [2286 x 6401 x 484]	PDF	SCE-82P76**

Note: Dimensions in inches [millimeters].
 ** Three of this subpanel part included.

Six-Door with Galvannized Subpanel				
Part Number	Price	Size HxWxD	Drawing Link	Included Subpanels
SCE-84XD6EW18G	\$17,207.00	84.00 x 252.00 x 19.05 [2134 x 6401 x 484]	PDF	SCE-76P76GALV**
SCE-90XD6EW18G	\$17,765.00	90.00 x 252.00 x 19.05 [2286 x 6401 x 484]	PDF	SCE-82P76GALV**

Note: Dimensions in inches [millimeters].
 ** Three of this subpanel part included.

Heavy Duty Freestanding Enclosures with External Disconnect



Dimensions

