

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding



Your Enclosure Source®



Applications

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides a degree of protection from dust, dirt, water and oil. The enclosures are extra deep for applications requiring more interior space.

Construction

- 12-gauge stainless steel Type 304
- Removable and interchangeable doors
- Stainless steel concealed hinges
- Seams continuously welded and ground smooth
- Strong, rigid construction with stiffeners welded on backs of single access boxes
- Lifting eyes for easy handling
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Flange trough collar around all sides of door opening
- A removable print pocket is provided on door with 3-point latch.
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Provisions for light kit

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604818SSFSD	\$8,299.00	60.00 x 48.00 x 19.05 [1524 x 1219 x 484]	PDF	SCE-60P48F1	\$503.00
SCE-724818SSFSD	\$9,141.00	72.00 x 48.00 x 19.05 [1829 x 1219 x 484]	PDF	SCE-72P48F1	\$569.00
SCE-724824SSFSD	\$9,903.00	72.00 x 48.00 x 25.05 [1829 x 1219 x 636]	PDF	SCE-72P48F1	\$569.00
SCE-726018SSFSD	\$10,284.00	72.00 x 60.00 x 19.05 [1829 x 1524 x 484]	PDF	SCE-72P60F1	\$658.00
SCE-726024SSFSD	\$11,126.00	72.00 x 60.00 x 25.05 [1829 x 1524 x 636]	PDF	SCE-72P60F1	\$658.00
SCE-726036SSFSD	\$12,800.00	72.00 x 60.00 x 37.05 [1829 x 1524 x 941]	PDF	SCE-72P60F1	\$658.00
SCE-727218SSFSD	\$11,426.00	72.00 x 72.00 x 19.05 [1829 x 1829 x 484]	PDF	SCE-72P72F1	\$752.00
SCE-727224SSFSD	\$12,350.00	72.00 x 72.00 x 25.05 [1829 x 1829 x 636]	PDF	SCE-72P72F1	\$752.00
SCE-904820SSFSD	\$10,861.00	90.00 x 48.00 x 21.05 [2286 x 1219 x 535]	PDF	SCE-90P48F1	\$669.00
SCE-907220SSFSD	\$13,654.00	90.00 x 72.00 x 21.05 [2286 x 1829 x 535]	PDF	SCE-90P72F1	\$903.00
SCE-907224SSFSD	\$14,335.00	90.00 x 72.00 x 25.05 [2286 x 1829 x 636]	PDF	SCE-90P72F1	\$903.00
SCE-907236SSFSD	\$16,401.00	90.00 x 72.00 x 37.05 [2286 x 1829 x 941]	PDF	SCE-90P72F1	\$903.00

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Double-Door Freestanding



Dimensions

