

# Enviroline Series NEMA 3R, 4, 12, and 13 Two-Door Freestanding



Your Enclosure Source®



## Applications

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides protection from dust, dirt, water and oil. For outdoor application a drip shield and drain holes are required. The enclosures are extra deep for applications requiring more interior space.

## Construction

- 12-gauge carbon steel
- Removable and interchangeable doors
- Concealed hinges
- Seams continuously welded and ground smooth
- Strong, rigid construction with stiffeners welded on backs of single access boxes
- Lifting eyes for easy handling
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods have ramp shoes for easier door closing.
- Flange trough collar around all sides of door opening
- Removable center post
- Removable print pocket
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Hole plugs are provided to seal holes in bottom of enclosure.
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Provisions for light kit

## Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

### Enviroline Series NEMA 3R, 4, 12, and 13 Two-Door Freestanding

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-60EL4818FSD</a>	\$2,998.00	60.00 x 48.00 x 19.05 [1524 x 1219 x 484]	<a href="#">PDF</a>	<a href="#">SCE-60P48F1</a>	\$503.00
<a href="#">SCE-72EL4818FSD</a>	\$3,318.00	72.00 x 48.00 x 19.05 [1829 x 1219 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P48F1</a>	\$569.00
<a href="#">SCE-72EL4824FSD</a>	\$3,534.00	72.00 x 48.00 x 25.05 [1829 x 1219 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P48F1</a>	\$569.00
<a href="#">SCE-72EL6018FSD</a>	\$3,641.00	72.00 x 60.00 x 19.05 [1829 x 1524 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P60F1</a>	\$658.00
<a href="#">SCE-72EL6024FSD</a>	\$3,878.00	72.00 x 60.00 x 25.05 [1829 x 1524 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P60F1</a>	\$658.00
<a href="#">SCE-72EL6036FSD</a>	\$4,348.00	72.00 x 60.00 x 37.05 [1829 x 1524 x 941]	<a href="#">PDF</a>	<a href="#">SCE-72P60F1</a>	\$658.00
<a href="#">SCE-72EL7218FSD</a>	\$3,990.00	72.00 x 72.00 x 19.05 [1829 x 1829 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P72F1</a>	\$752.00
<a href="#">SCE-72EL7224FSD</a>	\$4,250.00	72.00 x 72.00 x 25.05 [1829 x 1829 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P72F1</a>	\$752.00
<a href="#">SCE-90EL4820FSD</a>	\$4,035.00	90.00 x 48.00 x 21.05 [2286 x 1219 x 535]	<a href="#">PDF</a>	<a href="#">SCE-90P48F1</a>	\$669.00
<a href="#">SCE-90EL7220FSD</a>	\$4,848.00	90.00 x 72.00 x 21.05 [2286 x 1829 x 535]	<a href="#">PDF</a>	<a href="#">SCE-90P72F1</a>	\$903.00
<a href="#">SCE-90EL7224FSD</a>	\$5,040.00	90.00 x 72.00 x 25.05 [2286 x 1829 x 636]	<a href="#">PDF</a>	<a href="#">SCE-90P72F1</a>	\$903.00
<a href="#">SCE-90EL7236FSD</a>	\$5,620.00	90.00 x 72.00 x 37.05 [2286 x 1829 x 941]	<a href="#">PDF</a>	<a href="#">SCE-90P72F1</a>	\$903.00

Note: Dimensions in inches [millimeters].