

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding



Applications

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any equipment. Provides some protection from dust, dirt, water, and oil. Extra-deep for applications requiring more interior space.

Construction

- 12-gauge Stainless Steel Type 304 and 316/316L
- Removable and interchangeable doors
- Stainless steel concealed hinges
- Seams continuously welded and ground smooth
- Strong, rigid construction with stiffeners welded on backs of single access boxes
- Lifting eyes for easy handling
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Black, 1/4-turn latches, as required
- Latch rods have ramp shoes for easier door closing.
- Flange trough collar around all sides of door opening
- Removable center post
- Removable print pocket
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Provisions for light kit

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding

| 304 Stainless Steel | Price | 316L Stainless Steel | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
|-----------------------------------|-------------|------------------------------------|-------------|---|---------------------|-----------------------------|----------|
| SCE-60EL4818SSFSD | \$8,972.00 | SCE-60EL4818SS6FSD | \$10,964.00 | 60.00 x 48.00 x 19.05 [1524 x 1219 x 484] | PDF | SCE-60P48F1 | \$503.00 |
| SCE-72EL4818SSFSD | \$9,891.00 | SCE-72EL4818SS6FSD | \$12,087.00 | 72.00 x 48.00 x 19.05 [1829 x 1219 x 484] | PDF | SCE-72P48F1 | \$569.00 |
| SCE-72EL4824SSFSD | \$10,653.00 | SCE-72EL4824SS6FSD | \$13,018.00 | 72.00 x 48.00 x 25.05 [1829 x 1219 x 636] | PDF | SCE-72P48F1 | \$569.00 |
| SCE-72EL6018SSFSD | \$11,034.00 | SCE-72EL6018SS6FSD | \$13,484.00 | 72.00 x 60.00 x 19.05 [1829 x 1524 x 484] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-72EL6024SSFSD | \$11,876.00 | SCE-72EL6024SS6FSD | \$14,513.00 | 72.00 x 60.00 x 25.05 [1829 x 1524 x 636] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-72EL6036SSFSD | \$13,550.00 | SCE-72EL6036SS6FSD | \$16,558.00 | 72.00 x 60.00 x 37.05 [1829 x 1524 x 941] | PDF | SCE-72P60F1 | \$658.00 |
| SCE-72EL7218SSFSD | \$12,202.00 | SCE-72EL7218SS6FSD | \$14,911.00 | 72.00 x 72.00 x 19.05 [1829 x 1829 x 484] | PDF | SCE-72P72F1 | \$752.00 |
| SCE-72EL7224SSFSD | \$13,125.00 | SCE-72EL7224SS6FSD | \$16,039.00 | 72.00 x 72.00 x 25.05 [1829 x 1829 x 636] | PDF | SCE-72P72F1 | \$752.00 |
| SCE-90EL4820SSFSD | \$11,710.00 | SCE-90EL4820SS6FSD | \$14,273.00 | 90.00 x 48.00 x 21.05 [2286 x 1219 x 535] | PDF | SCE-90P48F1 | \$669.00 |
| SCE-90EL7220SSFSD | \$14,506.00 | SCE-90EL7220SS6FSD | \$17,690.00 | 90.00 x 72.00 x 21.05 [2286 x 1829 x 535] | PDF | SCE-90P72F1 | \$903.00 |
| SCE-90EL7224SSFSD | \$15,187.00 | SCE-90EL7224SS6FSD | \$18,523.00 | 90.00 x 72.00 x 25.05 [2286 x 1829 x 636] | PDF | SCE-90P72F1 | \$903.00 |
| SCE-90EL7236SSFSD | \$17,253.00 | SCE-90EL7236SS6FSD | \$21,047.00 | 90.00 x 72.00 x 37.05 [2286 x 1829 x 941] | PDF | SCE-90P72F1 | \$903.00 |

Note: Dimensions in inches [millimeters].

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding



Your Enclosure Source®

Dimensions

