

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top



Your Enclosure Source®



## Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor, outdoor and sanitary locations.

## Construction

- 12-gauge stainless steel Type 304 and 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- 15° slope top
- Removable center post
- Heavy duty lifting eyes anchor into the reinforced top.
- Body stiffeners
- Black, 1/4-turn latches, as required
- Stainless steel concealed hinges
- Stainless steel padlocking handles
- 3-point latching mechanism
- Removable print pocket
- Provisions for floor stands
- Panel supports
- Ground stud on door and body
- Provisions for light kit
- Poured-in-place oil- and water-resistant gasket

## Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-60EL4812SSST</a>	\$7,504.00	<a href="#">SCE-60EL4812SS6ST</a>	\$8,937.00	63.20 x 48.00 x 13.05 [1605 x 1219 x 331]	<a href="#">PDF</a>	<a href="#">SCE-60P48</a>	\$373.00
<a href="#">SCE-60EL4818SSST</a>	\$7,959.00	<a href="#">SCE-60EL4818SS6ST</a>	\$9,479.00	64.80 x 48.00 x 19.05 [1646 x 1219 x 484]	<a href="#">PDF</a>	<a href="#">SCE-60P48</a>	\$373.00
<a href="#">SCE-60EL6012SSST</a>	\$8,422.00	<a href="#">SCE-60EL6012SS6ST</a>	\$10,030.00	63.20 x 60.00 x 13.05 [1605 x 1524 x 331]	<a href="#">PDF</a>	<a href="#">SCE-60P60</a>	\$460.00
<a href="#">SCE-60EL6018SSST</a>	\$8,820.00	<a href="#">SCE-60EL6018SS6ST</a>	\$10,504.00	64.80 x 60.00 x 19.05 [1646 x 1524 x 484]	<a href="#">PDF</a>	<a href="#">SCE-60P60</a>	\$460.00
<a href="#">SCE-72EL6012SSST</a>	\$9,582.00	<a href="#">SCE-72EL6012SS6ST</a>	\$11,417.00	75.20 x 60.00 x 13.05 [1910 x 1524 x 331]	<a href="#">PDF</a>	<a href="#">SCE-72P60</a>	\$548.00
<a href="#">SCE-72EL6018SSST</a>	\$9,787.00	<a href="#">SCE-72EL6018SS6ST</a>	\$11,660.00	76.80 x 60.00 x 19.05 [1951 x 1524 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P60</a>	\$548.00
<a href="#">SCE-72EL7212SSST</a>	\$10,331.00	<a href="#">SCE-72EL7212SS6ST</a>	\$12,311.00	75.20 x 72.00 x 13.05 [1910 x 1829 x 331]	<a href="#">PDF</a>	<a href="#">SCE-72P72</a>	\$654.00
<a href="#">SCE-72EL7218SSST</a>	\$11,104.00	<a href="#">SCE-72EL7218SS6ST</a>	\$13,232.00	76.80 x 72.00 x 19.05 [1951 x 1829 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P72</a>	\$654.00
<a href="#">SCE-72EL7224SSST</a>	\$11,478.00	<a href="#">SCE-72EL7224SS6ST</a>	\$13,683.00	78.41 x 72.00 x 25.05 [1992 x 1829 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P72</a>	\$654.00

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top



## Dimensions

