

NEMA 4, 4X, 12, and 13 Extra-Large Stainless Steel Wall-Mount Pushbutton



Your Enclosure Source®



Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16-gauge stainless steel, Type 304 and 316/316L
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 0.87in [22.5 mm] or 1.20in [30.5 mm]
- Poured-in-place oil- and water-resistant gasket
- Provisions for subpanel
- Ground stud on door and body
- Bolt-on continuous hinge with stainless steel hinge pin
- Welded mounting provision top and bottom of back

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 4, 4X, 12, and 13
- cULus Listed Type 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 4X, 12, and 13 22mm Extra-Large Stainless Steel Wall-Mount Pushbutton

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Holes	Drawing Link	Optional Subpanel	Price
SCE-9PBHSSI	\$319.00	SCE-9PBHSS6I	\$397.00	10.38 x 10.31 x 6.20 [264 x 262 x 157]	9	PDF	SCE-10P10	\$9.25
SCE-16PBHSSI	\$544.00	SCE-16PBHSS6I	\$678.00	12.38 x 12.31 x 6.20 [314 x 313 x 157]	16	PDF	SCE-12P12	\$12.50

Note: Dimensions in inches [millimeters].

NEMA 4, 4X, 12, and 13 30mm Extra-Large Stainless Steel Wall-Mount Pushbutton

304 Stainless	Price	316 Stainless	Price	Size HxWxD	Holes	Drawing Link	Optional Subpanel	Price
SCE-9PBHSS	\$319.00	SCE-9PBHSS6	\$397.00	10.38 x 10.31 x 6.20 [264 x 262 x 157]	9	PDF	SCE-10P10	\$9.25
SCE-16PBHSS	\$544.00	SCE-16PBHSS6	\$678.00	12.38 x 12.31 x 6.20 [314 x 313 x 157]	16	PDF	SCE-12P12	\$12.50

Note: Dimensions in inches [millimeters].

NEMA 4, 4X, 12, and 13 Extra-Large Stainless Steel Wall-Mount Pushbutton

Dimensions

