

NEMA 1 Single-Door Wall-Mount



Applications

Designed to house electrical controls, instruments and components in areas that do not require oil, water and dust tight protection.

Construction

- 14 gauge, 16 gauge, or 18 gauge carbon steel depending on size. See drawings for details.
- Spot weld construction.
- Standoffs provided for mounting optional subpanels.
- Butt hinge.
- Doors open 180°.
- Black 1/4-turn latches.
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body.
- Mounting holes in back of enclosure.
- Subpanel mounting hardware included.
- Optional mounting straps available.

Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white.

Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30



NEMA 1 Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

| NEMA 1 Single-Door Wall-Mount | | | | | |
|-------------------------------|----------|---|---------------------|-------------------|---------|
| Part Number | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
| SCE-6N604LP | \$34.00 | 6.38 x 6.38 x 4.12 [162 x 162 x 105] | PDF | SCE-6N6MP | \$3.25 |
| SCE-8N604LP | \$37.00 | 8.38 x 6.38 x 4.12 [213 x 162 x 105] | PDF | SCE-8N6MP | \$3.75 |
| SCE-8N804LP | \$41.00 | 8.38 x 8.38 x 4.12 [213 x 213 x 105] | PDF | SCE-8N8MP | \$4.25 |
| SCE-8N806LP | \$46.00 | 8.38 x 8.38 x 6.12 [213 x 213 x 155] | PDF | SCE-8N8MP | \$4.25 |
| SCE-10N804LP | \$45.00 | 10.38 x 8.38 x 4.12 [264 x 213 x 105] | PDF | SCE-10N8MP | \$5.00 |
| SCE-10N806LP | \$51.00 | 10.38 x 8.38 x 6.12 [264 x 213 x 155] | PDF | SCE-10N8MP | \$5.00 |
| SCE-10N1004LP | \$45.50 | 10.38 x 10.38 x 4.12 [264 x 264 x 105] | PDF | SCE-10N10MP | \$6.00 |
| SCE-10N1006LP | \$56.00 | 10.38 x 10.38 x 6.12 [264 x 264 x 155] | PDF | SCE-10N10MP | \$6.00 |
| SCE-12N1004LP | \$54.00 | 12.38 x 10.38 x 4.12 [314 x 264 x 105] | PDF | SCE-12N10MP | \$6.75 |
| SCE-12N1006LP | \$61.00 | 12.38 x 10.38 x 6.12 [314 x 264 x 155] | PDF | SCE-12N10MP | \$6.75 |
| SCE-12N1204LP | \$59.00 | 12.38 x 12.38 x 4.12 [314 x 314 x 105] | PDF | SCE-12N12MP | \$8.00 |
| SCE-12N1206LP | \$67.00 | 12.38 x 12.38 x 6.12 [314 x 314 x 155] | PDF | SCE-12N12MP | \$8.00 |
| SCE-12N1208LP | \$75.00 | 12.38 x 12.38 x 8.12 [314 x 314 x 206] | PDF | SCE-12N12MP | \$8.00 |
| SCE-14N1204LP | \$65.00 | 14.38 x 12.38 x 4.12 [365 x 314 x 105] | PDF | SCE-14N12MP | \$8.75 |
| SCE-14N1206LP | \$73.00 | 14.38 x 12.38 x 6.12 [365 x 314 x 155] | PDF | SCE-14N12MP | \$8.75 |
| SCE-14N1208LP | \$82.00 | 14.38 x 12.38 x 8.12 [365 x 314 x 206] | PDF | SCE-14N12MP | \$8.75 |
| SCE-16N1206LP | \$110.00 | 16.38 x 12.38 x 6.12 [416 x 314 x 155] | PDF | SCE-16N12MP | \$13.00 |
| SCE-16N1208LP | \$119.00 | 16.38 x 12.38 x 8.12 [416 x 314 x 206] | PDF | SCE-16N12MP | \$13.00 |
| SCE-16N1606LP | \$122.00 | 16.38 x 16.38 x 6.12 [416 x 416 x 155] | PDF | SCE-16N16MP | \$21.50 |
| SCE-16N1608LP | \$133.00 | 16.38 x 16.38 x 8.12 [416 x 416 x 206] | PDF | SCE-16N16MP | \$21.50 |
| SCE-16N2006LP | \$135.00 | 16.38 x 20.38 x 6.12 [416 x 518 x 155] | PDF | SCE-20N16MP | \$24.00 |
| SCE-20N1606LP | \$135.00 | 20.38 x 16.38 x 6.12 [518 x 416 x 155] | PDF | SCE-20N16MP | \$24.00 |
| SCE-20N1608LP | \$148.00 | 20.38 x 16.38 x 8.12 [518 x 416 x 206] | PDF | SCE-20N16MP | \$24.00 |
| SCE-20N2006LP | \$149.00 | 20.38 x 20.38 x 6.12 [518 x 518 x 155] | PDF | SCE-20N20MP | \$31.00 |
| SCE-20N2008LP | \$163.00 | 20.38 x 20.38 x 8.12 [518 x 518 x 206] | PDF | SCE-20N20MP | \$31.00 |
| SCE-20N2010LP | \$177.00 | 20.38 x 20.38 x 10.12 [518 x 518 x 257] | PDF | SCE-20N20MP | \$31.00 |
| SCE-24N1606LP | \$147.00 | 24.38 x 16.38 x 6.12 [619 x 416 x 155] | PDF | SCE-24N16MP | \$25.50 |
| SCE-24N2006LP | \$164.00 | 24.38 x 20.38 x 6.12 [619 x 518 x 155] | PDF | SCE-24N20MP | \$35.50 |
| SCE-24N2008LP | \$180.00 | 24.38 x 20.38 x 8.12 [619 x 518 x 206] | PDF | SCE-24N20MP | \$35.50 |
| SCE-24N2406LP | \$167.00 | 24.38 x 24.38 x 6.12 [619 x 619 x 155] | PDF | SCE-24N24MP | \$41.50 |
| SCE-24N2408LP | \$184.00 | 24.38 x 24.38 x 8.12 [619 x 619 x 206] | PDF | SCE-24N24MP | \$41.50 |
| SCE-24N2010LP | \$195.00 | 24.38 x 20.38 x 10.12 [619 x 518 x 257] | PDF | SCE-24N20MP | \$35.50 |
| SCE-24N2412LP | \$217.00 | 24.38 x 24.38 x 12.12 [619 x 619 x 308] | PDF | SCE-24N24MP | \$41.50 |
| SCE-30N2406LP | \$185.00 | 30.38 x 24.38 x 6.12 [772 x 619 x 155] | PDF | SCE-30N24MP | \$49.00 |
| SCE-30N2408LP | \$206.00 | 30.38 x 24.38 x 8.12 [772 x 619 x 206] | PDF | SCE-30N24MP | \$49.00 |
| SCE-30N2412LP | \$242.00 | 30.38 x 24.38 x 12.12 [772 x 619 x 308] | PDF | SCE-30N24MP | \$49.00 |
| SCE-30N3008LP | \$232.00 | 30.38 x 30.38 x 8.12 [772 x 772 x 206] | PDF | SCE-30N30MP | \$65.00 |
| SCE-36N2406LP | \$215.00 | 36.38 x 24.38 x 6.12 [924 x 619 x 155] | PDF | SCE-36N24MP | \$59.00 |
| SCE-36N2408LP | \$237.00 | 36.38 x 24.38 x 8.12 [924 x 619 x 206] | PDF | SCE-36N24MP | \$59.00 |
| SCE-36N2412LP | \$274.00 | 36.38 x 24.38 x 12.12 [924 x 619 x 308] | PDF | SCE-36N24MP | \$59.00 |
| SCE-36N3006LP | \$236.00 | 36.38 x 30.38 x 6.12 [924 x 772 x 155] | PDF | SCE-36N30MP | \$79.00 |
| SCE-36N3008LP | \$259.00 | 36.38 x 30.38 x 8.12 [924 x 772 x 206] | PDF | SCE-36N30MP | \$79.00 |
| SCE-36N3012LP | \$306.00 | 36.38 x 30.38 x 12.12 [924 x 772 x 308] | PDF | SCE-36N30MP | \$79.00 |

Note: Dimensions in inches [millimeters].