

# NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



Your Enclosure Source®



## Applications

Designed for use as electrical junction boxes, terminal wiring boxes, instrument housings, and electrical control enclosures. Provides protection from dust, dirt, oil and water.

## Construction

- 16 gauge carbon steel.
- Seams continuously welded and ground smooth, no holes or knockouts.
- Captivated cover screws thread into sealed wells.
- Poured-in-place oil- and water-resistant gasket.
- Standoffs provided for mounting optional subpanels.

## Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-404SC</b>	\$39.50	4.44 x 4.31 x 3.15 [113 x 109 x 80]	<a href="#">PDF</a>	-	-
<b>SCE-4044SC</b>	\$39.50	4.44 x 4.31 x 4.15 [113 x 109 x 105]	<a href="#">PDF</a>	-	-
<b>SCE-604SC</b>	\$45.00	6.44 x 4.31 x 3.15 [164 x 109 x 80]	<a href="#">PDF</a>	<b>SCE-6P4</b>	\$3.25
<b>SCE-6044SC</b>	\$50.00	6.44 x 4.31 x 4.15 [164 x 109 x 105]	<a href="#">PDF</a>	<b>SCE-6P4</b>	\$3.25
<b>SCE-606SC</b>	\$53.00	6.44 x 6.31 x 4.15 [164 x 160 x 105]	<a href="#">PDF</a>	<b>SCE-6P6</b>	\$3.75
<b>SCE-806SC</b>	\$56.00	8.44 x 6.31 x 3.65 [214 x 160 x 93]	<a href="#">PDF</a>	<b>SCE-8P6</b>	\$4.50
<b>SCE-8066SC</b>	\$63.00	8.44 x 6.31 x 6.15 [214 x 160 x 156]	<a href="#">PDF</a>	<b>SCE-8P6</b>	\$4.50
<b>SCE-808SC</b>	\$63.00	8.44 x 8.31 x 4.15 [214 x 211 x 105]	<a href="#">PDF</a>	<b>SCE-8P8</b>	\$5.25
<b>SCE-1008SC</b>	\$69.00	10.44 x 8.31 x 4.15 [265 x 211 x 105]	<a href="#">PDF</a>	<b>SCE-10P8</b>	\$6.00
<b>SCE-10086SC</b>	\$78.00	10.44 x 8.31 x 6.15 [265 x 211 x 156]	<a href="#">PDF</a>	<b>SCE-10P8</b>	\$6.00
<b>SCE-1010SC</b>	\$77.00	10.44 x 10.31 x 4.15 [265 x 262 x 105]	<a href="#">PDF</a>	<b>SCE-10P10</b>	\$7.25
<b>SCE-10106SC</b>	\$86.00	10.44 x 10.31 x 6.15 [265 x 262 x 156]	<a href="#">PDF</a>	<b>SCE-10P10</b>	\$7.25
<b>SCE-1210SC</b>	\$87.00	12.44 x 10.31 x 5.15 [316 x 262 x 131]	<a href="#">PDF</a>	<b>SCE-12P10</b>	\$8.25
<b>SCE-1212SC</b>	\$102.00	12.44 x 12.31 x 6.15 [316 x 313 x 156]	<a href="#">PDF</a>	<b>SCE-12P12</b>	\$9.75
<b>SCE-121010SC</b>	\$132.00	12.44 x 10.31 x 10.15 [316 x 262 x 258]	<a href="#">PDF</a>	<b>SCE-12P10</b>	\$8.25
<b>SCE-1412SC</b>	\$111.00	14.44 x 12.31 x 6.15 [367 x 313 x 156]	<a href="#">PDF</a>	<b>SCE-14P12</b>	\$10.75
<b>SCE-1614SC</b>	\$130.00	16.44 x 14.31 x 6.15 [418 x 363 x 156]	<a href="#">PDF</a>	<b>SCE-16P14</b>	\$21.00

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



## Dimensions

