

# NEMA 3R Vented Single-Door Wall-Mount



Your Enclosure Source®



## Applications

Designed to house electrical controls, drives, instruments and components used in an outdoor environment to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects (falling dirt); and provide a degree of protection with respect to the harmful effects on the equipment due to the ingress of water (rain, sleet, snow).

## Finish

- White powder coated inside and out.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R
- cULus Listed Type 3R [File E69392]
- IEC 60529 IP32



## Construction

- 14 gauge galvanized steel.
- Black 1/4-turn latches and padlocking knob.
- Provisions for subpanel.
- Doors open 180°.
- Concealed hinges.
- Vented top hood with removable cover and washable reusable filter
- Top mounted fans.
- Vented rain hood with filter kits in door.
- DIN rail mounting provisions inside top for installation of thermostat and terminals.
- Poured-in-place oil- and water-resistant gasket.
- Ground studs on door and body.
- Mounting holes for optional mounting straps.
- 3/8-16 grounding kit.
- Subpanel mounting hardware included.
- 115VAC fan.
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm]. Lifting lug assembly will be included with the enclosure. Bolt pack and hole plugs provided to seal holes in bottom of enclosure.

## Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 3R Vented Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-29VR2412</b>	\$730.00	29.00 x 24.00 x 13.07 [737 x 610 x 332]	<a href="#">PDF</a>	<b>SCE-24P24</b>	\$56.00
<b>SCE-29VR2416</b>	\$806.00	29.00 x 24.00 x 17.07 [737 x 610 x 434]	<a href="#">PDF</a>	<b>SCE-24P24</b>	\$56.00
<b>SCE-35VR2412</b>	\$816.00	35.00 x 24.00 x 13.07 [889 x 610 x 332]	<a href="#">PDF</a>	<b>SCE-30P24</b>	\$67.00
<b>SCE-41VR2412</b>	\$923.00	41.00 x 24.00 x 13.07 [1041 x 610 x 332]	<a href="#">PDF</a>	<b>SCE-36P24</b>	\$81.00
<b>SCE-47VR2414</b>	\$1,115.00	47.00 x 24.00 x 15.07 [1194 x 610 x 383]	<a href="#">PDF</a>	<b>SCE-42P24</b>	\$97.00
<b>SCE-53VR3616</b>	\$1,794.00	53.00 x 36.00 x 17.07 [1346 x 914 x 434]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$164.00
<b>SCE-53VR3620</b>	\$1,997.00	53.00 x 36.00 x 21.07 [1346 x 914 x 535]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$164.00
<b>SCE-65VR3616</b>	\$2,029.00	65.00 x 36.00 x 17.07 [1651 x 914 x 434]	<a href="#">PDF</a>	<b>SCE-60P36</b>	\$202.00
<b>SCE-65VR3620</b>	\$2,226.00	65.00 x 36.00 x 21.07 [1651 x 914 x 535]	<a href="#">PDF</a>	<b>SCE-60P36</b>	\$202.00

Note: Dimensions in inches [millimeters].

# NEMA 3R Vented Single-Door Wall-Mount



## Dimensions

