

Enviroline Junction Series NEMA 3R, 4, 12, and 13 Wall-Mount



Applications

Designed to house electrical controls, instruments and components in areas, which are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water.

Construction

- 16 gauge carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Poured-in-place oil- and water-resistant gasket.
- Standoffs provided for mounting optional subpanels.
- Removable hinge.
- Doors open 180°.
- Black mini 1/4-turn latches.
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs included.
- Ground stud on door and body.
- Mounting feet included.

Finish

- ANSI 61 gray or RAL7035 gray powder coated inside and out.
- Optional subpanels powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 12, and 13 Wall-Mount

ANSI 61	RAL 7035	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604ELJ	SCE-604ELJLG	\$39.50	6.00 x 4.00 x 4.18 [152 x 102 x 106]	PDF	SCE-6P4	\$3.25
SCE-606ELJ	SCE-606ELJLG	\$46.00	6.00 x 6.00 x 4.18 [152 x 152 x 106]	PDF	SCE-6P6	\$3.75
SCE-806ELJ	SCE-806ELJLG	\$50.00	8.00 x 6.00 x 4.18 [203 x 152 x 106]	PDF	SCE-8P6	\$4.50
SCE-8066ELJ	SCE-8066ELJLG	\$59.00	8.00 x 6.00 x 6.18 [203 x 152 x 157]	PDF	SCE-8P6	\$4.50
SCE-808ELJ	SCE-808ELJLG	\$61.00	8.00 x 8.00 x 4.18 [203 x 203 x 106]	PDF	SCE-8P8	\$5.25
SCE-8086ELJ	SCE-8086ELJLG	\$66.00	8.00 x 8.00 x 6.18 [203 x 203 x 157]	PDF	SCE-8P8	\$5.25
SCE-1008ELJ	SCE-1008ELJLG	\$68.00	10.00 x 8.00 x 4.18 [254 x 203 x 106]	PDF	SCE-10P8	\$6.00
SCE-10086ELJ	SCE-10086ELJLG	\$76.00	10.00 x 8.00 x 6.18 [254 x 203 x 157]	PDF	SCE-10P8	\$6.00
SCE-10106ELJ	SCE-10106ELJLG	\$80.00	10.00 x 10.00 x 6.18 [254 x 254 x 157]	PDF	SCE-10P10	\$7.25
SCE-1210ELJ	SCE-1210ELJLG	\$83.00	12.00 x 10.00 x 6.18 [305 x 254 x 157]	PDF	SCE-12P10	\$8.25
SCE-12108ELJ	SCE-12108ELJLG	\$95.00	12.00 x 10.00 x 8.18 [305 x 254 x 208]	PDF	SCE-12P10	\$8.25
SCE-1212ELJ	SCE-1212ELJLG	\$97.00	12.00 x 12.00 x 6.18 [305 x 305 x 157]	PDF	SCE-12P12	\$9.75
SCE-1412ELJ	SCE-1412ELJLG	\$107.00	14.00 x 12.00 x 6.18 [356 x 305 x 157]	PDF	SCE-14P12	\$10.75
SCE-14128ELJ	SCE-14128ELJLG	\$114.00	14.00 x 12.00 x 8.18 [356 x 305 x 208]	PDF	SCE-14P12	\$10.75
SCE-1614ELJ	SCE-1614ELJLG	\$126.00	16.00 x 14.00 x 6.18 [406 x 356 x 157]	PDF	SCE-16P14	\$21.00
SCE-16148ELJ	SCE-16148ELJLG	\$138.00	16.00 x 14.00 x 8.18 [406 x 356 x 208]	PDF	SCE-16P14	\$21.00
SCE-20166ELJ	SCE-20166ELJLG	\$145.00	20.00 x 16.00 x 6.18 [508 x 406 x 157]	PDF	SCE-20P16J	\$32.50
SCE-20168ELJ	SCE-20168ELJLG	\$152.00	20.00 x 16.00 x 8.18 [508 x 406 x 208]	PDF	SCE-20P16J	\$32.50
SCE-201610ELJ	SCE-201610ELJLG	\$178.00	20.00 x 16.00 x 10.18 [508 x 406 x 259]	PDF	SCE-20P16J	\$32.50
SCE-20206ELJ	SCE-20206ELJLG	\$162.00	20.00 x 20.00 x 6.18 [508 x 508 x 157]	PDF	SCE-20P20J	\$37.50
SCE-20208ELJ	SCE-20208ELJLG	\$171.00	20.00 x 20.00 x 8.18 [508 x 508 x 208]	PDF	SCE-20P20J	\$37.50
SCE-202010ELJ	SCE-202010ELJLG	\$180.00	20.00 x 20.00 x 10.18 [508 x 508 x 259]	PDF	SCE-20P20J	\$37.50

Note: Dimensions in inches [millimeters].