

# Enviroline Series NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



## Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor, outdoor and sanitary locations.

## Construction

- 14 gauge 304 stainless steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- 15° Slope Top.
- Collar studs provided for mounting optional sub-panels.
- Mounting holes in back of the enclosure for wall-mounting.
- Mounting hardware, sealing washers and hole plugs included.
- Stainless steel concealed hinges.
- Removable and interchangeable doors.
- Black 1/4-turn latches.
- Latches are opened or closed with a screwdriver (optional tamper-resistant latches are available).
- Removable print pocket furnished on enclosures with width greater than 12in [305mm].
- Poured-in-place oil- and water-resistant gasket.
- Ground stud on door and body.

## Options

- Optional mounting feet available.
- Door hardware available.

## Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



# Enviroline Series NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



## Shipping Schedule

|          |             |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

| Enviroline Series NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Single-Door Wall-Mount with Slope Top |             |   |                     |                   |          |
|---|-------------|---|---------------------|-------------------|----------|
| Part Number   | Price       | Size HxWxD                                | Drawing Link        | Optional Subpanel | Price    |
| SCE-16EL1208SSST  | \$704.00    | 18.10 x 12.00 x 9.10 [460 x 305 x 231]    | <a href="#">PDF</a> | SCE-16P12         | \$15.75  |
| SCE-16EL1608SSST  | \$768.00    | 18.10 x 16.00 x 9.10 [460 x 406 x 231]    | <a href="#">PDF</a> | SCE-16P16         | \$26.00  |
| SCE-20EL1608SSST  | \$860.00    | 22.10 x 16.00 x 9.10 [561 x 406 x 231]    | <a href="#">PDF</a> | SCE-20P16         | \$32.50  |
| SCE-20EL1612SSST  | \$964.00    | 23.17 x 16.00 x 13.10 [589 x 406 x 333]   | <a href="#">PDF</a> | SCE-20P16         | \$32.50  |
| SCE-20EL2008SSST  | \$953.00    | 22.10 x 20.00 x 9.10 [561 x 508 x 231]    | <a href="#">PDF</a> | SCE-20P20         | \$37.50  |
| SCE-20EL2012SSST  | \$1,071.00  | 23.17 x 20.00 x 13.10 [589 x 508 x 333]   | <a href="#">PDF</a> | SCE-20P20         | \$37.50  |
| SCE-24EL2008SSST  | \$1,042.00  | 26.10 x 20.00 x 9.10 [663 x 508 x 231]    | <a href="#">PDF</a> | SCE-24P20         | \$48.50  |
| SCE-24EL2012SSST  | \$1,181.00  | 27.17 x 20.00 x 13.10 [690 x 508 x 333]   | <a href="#">PDF</a> | SCE-24P20         | \$48.50  |
| SCE-24EL2408SSST  | \$1,145.00  | 26.10 x 24.00 x 9.10 [663 x 610 x 231]    | <a href="#">PDF</a> | SCE-24P24         | \$56.00  |
| SCE-24EL2412SSST  | \$1,302.00  | 27.17 x 24.00 x 13.10 [690 x 610 x 333]   | <a href="#">PDF</a> | SCE-24P24         | \$56.00  |
| SCE-24EL2416SSST  | \$1,736.00  | 28.24 x 24.00 x 17.10 [717 x 610 x 434]   | <a href="#">PDF</a> | SCE-24P24         | \$56.00  |
| SCE-30EL2408SSST  | \$1,302.00  | 32.10 x 24.00 x 9.10 [815 x 610 x 231]    | <a href="#">PDF</a> | SCE-30P24         | \$67.00  |
| SCE-30EL2412SSST  | \$1,484.00  | 33.17 x 24.00 x 13.10 [843 x 610 x 333]   | <a href="#">PDF</a> | SCE-30P24         | \$67.00  |
| SCE-30EL3008SSST  | \$1,492.00  | 32.10 x 30.00 x 9.10 [815 x 762 x 231]    | <a href="#">PDF</a> | SCE-30P30         | \$89.00  |
| SCE-30EL3012SSST  | \$1,855.00  | 33.17 x 30.00 x 13.10 [843 x 762 x 333]   | <a href="#">PDF</a> | SCE-30P30         | \$89.00  |
| SCE-36EL2408SSST  | \$1,469.00  | 38.10 x 24.00 x 9.10 [968 x 610 x 231]    | <a href="#">PDF</a> | SCE-36P24         | \$81.00  |
| SCE-36EL2412SSST  | \$1,652.00  | 39.17 x 24.00 x 13.10 [995 x 610 x 333]   | <a href="#">PDF</a> | SCE-36P24         | \$81.00  |
| SCE-36EL3008SSST  | \$1,669.00  | 38.10 x 30.00 x 9.10 [968 x 762 x 231]    | <a href="#">PDF</a> | SCE-36P30         | \$108.00 |
| SCE-36EL3012SSST  | \$1,900.00  | 39.17 x 30.00 x 13.10 [995 x 762 x 333]   | <a href="#">PDF</a> | SCE-36P30         | \$108.00 |
| SCE-36EL3016SSST  | \$2,015.00  | 40.24 x 30.00 x 17.10 [1022 x 762 x 434]  | <a href="#">PDF</a> | SCE-36P30         | \$108.00 |
| SCE-36EL3612SSST  | \$1,941.00  | 39.17 x 36.00 x 13.10 [995 x 914 x 333]   | <a href="#">PDF</a> | SCE-36P36         | \$126.00 |
| SCE-48EL3612SSST  | \$2,778.00  | 51.17 x 36.00 x 13.10 [1300 x 914 x 333]  | <a href="#">PDF</a> | SCE-48P36         | \$164.00 |
| SCE-48EL3616SSST  | \$2,839.00  | 52.24 x 36.00 x 17.10 [1327 x 914 x 434]  | <a href="#">PDF</a> | SCE-48P36         | \$164.00 |
| SCE-60EL3612SSST  | \$3,177.00  | 63.17 x 36.00 x 13.10 [1605 x 914 x 333]  | <a href="#">PDF</a> | SCE-60P36         | \$202.00 |
| SCE-60EL3616SSST  | \$3,317.00  | 64.24 x 36.00 x 17.10 [1632 x 914 x 434]  | <a href="#">PDF</a> | SCE-60P36         | \$202.00 |
| SCE-60EL4812SSST  | \$7,761.00  | 63.20 x 48.00 x 13.05 [1605 x 1219 x 331] | <a href="#">PDF</a> | SCE-60P48         | \$285.00 |
| SCE-60EL4818SSST  | \$8,232.00  | 64.80 x 48.00 x 19.05 [1646 x 1219 x 484] | <a href="#">PDF</a> | SCE-60P48         | \$285.00 |
| SCE-60EL6012SSST  | \$8,710.00  | 63.20 x 60.00 x 13.05 [1605 x 1524 x 331] | <a href="#">PDF</a> | SCE-60P60         | \$352.00 |
| SCE-60EL6018SSST  | \$9,122.00  | 64.80 x 60.00 x 19.05 [1646 x 1524 x 484] | <a href="#">PDF</a> | SCE-60P60         | \$352.00 |
| SCE-72EL6012SSST  | \$9,934.00  | 75.20 x 60.00 x 13.05 [1910 x 1524 x 331] | <a href="#">PDF</a> | SCE-72P60         | \$420.00 |
| SCE-72EL6018SSST  | \$10,146.00 | 76.80 x 60.00 x 19.05 [1951 x 1524 x 484] | <a href="#">PDF</a> | SCE-72P60         | \$420.00 |

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Single-Door Wall-Mount with Slope Top



## Dimensions

