

Enviroline Series NEMA 3R, 4, 12 and 13 Double-Door Wall-Mount with 3-Point Handles



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components. For outdoor applications a drip shield is recommended.

Construction

- 14 gauge carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Collar studs provided for mounting optional subpanels.
- Removable center posts permit easy subpanel installation.
- Mounting holes in back of the enclosure for wall-mounting.
- Mounting hardware, sealing washers and hole plugs included.
- Concealed hinges.
- Removable and interchangeable doors.
- Black keylocking/padlocking handles.
- 3-point latching mechanism.
- Removable print pocket.
- Poured-in-place oil- and water-resistant gasket.
- Ground stud on door and body.
- Note: Mechanical Interlock not for use in enclosures 24in in height.

Options

- Optional tamper-resistant inserts available.
- Optional mounting feet available (SCE-ELMFK4)
- Door hardware available.

Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 12 and 13 Double-Door Wall-Mount with 3-Point Handles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-24EL4210WFLP	\$828.00	24.00 x 42.00 x 11.10 [610 x 1067 x 282]	PDF	SCE-42P24	\$97.00
SCE-24EL4810WFLP	\$862.00	24.00 x 48.00 x 11.10 [610 x 1219 x 282]	PDF	SCE-48P24	\$105.00
SCE-30EL4210WFLP	\$874.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	PDF	SCE-42P30	\$124.00
SCE-30EL4810WFLP	\$962.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	PDF	SCE-48P30	\$137.00
SCE-30EL6010WFLP	\$1,064.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	PDF	SCE-60P30	\$169.00
SCE-36EL4216WFLP	\$1,055.00	36.00 x 42.00 x 17.10 [914 x 1067 x 434]	PDF	SCE-42P36	\$145.00
SCE-36EL4812WFLP	\$1,110.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	PDF	SCE-48P36	\$164.00
SCE-36EL6012WFLP	\$1,233.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	PDF	SCE-60P36	\$202.00
SCE-42EL4212WFLP	\$1,176.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	PDF	SCE-42P42	\$167.00
SCE-42EL4812WFLP	\$1,284.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	PDF	SCE-48P42	\$188.00
SCE-42EL6012WFLP	\$1,431.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	PDF	SCE-60P42	\$226.00
SCE-48EL4812WFLP	\$1,394.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	PDF	SCE-48P48	\$226.00

Note: Dimensions in inches [millimeters].