

Enviroline Series NEMA 3R, 4, 12 and 13 Two-Door Wall-Mount with 3-Point Handles



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Removable center posts permit easy subpanel installation.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers, and hole plugs are included.
- Concealed hinges
- Removable and interchangeable doors
- Black, keylocking/padlocking handles
- 3-point latching mechanism
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

Note: Mechanical Interlock not for use in enclosures 24.0in [610mm] in height.

Options

- Optional tamper-resistant inserts are available.
- Optional mounting feet are available (SCE-ELMFK4).
- Door hardware available

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 12 and 13 Two-Door Wall-Mount with 3-Point Handles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-24EL4210WFLP	\$1,083.00	24.00 x 42.00 x 11.10 [610 x 1067 x 282]	PDF	SCE-42P24	\$127.00
SCE-24EL4810WFLP	\$1,126.00	24.00 x 48.00 x 11.10 [610 x 1219 x 282]	PDF	SCE-48P24	\$137.00
SCE-30EL4210WFLP	\$1,142.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	PDF	SCE-42P30	\$162.00
SCE-30EL4810WFLP	\$1,258.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	PDF	SCE-48P30	\$179.00
SCE-30EL6010WFLP	\$1,391.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	PDF	SCE-60P30	\$221.00
SCE-36EL4216WFLP	\$1,380.00	36.00 x 42.00 x 17.10 [914 x 1067 x 434]	PDF	SCE-42P36	\$190.00
SCE-36EL4812WFLP	\$1,451.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	PDF	SCE-48P36	\$214.00
SCE-36EL6012WFLP	\$1,612.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	PDF	SCE-60P36	\$264.00
SCE-42EL4212WFLP	\$1,538.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	PDF	SCE-42P42	\$218.00
SCE-42EL4812WFLP	\$1,678.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	PDF	SCE-48P42	\$246.00
SCE-42EL6012WFALP	\$1,871.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	PDF	SCE-42P30	\$162.00
SCE-48EL4812WFLP	\$1,822.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	PDF	SCE-48P48	\$295.00

Note: Dimensions in inches [millimeters].