

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount



Applications

Designed to house electrical and electronic controls, instruments and components. Provides protection from dust, oil and water. For outdoor application a drip shield is recommended.

Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Collar studs are provided for mounting optional subpanels.
- Easy to install swing-out panel kits mount to the concealed hinges
- Concealed hinges are removed by pulling the pin.
- Removable and interchangeable doors
- Black, 1/4-turn latches
- Latches can be replaced with a variety of latches, including wing knob, keylocking, padlocking, coinproof, and tamper resistant inserts.
- Latches can be replaced with several handles, including chrome keylocking and padlocking, and the black 5in and 7in SCE handles, including keylocking, padlocking, and coinproof.
- Latches are opened or closed with a screwdriver.
- A three-point latching system is available for enclosures over 40in [1016mm] high.
- Mounting holes in back of enclosure
- Mounting hardware, sealing washers, and hole plugs are included.
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Ground studs on door and body
- Provision for lifting lugs are included on enclosures with height greater than 48in [1219mm] and with depth greater than 16 in [406 mm].
 - Lifting lug assembly is included with the enclosure bolt pack.

Options

- Optional mounting feet available ([SCE-ELMFK4](#))
- Door hardware available

Finish

- ANSI 61 gray or RAL 7035 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount						
ANSI 61 Gray	RAL 7035 Gray	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-12EL1206LP	SCE-12EL1206LPLG	\$227.00	12.00 x 12.00 x 7.10 [305 x 305 x 180]	PDF	SCE-12DLP12	\$19.00
SCE-12EL2406LP	SCE-12EL2406LPLG	\$271.00	12.00 x 24.00 x 7.10 [305 x 610 x 180]	PDF	SCE-12P24	\$38.50
SCE-12EL2408LP	SCE-12EL2408LPLG	\$296.00	12.00 x 24.00 x 9.10 [305 x 610 x 231]	PDF	SCE-12P24	\$38.50
SCE-16EL1206LP	SCE-16EL1206LPLG	\$240.00	16.00 x 12.00 x 7.10 [406 x 305 x 180]	PDF	SCE-16P12	\$20.50
SCE-16EL1208LP	SCE-16EL1208LPLG	\$254.00	16.00 x 12.00 x 9.10 [406 x 305 x 231]	PDF	SCE-16P12	\$20.50
SCE-16EL1408LP	SCE-16EL1408LPLG	\$262.00	16.00 x 14.00 x 9.10 [406 x 356 x 231]	PDF	SCE-16DLP14	\$24.50
SCE-16EL1606LP	SCE-16EL1606LPLG	\$260.00	16.00 x 16.00 x 7.10 [406 x 406 x 180]	PDF	SCE-16P16	\$34.00
SCE-16EL1608LP	SCE-16EL1608LPLG	\$290.00	16.00 x 16.00 x 9.10 [406 x 406 x 231]	PDF	SCE-16P16	\$34.00
SCE-16EL2006LP	SCE-16EL2006LPLG	\$292.00	16.00 x 20.00 x 7.10 [406 x 508 x 180]	PDF	SCE-20P16	\$42.00
SCE-16EL2008LP	SCE-16EL2008LPLG	\$294.00	16.00 x 20.00 x 9.10 [406 x 508 x 231]	PDF	SCE-20P16	\$42.00
SCE-20EL1206LP	SCE-20EL1206LPLG	\$259.00	20.00 x 12.00 x 7.10 [508 x 305 x 180]	PDF	SCE-20P12	\$32.00
SCE-20EL1606LP	SCE-20EL1606LPLG	\$278.00	20.00 x 16.00 x 7.10 [508 x 406 x 180]	PDF	SCE-20P16	\$42.00
SCE-20EL1608LP	SCE-20EL1608LPLG	\$294.00	20.00 x 16.00 x 9.10 [508 x 406 x 231]	PDF	SCE-20P16	\$42.00
SCE-20EL1610LP	SCE-20EL1610LPLG	\$312.00	20.00 x 16.00 x 11.10 [508 x 406 x 282]	PDF	SCE-20P16	\$42.00
SCE-20EL1612LP	SCE-20EL1612LPLG	\$325.00	20.00 x 16.00 x 13.10 [508 x 406 x 333]	PDF	SCE-20P16	\$42.00
SCE-20EL2006LP	SCE-20EL2006LPLG	\$300.00	20.00 x 20.00 x 7.10 [508 x 508 x 180]	PDF	SCE-20P20	\$49.00
SCE-20EL2008LP	SCE-20EL2008LPLG	\$316.00	20.00 x 20.00 x 9.10 [508 x 508 x 231]	PDF	SCE-20P20	\$49.00
SCE-20EL2010LP	SCE-20EL2010LPLG	\$334.00	20.00 x 20.00 x 11.10 [508 x 508 x 282]	PDF	SCE-20P20	\$49.00
SCE-20EL2012LP	SCE-20EL2012LPLG	\$351.00	20.00 x 20.00 x 13.10 [508 x 508 x 333]	PDF	SCE-20P20	\$49.00
SCE-20EL2408LP	SCE-20EL2408LPLG	\$341.00	20.00 x 24.00 x 9.10 [508 x 610 x 231]	PDF	SCE-24P20	\$63.00
SCE-24EL1206LP	SCE-24EL1206LPLG	\$271.00	24.00 x 12.00 x 7.10 [610 x 305 x 180]	PDF	SCE-12P24	\$38.50
SCE-24EL1606LP	SCE-24EL1606LPLG	\$297.00	24.00 x 16.00 x 7.10 [610 x 406 x 180]	PDF	SCE-24P16	\$45.50
SCE-24EL1608LP	SCE-24EL1608LPLG	\$313.00	24.00 x 16.00 x 9.10 [610 x 406 x 231]	PDF	SCE-24P16	\$45.50
SCE-24EL2006LP	SCE-24EL2006LPLG	\$322.00	24.00 x 20.00 x 7.10 [610 x 508 x 180]	PDF	SCE-24P20	\$63.00
SCE-24EL2008LP	SCE-24EL2008LPLG	\$341.00	24.00 x 20.00 x 9.10 [610 x 508 x 231]	PDF	SCE-24P20	\$63.00
SCE-24EL2010LP	SCE-24EL2010LPLG	\$362.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$63.00
SCE-24EL2012LP	SCE-24EL2012LPLG	\$380.00	24.00 x 20.00 x 13.10 [610 x 508 x 333]	PDF	SCE-24P20	\$63.00
SCE-24EL2016LP	SCE-24EL2016LPLG	\$417.00	24.00 x 20.00 x 17.10 [610 x 508 x 434]	PDF	SCE-24P20	\$63.00
SCE-24EL2406LP	SCE-24EL2406LPLG	\$348.00	24.00 x 24.00 x 7.10 [610 x 610 x 180]	PDF	SCE-24P24	\$74.00
SCE-24EL2408LP	SCE-24EL2408LPLG	\$368.00	24.00 x 24.00 x 9.10 [610 x 610 x 231]	PDF	SCE-24P24	\$74.00
SCE-24EL2410LP	SCE-24EL2410LPLG	\$389.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$74.00
SCE-24EL2412LP	SCE-24EL2412LPLG	\$408.00	24.00 x 24.00 x 13.10 [610 x 610 x 333]	PDF	SCE-24P24	\$74.00
SCE-24EL2416LP	SCE-24EL2416LPLG	\$449.00	24.00 x 24.00 x 17.10 [610 x 610 x 434]	PDF	SCE-24P24	\$74.00
SCE-24EL3008LP	SCE-24EL3008LPLG	\$408.00	24.00 x 30.00 x 9.10 [610 x 762 x 231]	PDF	SCE-30P24	\$88.00
SCE-24EL3010LP	SCE-24EL3010LPLG	\$440.00	24.00 x 30.00 x 11.10 [610 x 762 x 282]	PDF	SCE-30P24	\$88.00
SCE-24EL3012LP	SCE-24EL3012LPLG	\$470.00	24.00 x 30.00 x 13.10 [610 x 762 x 333]	PDF	SCE-30P24	\$88.00
SCE-30EL1606LP	SCE-30EL1606LPLG	\$325.00	30.00 x 16.00 x 7.10 [762 x 406 x 180]	PDF	SCE-30P16	\$63.00
SCE-30EL2008LP	SCE-30EL2008LPLG	\$376.00	30.00 x 20.00 x 9.10 [762 x 508 x 231]	PDF	SCE-30P20	\$77.00
SCE-30EL2010LP	SCE-30EL2010LPLG	\$395.00	30.00 x 20.00 x 11.10 [762 x 508 x 282]	PDF	SCE-30P20	\$77.00
SCE-30EL2406LP	SCE-30EL2406LPLG	\$383.00	30.00 x 24.00 x 7.10 [762 x 610 x 180]	PDF	SCE-30P24	\$88.00
SCE-30EL2408LP	SCE-30EL2408LPLG	\$408.00	30.00 x 24.00 x 9.10 [762 x 610 x 231]	PDF	SCE-30P24	\$88.00

Note: Dimensions in inches [millimeters].

Table continued on next page

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page.

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount						
ANSI 61 Gray	RAL 7035 Gray	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-30EL2410LP	SCE-30EL2410PLG	\$440.00	30.00 x 24.00 x 11.10 [762 x 610 x 282]	PDF	SCE-30P24	\$88.00
SCE-30EL2412LP	SCE-30EL2412PLG	\$453.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$88.00
SCE-30EL2416LP	SCE-30EL2416PLG	\$500.00	30.00 x 24.00 x 17.10 [762 x 610 x 434]	PDF	SCE-30P24	\$88.00
SCE-30EL2420LP	SCE-30EL2420PLG	\$546.00	30.00 x 24.00 x 21.10 [762 x 610 x 536]	PDF	SCE-30P24	\$88.00
SCE-30EL2424LP	SCE-30EL2424PLG	\$592.00	30.00 x 24.00 x 25.10 [762 x 610 x 638]	PDF	SCE-30P24	\$88.00
SCE-30EL3008LP	SCE-30EL3008PLG	\$456.00	30.00 x 30.00 x 9.10 [762 x 762 x 231]	PDF	SCE-30P30	\$116.00
SCE-30EL3010LP	SCE-30EL3010PLG	\$508.00	30.00 x 30.00 x 11.10 [762 x 762 x 282]	PDF	SCE-30P30	\$116.00
SCE-30EL3012LP	SCE-30EL3012PLG	\$523.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$116.00
SCE-30EL3608LP	SCE-30EL3608PLG	\$505.00	30.00 x 36.00 x 9.10 [762 x 914 x 231]	PDF	SCE-36P30	\$141.00
SCE-36EL2408LP	SCE-36EL2408PLG	\$449.00	36.00 x 24.00 x 9.10 [914 x 610 x 231]	PDF	SCE-36P24	\$105.00
SCE-36EL2410LP	SCE-36EL2410PLG	\$488.00	36.00 x 24.00 x 11.10 [914 x 610 x 282]	PDF	SCE-36P24	\$105.00
SCE-36EL2412LP	SCE-36EL2412PLG	\$500.00	36.00 x 24.00 x 13.10 [914 x 610 x 333]	PDF	SCE-36P24	\$105.00
SCE-36EL2416LP	SCE-36EL2416PLG	\$517.00	36.00 x 24.00 x 17.10 [914 x 610 x 434]	PDF	SCE-36P24	\$105.00
SCE-36EL3008LP	SCE-36EL3008PLG	\$505.00	36.00 x 30.00 x 9.10 [914 x 762 x 231]	PDF	SCE-36P30	\$141.00
SCE-36EL3010LP	SCE-36EL3010PLG	\$538.00	36.00 x 30.00 x 11.10 [914 x 762 x 282]	PDF	SCE-36P30	\$141.00
SCE-36EL3012LP	SCE-36EL3012PLG	\$560.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$141.00
SCE-36EL3016LP	SCE-36EL3016PLG	\$616.00	36.00 x 30.00 x 17.10 [914 x 762 x 434]	PDF	SCE-36P30	\$141.00
SCE-36EL3020LP	SCE-36EL3020PLG	\$671.00	36.00 x 30.00 x 21.10 [914 x 762 x 536]	PDF	SCE-36P30	\$141.00
SCE-36EL3608LP	SCE-36EL3608PLG	\$560.00	36.00 x 36.00 x 9.10 [914 x 914 x 231]	PDF	SCE-36P36	\$165.00
SCE-36EL3610LP	SCE-36EL3610PLG	\$604.00	36.00 x 36.00 x 11.10 [914 x 914 x 282]	PDF	SCE-36P36	\$165.00
SCE-36EL3612LP	SCE-36EL3612PLG	\$620.00	36.00 x 36.00 x 13.10 [914 x 914 x 333]	PDF	SCE-36P36	\$165.00
SCE-36EL3616LP	SCE-36EL3616PLG	\$681.00	36.00 x 36.00 x 17.10 [914 x 914 x 434]	PDF	SCE-36P36	\$165.00
SCE-40EL2412LP	SCE-40EL2412PLG	\$529.00	40.00 x 24.00 x 13.10 [1016 x 610 x 333]	PDF	SCE-40P24	\$119.00
SCE-42EL2410LP	SCE-42EL2410PLG	\$566.00	42.00 x 24.00 x 11.10 [1067 x 610 x 282]	PDF	SCE-42P24	\$127.00
SCE-42EL3008LP	SCE-42EL3008PLG	\$555.00	42.00 x 30.00 x 9.10 [1067 x 762 x 231]	PDF	SCE-42P30	\$162.00
SCE-42EL3010LP	SCE-42EL3010PLG	\$582.00	42.00 x 30.00 x 11.10 [1067 x 762 x 282]	PDF	SCE-42P30	\$162.00
SCE-42EL3012LP	SCE-42EL3012PLG	\$614.00	42.00 x 30.00 x 13.10 [1067 x 762 x 333]	PDF	SCE-42P30	\$162.00
SCE-42EL3016LP	SCE-42EL3016PLG	\$654.00	42.00 x 30.00 x 17.10 [1067 x 762 x 434]	PDF	SCE-42P30	\$162.00
SCE-42EL3608LP	SCE-42EL3608PLG	\$617.00	42.00 x 36.00 x 9.10 [1067 x 914 x 231]	PDF	SCE-42P36	\$190.00
SCE-42EL3610LP	SCE-42EL3610PLG	\$648.00	42.00 x 36.00 x 11.10 [1067 x 914 x 282]	PDF	SCE-42P36	\$190.00
SCE-42EL3612LP	SCE-42EL3612PLG	\$681.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$190.00
SCE-42EL3616LP	SCE-42EL3616PLG	\$748.00	42.00 x 36.00 x 17.10 [1067 x 914 x 434]	PDF	SCE-42P36	\$190.00
SCE-48EL2408LP	SCE-48EL2408PLG	\$531.00	48.00 x 24.00 x 9.10 [1219 x 610 x 231]	PDF	SCE-48P24	\$137.00
SCE-48EL2412LP	SCE-48EL2412PLG	\$590.00	48.00 x 24.00 x 13.10 [1219 x 610 x 333]	PDF	SCE-48P24	\$137.00
SCE-48EL3008LP	SCE-48EL3008PLG	\$617.00	48.00 x 30.00 x 9.10 [1219 x 762 x 231]	PDF	SCE-48P30	\$179.00
SCE-48EL3010LP	SCE-48EL3010PLG	\$634.00	48.00 x 30.00 x 11.10 [1219 x 762 x 282]	PDF	SCE-48P30	\$179.00
SCE-48EL3012LP	—	—	48.00 x 30.00 x 13.10 [1219 x 762 x 333]	PDF	SCE-48P30	\$179.00
SCE-48EL3016LP	SCE-48EL3016PLG	\$710.00	48.00 x 30.00 x 17.10 [1219 x 762 x 434]	PDF	SCE-48P30	\$179.00
SCE-48EL3608LP	SCE-48EL3608PLG	\$671.00	48.00 x 36.00 x 9.10 [1219 x 914 x 231]	PDF	SCE-48P36	\$214.00
SCE-48EL3610LP	SCE-48EL3610PLG	\$709.00	48.00 x 36.00 x 11.10 [1219 x 914 x 282]	PDF	SCE-48P36	\$214.00
SCE-48EL3612LP	SCE-48EL3612PLG	\$742.00	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$214.00

Note: Dimensions in inches [millimeters].

Table continued on next page

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount



Your Enclosure Source®

Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page.

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount						
ANSI 61 Gray	RAL 7035 Gray	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-48EL3616LP	SCE-48EL3616LPLG	\$814.00	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$214.00
SCE-48EL3620LP	SCE-48EL3620LPLG	\$885.00	48.00 x 36.00 x 21.10 [1219 x 914 x 536]	PDF	SCE-48P36	\$214.00
SCE-60EL2412LP	SCE-60EL2412LPLG	\$681.00	60.00 x 24.00 x 13.10 [1524 x 610 x 333]	PDF	SCE-60P24	\$179.00
SCE-60EL3608LP	SCE-60EL3608LPLG	\$803.00	60.00 x 36.00 x 9.10 [1524 x 914 x 231]	PDF	SCE-60P36	\$264.00
SCE-60EL3610LP	SCE-60EL3610LPLG	\$826.00	60.00 x 36.00 x 11.10 [1524 x 914 x 282]	PDF	SCE-60P36	\$264.00
SCE-60EL3612LP	SCE-60EL3612LPLG	\$864.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$264.00
SCE-60EL3616LP	SCE-60EL3616LPLG	\$946.00	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$264.00
SCE-60EL3620LP	SCE-60EL3620LPLG	\$1,030.00	60.00 x 36.00 x 21.10 [1524 x 914 x 536]	PDF	SCE-60P36	\$264.00
SCE-60EL3624LP	SCE-60EL3624LPLG	\$1,394.00	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$264.00
SCE-72EL3012LP	SCE-72EL3012LPLG	\$926.00	72.00 x 30.00 x 13.10 [1829 x 762 x 333]	PDF	SCE-72P30	\$292.00
SCE-72EL3016LP	SCE-72EL3016LPLG	\$1,059.00	72.00 x 30.00 x 17.10 [1829 x 762 x 434]	PDF	SCE-72P30	\$292.00
SCE-72EL3024LP	SCE-72EL3024LPLG	\$1,163.00	72.00 x 30.00 x 25.10 [1829 x 762 x 638]	PDF	SCE-72P30	\$292.00
SCE-72EL3612LP	SCE-72EL3612LPLG	\$989.00	72.00 x 36.00 x 13.10 [1829 x 914 x 333]	PDF	SCE-72P36	\$313.00
SCE-72EL3616LP	SCE-72EL3616LPLG	\$1,125.00	72.00 x 36.00 x 17.10 [1829 x 914 x 434]	PDF	SCE-72P36	\$313.00
SCE-72EL3624LP	SCE-72EL3624LPLG	\$1,532.00	72.00 x 36.00 x 25.10 [1829 x 914 x 638]	PDF	SCE-72P36	\$313.00

Note: Dimensions in inches [millimeters].