

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount with 3-Point Handle



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor application a drip shield is recommended.

Construction

- 14 gauge carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Collar studs provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for all-mounting.
- Mounting hardware, sealing washers and hole plugs included.
- Concealed hinges.
- Removable and interchangeable doors.
- Black zinc die cast keylocking/padlocking handles.
- 3-point latching mechanism.
- Black 1/4-turn latches as required.
- Removable print pocket.
- Oil- and water-resistant gasket.
- Ground stud on door and body.
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm]. Lifting lug assembly included with the enclosure bolt pack.

Options

- Optional mounting feet available.
- Door hardware available.

Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Enviroline Series NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount with 3-Point Handle

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-24EL2010LPPL	\$388.00	24.00 x 20.00 x 11.10 [610 x 508 x 282]	PDF	SCE-24P20	\$48.50
SCE-24EL2410LPPL	\$409.00	24.00 x 24.00 x 11.10 [610 x 610 x 282]	PDF	SCE-24P24	\$56.00
SCE-30EL2412LPPL	\$459.00	30.00 x 24.00 x 13.10 [762 x 610 x 333]	PDF	SCE-30P24	\$67.00
SCE-30EL3012LPPL	\$513.00	30.00 x 30.00 x 13.10 [762 x 762 x 333]	PDF	SCE-30P30	\$89.00
SCE-36EL2412LPPL	\$496.00	36.00 x 24.00 x 13.10 [914 x 610 x 333]	PDF	SCE-36P24	\$81.00
SCE-36EL3012LPPL	\$542.00	36.00 x 30.00 x 13.10 [914 x 762 x 333]	PDF	SCE-36P30	\$108.00
SCE-42EL3612LPPL	\$636.00	42.00 x 36.00 x 13.10 [1067 x 914 x 333]	PDF	SCE-42P36	\$145.00
SCE-48EL3612LPPL	\$684.00	48.00 x 36.00 x 13.10 [1219 x 914 x 333]	PDF	SCE-48P36	\$164.00
SCE-48EL3616LPPL	\$739.00	48.00 x 36.00 x 17.10 [1219 x 914 x 434]	PDF	SCE-48P36	\$164.00
SCE-60EL3612LPPL	\$778.00	60.00 x 36.00 x 13.10 [1524 x 914 x 333]	PDF	SCE-60P36	\$202.00
SCE-60EL3616LPPL	\$842.00	60.00 x 36.00 x 17.10 [1524 x 914 x 434]	PDF	SCE-60P36	\$202.00
SCE-60EL3624LPPL	\$1,190.00	60.00 x 36.00 x 25.10 [1524 x 914 x 638]	PDF	SCE-60P36	\$202.00
SCE-72EL3624LPPL	\$1,350.00	72.00 x 36.00 x 25.10 [1829 x 914 x 638]	PDF	SCE-72P36	\$239.00

Note: Dimensions in inches [millimeters].