

# Enviroline Series NEMA 3R, 4, 4X, 12 & 13 Stainless Steel Double-Door Wall-Mount with 3-Point Handle



## Applications

Designed to house electrical and electronic controls, instrumentation and components. For outdoor applications a drip shield is recommended.

## Construction

- 14 gauge stainless steel Type 304.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Collar studs provided for mounting optional subpanels.
- Removable center posts permit easy subpanel installation.
- Mounting holes in back of the enclosure for wall-mounting.
- Mounting hardware, sealing washers and hole plugs included.
- Stainless steel concealed hinges.
- Removable and interchangeable doors.
- Black keylocking/padlocking handles.
- 3-point latching mechanism.
- Removable print pocket.
- Poured-in-place oil- and water-resistant gasket.
- Ground stud on door and body.

## Options

- Optional tamper-resistant inserts available.
- Optional mounting feet available.
- Door hardware available.
- Note: Mechanical Interlock not for use in enclosures 24in in height.

## Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



# Enviroline Series NEMA 3R, 4, 4X, 12 & 13 Stainless Steel Double-Door Wall-Mount with 3-Point Handle



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Stainless Steel Enviroline Series Wall-Mount Double-Door Enclosures with 3-Point Handle					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-24EL4210SSWFLP</b>	\$2,500.00	24.00 x 42.00 x 11.10 [610 x 1067 x 282]	<a href="#">PDF</a>	<b>SCE-42P24</b>	\$97.00
<b>SCE-24EL4810SSWFLP</b>	\$2,599.00	24.00 x 48.00 x 11.10 [610 x 1219 x 282]	<a href="#">PDF</a>	<b>SCE-48P24</b>	\$105.00
<b>SCE-30EL4210SSWFLP</b>	\$2,648.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	<a href="#">PDF</a>	<b>SCE-42P30</b>	\$124.00
<b>SCE-30EL4810SSWFLP</b>	\$2,798.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	<a href="#">PDF</a>	<b>SCE-48P30</b>	\$137.00
<b>SCE-30EL6010SSWFLP</b>	\$3,142.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	<a href="#">PDF</a>	<b>SCE-60P30</b>	\$169.00
<b>SCE-36EL4212SSWFLP</b>	\$3,154.00	36.00 x 42.00 x 13.10 [914 x 1067 x 333]	<a href="#">PDF</a>	<b>SCE-42P36</b>	\$145.00
<b>SCE-36EL4812SSWFLP</b>	\$3,232.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	<a href="#">PDF</a>	<b>SCE-48P36</b>	\$164.00
<b>SCE-36EL6012SSWFLP</b>	\$3,569.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	<a href="#">PDF</a>	<b>SCE-60P36</b>	\$202.00
<b>SCE-42EL4212SSWFLP</b>	\$3,197.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	<a href="#">PDF</a>	<b>SCE-42P42</b>	\$167.00
<b>SCE-42EL4812SSWFLP</b>	\$3,551.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	<a href="#">PDF</a>	<b>SCE-48P42</b>	\$188.00
<b>SCE-42EL6012SSWFALP</b>	\$3,729.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	<a href="#">PDF</a>	<b>SCE-60BFP42</b>	\$245.00
<b>SCE-48EL4812SSWFLP</b>	\$3,644.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	<a href="#">PDF</a>	<b>SCE-48P48</b>	\$226.00

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12 & 13 Stainless Steel Double-Door Wall-Mount with 3-Point Handle



## Dimensions

