

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Applications

Designed to house electrical and electronic controls, instrumentation and components. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge stainless steel Type 304
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar and studs are provided for mounting optional subpanels.
- Removable center posts permit easy subpanel installation.
- Mounting holes in back of the enclosure for wall-mounting
- Mounting hardware, sealing washers, and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black, keylocking/padlocking handles
- 3-point latching mechanism
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground studs on door and body

Options

- Optional tamper-resistant inserts are available.
- Optional mounting feet are available.
- Door hardware is available.

Note: Mechanical Interlock not for use in enclosures 24.0in [610mm] in height.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Stainless Steel Enviroline Series Wall-Mount Two-Door Enclosures with 3-Point Handle

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<u>SCE-24EL4210SSWFLP</u>	\$3,344.00	24.00 x 42.00 x 11.10 [610 x 1067 x 282]	<u>PDF</u>	<u>SCE-42P24</u>	\$127.00
<u>SCE-24EL4810SSWFLP</u>	\$3,477.00	24.00 x 48.00 x 11.10 [610 x 1219 x 282]	<u>PDF</u>	<u>SCE-48P24</u>	\$137.00
<u>SCE-30EL4210SSWFLP</u>	\$3,544.00	30.00 x 42.00 x 11.10 [762 x 1067 x 282]	<u>PDF</u>	<u>SCE-42P30</u>	\$162.00
<u>SCE-30EL4810SSWFLP</u>	\$3,744.00	30.00 x 48.00 x 11.10 [762 x 1219 x 282]	<u>PDF</u>	<u>SCE-48P30</u>	\$179.00
<u>SCE-30EL6010SSWFLP</u>	\$4,203.00	30.00 x 60.00 x 11.10 [762 x 1524 x 282]	<u>PDF</u>	<u>SCE-60P30</u>	\$221.00
<u>SCE-36EL4212SSWFLP</u>	\$4,219.00	36.00 x 42.00 x 13.10 [914 x 1067 x 333]	<u>PDF</u>	<u>SCE-42P36</u>	\$190.00
<u>SCE-36EL4812SSWFLP</u>	\$4,325.00	36.00 x 48.00 x 13.10 [914 x 1219 x 333]	<u>PDF</u>	<u>SCE-48P36</u>	\$214.00
<u>SCE-36EL6012SSWFLP</u>	\$4,775.00	36.00 x 60.00 x 13.10 [914 x 1524 x 333]	<u>PDF</u>	<u>SCE-60P36</u>	\$264.00
<u>SCE-42EL4212SSWFLP</u>	\$4,277.00	42.00 x 42.00 x 13.10 [1067 x 1067 x 333]	<u>PDF</u>	<u>SCE-42P42</u>	\$218.00
<u>SCE-42EL4812SSWFLP</u>	\$4,751.00	42.00 x 48.00 x 13.10 [1067 x 1219 x 333]	<u>PDF</u>	<u>SCE-48P42</u>	\$246.00
<u>SCE-42EL6012SSWFLP</u>	\$4,989.00	42.00 x 60.00 x 13.10 [1067 x 1524 x 333]	<u>PDF</u>	<u>SCE-60BFP42</u>	\$320.00
<u>SCE-48EL4812SSWFLP</u>	\$4,875.00	48.00 x 48.00 x 13.10 [1219 x 1219 x 333]	<u>PDF</u>	<u>SCE-48P48</u>	\$295.00

Note: Dimensions in inches [millimeters].

Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Wall-Mount with 3-Point Handle



Dimensions

