

# Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



## Applications

Designed to house electrical controls, instruments and components in areas, which are in very wet or oily conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

## Construction

- 16 gauge stainless steel Type 304 and 316/316L.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Poured-in-place oil- and water-resistant gasket.
- Standoffs provided for mounting optional subpanels.
- Removable hinge.
- Doors open 180 degrees.
- Black mini 1/4-turn latches.
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs included.
- Ground stud on door and body.
- Mounting feet included.
- Optional latches available.

## Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<b>SCE-604ELJSS</b>	\$113.00	<b>SCE-604ELJSS6</b>	\$136.00	6.00 x 4.00 x 4.18 [152 x 102 x 106]	<a href="#">PDF</a>	<b>SCE-6P4</b>	\$3.25
<b>SCE-606ELJSS</b>	\$142.00	<b>SCE-606ELJSS6</b>	\$170.00	6.00 x 6.00 x 4.18 [152 x 152 x 106]	<a href="#">PDF</a>	<b>SCE-6P6</b>	\$3.75
<b>SCE-806ELJSS</b>	\$148.00	<b>SCE-806ELJSS6</b>	\$177.00	8.00 x 6.00 x 4.18 [203 x 152 x 106]	<a href="#">PDF</a>	<b>SCE-8P6</b>	\$4.50
<b>SCE-8066ELJSS</b>	\$169.00	<b>SCE-8066ELJSS6</b>	\$203.00	8.00 x 6.00 x 6.18 [203 x 152 x 157]	<a href="#">PDF</a>	<b>SCE-8P6</b>	\$4.50
<b>SCE-1008ELJSS</b>	\$218.00	<b>SCE-1008ELJSS6</b>	\$262.00	10.00 x 8.00 x 4.18 [254 x 203 x 106]	<a href="#">PDF</a>	<b>SCE-10P8</b>	\$6.00
<b>SCE-10086ELJSS</b>	\$243.00	<b>SCE-10086ELJSS6</b>	\$291.00	10.00 x 8.00 x 6.18 [254 x 203 x 157]	<a href="#">PDF</a>	<b>SCE-10P8</b>	\$6.00
<b>SCE-1210ELJSS</b>	\$275.00	<b>SCE-1210ELJSS6</b>	\$330.00	12.00 x 10.00 x 6.18 [305 x 254 x 157]	<a href="#">PDF</a>	<b>SCE-12P10</b>	\$8.25
<b>SCE-12108ELJSS</b>	\$295.00	<b>SCE-12108ELJSS6</b>	\$354.00	12.00 x 10.00 x 8.18 [305 x 254 x 208]	<a href="#">PDF</a>	<b>SCE-12P10</b>	\$8.25
<b>SCE-1212ELJSS</b>	\$297.00	<b>SCE-1212ELJSS6</b>	\$357.00	12.00 x 12.00 x 6.18 [305 x 305 x 157]	<a href="#">PDF</a>	<b>SCE-12P12</b>	\$9.75
<b>SCE-1412ELJSS</b>	\$316.00	<b>SCE-1412ELJSS6</b>	\$379.00	14.00 x 12.00 x 6.18 [356 x 305 x 157]	<a href="#">PDF</a>	<b>SCE-14P12</b>	\$10.75
<b>SCE-14128ELJSS</b>	\$335.00	<b>SCE-14128ELJSS6</b>	\$402.00	14.00 x 12.00 x 8.18 [356 x 305 x 208]	<a href="#">PDF</a>	<b>SCE-14P12</b>	\$10.75
<b>SCE-1614ELJSS</b>	\$372.00	<b>SCE-1614ELJSS6</b>	\$446.00	16.00 x 14.00 x 6.18 [406 x 356 x 157]	<a href="#">PDF</a>	<b>SCE-16P14</b>	\$21.00
<b>SCE-16148ELJSS</b>	\$425.00	<b>SCE-16148ELJSS6</b>	\$510.00	16.00 x 14.00 x 8.18 [406 x 356 x 208]	<a href="#">PDF</a>	<b>SCE-16P14</b>	\$21.00

Note: Dimensions in inches [millimeters].