

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Window



Applications

Designed to house electrical controls, instruments and components that require unrestricted viewing of the gauges or controls, in areas which are in wet or oily conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 16 gauge stainless steel Type 304 and 316/316L.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Poured-in-place oil- and water-resistant gasket.
- 0.25 in [6mm] polycarbonate viewing window.
- Standoffs provided for mounting optional subpanels.
- Removable hinge.
- Doors open 180 degrees.
- Black mini 1/4-turn latches.
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs included.
- Ground stud on door and body.
- Mounting feet included.
- Optional latches available.
- Note: Recommend use as NEMA 3R in fcULus1 outdoor exposure and extreme weather environments.

Finish

- #4 brushed finish on all exterior surfaces.
- Optional subpanels powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



| Shipping Schedule | |
|-------------------|-------------|
| Same day | 1 - 15 days |

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount with Window

| 304 Stainless Steel | Price | 316L Stainless Steel | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
|------------------------|----------|-------------------------|----------|--|---------------------|-------------------|---------|
| SCE-1008ELJWSS | \$300.00 | SCE-1008ELJWSS6 | \$360.00 | 10.00 x 8.00 x 4.18 [254 x 203 x 106] | PDF | SCE-10P8 | \$6.00 |
| SCE-10086ELJWSS | \$317.00 | SCE-10086ELJWSS6 | \$380.00 | 10.00 x 8.00 x 6.18 [254 x 203 x 157] | PDF | SCE-10P8 | \$6.00 |
| SCE-1210ELJWSS | \$350.00 | SCE-1210ELJWSS6 | \$420.00 | 12.00 x 10.00 x 6.18 [305 x 254 x 157] | PDF | SCE-12P10 | \$8.25 |
| SCE-12108ELJWSS | \$361.00 | SCE-12108ELJWSS6 | \$433.00 | 12.00 x 10.00 x 8.18 [305 x 254 x 208] | PDF | SCE-12P10 | \$8.25 |
| SCE-1614ELJWSS | \$471.00 | SCE-1614ELJWSS6 | \$566.00 | 16.00 x 14.00 x 6.18 [406 x 356 x 157] | PDF | SCE-16P14 | \$21.00 |
| SCE-16148ELJWSS | \$499.00 | SCE-16148ELJWSS6 | \$599.00 | 16.00 x 14.00 x 8.18 [406 x 356 x 208] | PDF | SCE-16P14 | \$21.00 |

Note: Dimensions in inches [millimeters].