

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



Your Enclosure Source®



Applications

Designed to house electrical controls, instruments, and components in areas, which are in very wet or oily conditions. Provides a degree of protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

Construction

- 16-gauge stainless steel Type 304 or 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.
- Removable hinge
- Doors open 180°
- Black, mini 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs are included.
- Ground stud on door and body
- Mounting feet are included.
- Optional latches are available.

Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

Enviroline Junction Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount

| 304 Stainless Steel | Price | 316L Stainless Steel | Price | Size HxWxD | Drawing Link | Optional Subpanel | Price |
|--------------------------------|----------|---------------------------------|----------|--|---------------------|---------------------------|---------|
| SCE-604ELJSS | \$150.00 | SCE-604ELJSS6 | \$187.00 | 6.00 x 4.00 x 4.18 [152 x 102 x 106] | PDF | SCE-6P4 | \$4.25 |
| SCE-606ELJSS | \$188.00 | SCE-606ELJSS6 | \$234.00 | 6.00 x 6.00 x 4.18 [152 x 152 x 106] | PDF | SCE-6P6 | \$5.00 |
| SCE-806ELJSS | \$196.00 | SCE-806ELJSS6 | \$244.00 | 8.00 x 6.00 x 4.18 [203 x 152 x 106] | PDF | SCE-8P6 | \$5.75 |
| SCE-8066ELJSS | \$224.00 | SCE-8066ELJSS6 | \$279.00 | 8.00 x 6.00 x 6.18 [203 x 152 x 157] | PDF | SCE-8P6 | \$5.75 |
| SCE-1008ELJSS | \$289.00 | SCE-1008ELJSS6 | \$360.00 | 10.00 x 8.00 x 4.18 [254 x 203 x 106] | PDF | SCE-10P8 | \$8.00 |
| SCE-10086ELJSS | \$322.00 | SCE-10086ELJSS6 | \$401.00 | 10.00 x 8.00 x 6.18 [254 x 203 x 157] | PDF | SCE-10P8 | \$8.00 |
| SCE-1210ELJSS | \$364.00 | SCE-1210ELJSS6 | \$454.00 | 12.00 x 10.00 x 6.18 [305 x 254 x 157] | PDF | SCE-12P10 | \$10.75 |
| SCE-12108ELJSS | \$391.00 | SCE-12108ELJSS6 | \$487.00 | 12.00 x 10.00 x 8.18 [305 x 254 x 208] | PDF | SCE-12P10 | \$10.75 |
| SCE-1212ELJSS | \$394.00 | SCE-1212ELJSS6 | \$490.00 | 12.00 x 12.00 x 6.18 [305 x 305 x 157] | PDF | SCE-12P12 | \$12.50 |
| SCE-1412ELJSS | \$419.00 | SCE-1412ELJSS6 | \$522.00 | 14.00 x 12.00 x 6.18 [356 x 305 x 157] | PDF | SCE-14P12 | \$14.00 |
| SCE-14128ELJSS | \$444.00 | SCE-14128ELJSS6 | \$553.00 | 14.00 x 12.00 x 8.18 [356 x 305 x 208] | PDF | SCE-14P12 | \$14.00 |
| SCE-1614ELJSS | \$493.00 | SCE-1614ELJSS6 | \$614.00 | 16.00 x 14.00 x 6.18 [406 x 356 x 157] | PDF | SCE-16P14 | \$27.50 |
| SCE-16148ELJSS | \$563.00 | SCE-16148ELJSS6 | \$701.00 | 16.00 x 14.00 x 8.18 [406 x 356 x 208] | PDF | SCE-16P14 | \$27.50 |

Note: Dimensions in inches [millimeters].