NEMA 1 Wire Trough

SAGINAW CONTROL & ENGINEERING
Your Enclosure Source ®

Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust tight protection.

Construction

- 16-gauge or 18-gauge carbon steel, depending on size
  - See drawings for details
- Spot weld construction
- Standoffs are provided for mounting optional subpanels.
- Removable cover
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body
- Mounting holes in back of enclosure
- Tamper-resistant 1/4-turn latches available

Finish

- ANSI 61 gray powder coated inside and out

Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

NEMA 1 Single-Door Wall-Mount			
Part Number	***Price***	***Size HxWxD***	***Drawing Link***
SCE-L9N126LP	$219.00	6.00 x 12.00 x 9.00 [152 x 305 x 229]	PDF
SCE-L9N128LP	$232.00	8.00 x 12.00 x 9.00 [203 x 305 x 229]	PDF
SCE-L9N186LP	$221.00	6.00 x 18.00 x 9.00 [152 x 457 x 229]	PDF
SCE-L9N188LP	$234.00	8.00 x 18.00 x 9.00 [203 x 457 x 229]	PDF
SCE-L9N246LP	$228.00	6.00 x 24.00 x 9.00 [152 x 610 x 229]	PDF
SCE-L9N248LP	$241.00	8.00 x 24.00 x 9.00 [203 x 610 x 229]	PDF
SCE-L9N306LP	$229.00	6.00 x 30.00 x 9.00 [152 x 762 x 229]	PDF
SCE-L9N308LP	$242.00	8.00 x 30.00 x 9.00 [203 x 762 x 229]	PDF
SCE-L9N366LP	$232.00	6.00 x 36.00 x 9.00 [152 x 914 x 229]	PDF
SCE-L9N368LP	$234.00	8.00 x 36.00 x 9.00 [203 x 914 x 229]	PDF
Note: Dimensions in inches [millimeters].			