



# Vacuum Ejectors

## Multi-Stage Ejectors

## Basic Ejector

Schmalz multi-stage and basic ejectors are efficient with a very high suction rate. They are excellent for vacuum applications with both airtight and porous products. Either ejector is easily maintained.



**Part No. 10.02.01.01606**  
**Model No. SBPL-100-HF-NPT**



**Part No. 10.02.01.00566**  
**Model No. SBP-15-S02-SDA**



**Part No. 10.02.01.01598**  
**Model No. SBPL-100-HF**

## Features:

- SBPL multi-stage ejectors can be used for central vacuum applications with suction rates of 500 l/min [17.7 cfm] to 860 l/min [30.4 cfm]
- SBP basic ejectors can mount very close to the cup with suction rates of 37.7 l/min [1.3 cfm] to 71 l/min [2.5 cfm]

| Vacuum Ejectors       |                   |          |                        |                     |                     |                     |                     |
|-----------------------|-------------------|----------|------------------------|---------------------|---------------------|---------------------|---------------------|
| Part No.              | Schmalz Model No. | Price    | Suction Rate           | Inlet(s)            | Vacuum Port         | Drawing Link        | Manufacturer Specs  |
| <b>10.02.01.01605</b> | SBPL-50-HF-NPT    | \$320.00 | 500.0 l/min [17.7 cfm] | 3/8 in female NPT   | 3/4 in female NPT   | <a href="#">PDF</a> | <a href="#">PDF</a> |
| <b>10.02.01.01606</b> | SBPL-100-HF-NPT   | \$553.00 | 860.0 l/min [30.4 cfm] |                     | 1 inch female NPT   | <a href="#">PDF</a> | <a href="#">PDF</a> |
| <b>10.02.01.01597</b> | SBPL-50-HF        | \$320.00 | 500.0 l/min [17.7 cfm] | G3/8 female BSPP    | G3/4 female BSPP    | <a href="#">PDF</a> | <a href="#">PDF</a> |
| <b>10.02.01.01598</b> | SBPL-100-HF       | \$553.00 | 860.0 l/min [30.4 cfm] |                     | G1 female BSPP      | <a href="#">PDF</a> | <a href="#">PDF</a> |
| <b>10.02.01.00565</b> | SBP-10-S02-SDA    | \$38.00  | 37.7 l/min [1.3 cfm]   | 6mm push-to-connect | 8mm push-to-connect | <a href="#">PDF</a> | <a href="#">PDF</a> |
| <b>10.02.01.00566</b> | SBP-15-S02-SDA    | \$41.00  | 71.0 l/min [2.5 cfm]   |                     |                     | <a href="#">PDF</a> | <a href="#">PDF</a> |

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).