



Vacuum Suction Cups with Fittings - Silicone



Part No. 10.01.06.00092
Model No. FSGA-43-SI-55-G1/4-AG



Part No. 10.01.06.03526
Model No. SPB4-40-SI-55-G1/4-AG

Schmalz silicone suction cups are an excellent choice for applications requiring resistance to elevated temperatures and FDA requirements. AutomationDirect.com's offering includes bellows cups with G-thread (BSPP) fittings. Sizes range from 14 to 63mm diameter. Replacement cups are available for all sizes.

Features:

- Silicone cup material with aluminum fitting
- Single and quadruple bellows styles
- Sizes 14 to 63mm diameter
- Fitting sizes G 1/8 to G 1/4

Vacuum Suction Cups with Fittings - Silicone								
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs
10.01.06.00384	FSGA-14-SI-55-G1/8-AG	\$10.00	Bellows	1	14mm	G1/8 male BSPP	PDF	PDF
10.01.06.00393	FSGA-20-SI-55-G1/8-AG	\$10.50			20mm		PDF	PDF
10.01.06.00091	FSGA-33-SI-55-G1/4-AG	\$13.00			33mm	G1/4 male BSPP	PDF	PDF
10.01.06.00092	FSGA-43-SI-55-G1/4-AG	\$15.50			43mm		PDF	PDF
10.01.06.00093	FSGA-53-SI-55-G1/4-AG	\$18.50			53mm		PDF	PDF
10.01.06.00686	FSGA-63-SI-55-G1/4-AG	\$24.50			63mm		PDF	PDF
10.01.06.03515	SPB4-20-SI-55-G1/4-AG	\$18.00		4	20mm	G1/4 male BSPP	PDF	PDF
10.01.06.03521	SPB4-30-SI-55-G1/4-AG	\$20.00			30mm		PDF	PDF
10.01.06.03526	SPB4-40-SI-55-G1/4-AG	\$26.00			40mm		PDF	PDF
10.01.06.03532	SPB4-50-SI-55-G1/4-AG	\$34.50			50mm		PDF	PDF



Part No. 10.01.06.00127
Model No. FGA-43-SI-55-N018



Part No. 10.01.06.02590
Model No. SPB4-40-SI-55-SC090

Replacement Vacuum Suction Cups - Silicone						
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs
10.01.06.00371	FGA-14-SI-55-N016	\$7.25	Bellows	1	14mm	PDF
10.01.06.00374	FGA-20-SI-55-N016	\$8.00			20mm	PDF
10.01.06.00126	FGA-33-SI-55-N018	\$8.50			33mm	PDF
10.01.06.00127	FGA-43-SI-55-N018	\$10.50			43mm	PDF
10.01.06.00128	FGA-53-SI-55-N018	\$14.00			53mm	PDF
10.01.06.00689	FGA-63-SI-55-N018	\$20.00			63mm	PDF
10.01.06.02588	SPB4-20-SI-55-SC080	\$12.50		4	20mm	PDF
10.01.06.02589	SPB4-30-SI-55-SC080	\$14.50			30mm	PDF
10.01.06.02590	SPB4-40-SI-55-SC090	\$19.50			40mm	PDF
10.01.06.02613	SPB4-50-SI-55-SC090	\$27.50			50mm	PDF

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).