

# NEMA 1 Screw Cover Wall-Mount



SC080806NK



SC080806

## Applications

This style is designed for use as a junction box and pull box in commercial and general industrial applications.

## Construction

- Bodies and doors fabricated from 16-, 14-, or 12-gauge steel
- Flat, removable covers fastened with plated steel screws
- Cover design permits easy removal without extracting cover screws
- Mounting holes on back of enclosure
- Available with or without knockouts
- Removable concentric knockouts on all four sides of standard enclosures with knockouts

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, 1 [UL File E23553]
- Meets NEMA/EEMAC 1 requirements



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## NEMA 1 Screw Cover Wall-Mount

Painted		Body/Door Steel Gauge	Enclosure SizeHxD	Knockout Pattern			
With Knockouts	Price			Without Knockouts	Price	Width Side	Height Side
<a href="#">SC040404*</a>	\$9.75	<a href="#">SC040404NK*</a>	\$9.75	16/16	4.13 x 4.13 x 4.47 [105 x 105 x 114]	A	A
<a href="#">SC040604*</a>	\$11.75	<a href="#">SC040604NK*</a>	\$11.75	16/16	6.13 x 4.13 x 4.47 [156 x 105 x 114]	A	A-B-A
<a href="#">SC060604</a>	\$14.00	<a href="#">SC060604NK</a>	\$14.00	16/16	6.13 x 6.13 x 4.47 [156 x 156 x 114]	A-B-A	A-B-A
<a href="#">SC060606</a>	\$17.00	<a href="#">SC060606NK</a>	\$17.00	16/16	6.13 x 6.13 x 6.47 [156 x 156 x 164]	A-B-A	A-B-A
<a href="#">SC060804</a>	\$16.50	<a href="#">SC060804NK</a>	\$16.50	16/16	8.13 x 6.13 x 4.47 [207 x 156 x 114]	A-B-A	A-B-A
<a href="#">SC060806</a>	\$19.00	<a href="#">SC060806NK</a>	\$19.00	16/16	8.13 x 6.13 x 6.47 [207 x 156 x 164]	A-B-A	A-B-A
<a href="#">SC061204</a>	\$22.00	<a href="#">SC061204NK</a>	\$22.00	16/16	12.13 x 6.13 x 4.47 [308 x 156 x 114]	A-B-A	B-A-F-F-A-B
<a href="#">SC061206</a>	\$24.00	<a href="#">SC061206NK</a>	\$24.00	16/16	12.13 x 6.13 x 6.47 [308 x 156 x 164]	A-B-A	B-A-F-F-A-B
<a href="#">SC080804</a>	\$19.25	<a href="#">SC080804NK</a>	\$19.25	16/16	8.13 x 4.47 x 8.13 [207 x 207 x 114]	A-B-A	A-B-A
<a href="#">SC080806</a>	\$23.00	<a href="#">SC080806NK</a>	\$23.00	16/16	8.13 x 8.13 x 6.47 [207 x 207 x 164]	A-B-A	A-B-A
<a href="#">SC080808</a>	\$26.50	<a href="#">SC080808NK</a>	\$26.50	16/16	8.00 x 8.13 x 8.13 [203 x 207 x 207]	A-B-A	A-B-A
<a href="#">SC081004</a>	\$22.00	<a href="#">SC081004NK</a>	\$22.00	16/16	10.13 x 8.13 x 4.47 [257 x 207 x 114]	A-B-A	B-A-F-F-A
<a href="#">SC081006</a>	\$26.50	<a href="#">SC081006NK</a>	\$26.50	16/16	10.13 x 8.13 x 6.47 [257 x 207 x 164]	A-B-A	B-A-F-F-A
<a href="#">SC081204</a>	\$25.00	<a href="#">SC081204NK</a>	\$25.00	16/16	12.13 x 8.13 x 4.47 [308 x 207 x 114]	A-B-A	B-A-F-F-A-B
<a href="#">SC081206</a>	\$28.50	<a href="#">SC081206NK</a>	\$28.50	16/16	12.13 x 8.13 x 6.47 [308 x 207 x 164]	A-B-A	B-A-F-F-A-B

Notes: Dimensions in inches [millimeters]

Not UL listed.

A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

Continued on next page

# NEMA 1 Screw Cover Wall-Mount



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Continued from previous page

NEMA 1 Screw Cover Wall-Mount							
Painted				Body/Door Steel Gauge	Enclosure SizeHxWxD	Knockout Pattern	
With Knockouts	Price	Without Knockouts	Price			Width Side	Height Side
<a href="#">SC101004</a>	\$25.50	<a href="#">SC101004NK</a>	\$25.50	16/16	10.13 x 10.13 x 4.47 [257 x 257 x 114]	B-A-F-F-A	B-A-F-F-A
<a href="#">SC101006</a>	\$30.00	<a href="#">SC101006NK</a>	\$30.00	16/16	10.13 x 10.13 x 6.47 [257 x 257 x 164]	B-A-F-F-A	B-A-F-F-A
<a href="#">SC101204</a>	\$29.00	<a href="#">SC101204NK</a>	\$29.00	16/16	12.13 x 10.13 x 4.47 [308 x 257 x 114]	B-A-F-F-A	B-A-F-F-A-B
<a href="#">SC101206</a>	\$34.00	<a href="#">SC101206NK</a>	\$34.00	16/16	12.13 x 10.13 x 6.47 [308 x 257 x 164]	B-A-F-F-A	B-A-F-F-A-B
<a href="#">SC121204</a>	\$32.50	<a href="#">SC121204NK</a>	\$32.50	16/16	12.13 x 12.13 x 4.47 [308 x 308 x 114]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">SC121206</a>	\$38.50	<a href="#">SC121206NK</a>	\$38.50	16/16	12.13 x 12.13 x 6.47 [308 x 308 x 164]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">SC121208</a>	\$40.50	<a href="#">SC121208NK</a>	\$40.50	16/16	12.00 x 12.13 x 8.13 [305 x 308 x 207]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">SC121210</a>	\$43.50	<a href="#">SC121210NK</a>	\$43.50	16/16	12.00 x 12.13 x 10.13 [305 x 308 x 257]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">SC121212</a>	\$66.00	<a href="#">SC121212NK</a>	\$66.00	16/16	12.00 x 12.13 x 12.13 [305 x 308 x 308]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">SC121504</a>	\$37.50	<a href="#">SC121504NK</a>	\$37.50	16/16	15.13 x 12.13 x 4.47 [384 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121506</a>	\$44.00	<a href="#">SC121506NK</a>	\$44.00	16/16	15.13 x 12.13 x 6.47 [384 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121608</a>	\$54.00	<a href="#">SC121608NK</a>	\$54.00	16/16	16.00 x 12.13 x 8.13 [406 x 308 x 207]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121804</a>	\$44.00	<a href="#">SC121804NK</a>	\$44.00	16/16	18.13 x 12.13 x 4.47 [461 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121806</a>	\$51.00	<a href="#">SC121806NK</a>	\$51.00	16/16	18.13 x 12.13 x 6.47 [461 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121808</a>	\$53.00	<a href="#">SC121808NK</a>	\$53.00	16/16	18.00 x 12.13 x 8.13 [457 x 308 x 207]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC121810</a>	\$71.00	<a href="#">SC121810NK</a>	\$71.00	16/16	18.00 x 12.13 x 10.13 [457 x 308 x 257]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC122404</a>	\$56.00	<a href="#">SC122404NK</a>	\$56.00	16/16	24.12 x 12.13 x 4.47 [613 x 308 x 114]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC122406</a>	\$65.00	<a href="#">SC122406NK</a>	\$65.00	16/16	24.12 x 12.13 x 6.47 [613 x 308 x 164]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC122408</a>	\$77.00	<a href="#">SC122408NK</a>	\$77.00	16/16	24.00 x 12.13 x 8.13 [610 x 308 x 207]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC122410</a>	\$65.00	<a href="#">SC122410NK</a>	\$65.00	16/16	24.00 x 12.13 x 10.13 [610 x 308 x 257]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC122412</a>	\$68.00	<a href="#">SC122412NK</a>	\$68.00	16/16	24.00 x 12.13 x 12.13 [610 x 308 x 308]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">SC151504</a>	\$45.50	<a href="#">SC151504NK</a>	\$45.50	16/16	15.13 x 15.13 x 4.47 [384 x 384 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC151506</a>	\$51.00	<a href="#">SC151506NK</a>	\$51.00	16/16	15.13 x 15.13 x 6.47 [384 x 384 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC151804</a>	\$56.00	<a href="#">SC151804NK</a>	\$56.00	16/16	18.13 x 15.13 x 4.47 [461 x 384 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC151806</a>	\$59.00	<a href="#">SC151806NK</a>	\$59.00	16/16	18.13 x 15.13 x 6.47 [461 x 384 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC181804</a>	\$59.00	<a href="#">SC181804NK</a>	\$59.00	16/16	18.13 x 18.13 x 4.47 [461 x 461 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC181806</a>	\$68.00	<a href="#">SC181806NK</a>	\$68.00	16/16	18.13 x 18.13 x 6.47 [461 x 461 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC181808</a>	\$77.00	<a href="#">SC181808NK</a>	\$77.00	16/16	18.00 x 18.13 x 8.13 [457 x 461 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC181810</a>	\$99.00	<a href="#">SC181810NK</a>	\$99.00	16/16	18.00 x 18.13 x 10.13 [457 x 461 x 257]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC181812</a>	\$85.00	<a href="#">SC181812NK</a>	\$85.00	16/16	18.00 x 18.13 x 12.13 [457 x 461 x 308]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC182404</a>	\$91.00	<a href="#">SC182404NK</a>	\$91.00	16/16	24.12 x 18.13 x 4.09 [613 x 461 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC182406</a>	\$107.00	<a href="#">SC182406NK</a>	\$107.00	16/16	24.12 x 18.13 x 6.49 [613 x 461 x 164]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC182408</a>	\$115.00	<a href="#">SC182408NK</a>	\$115.00	16/16	24.00 x 18.13 x 8.13 [610 x 461 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC182410</a>	\$177.00	<a href="#">SC182410NK</a>	\$177.00	16/16	24.00 x 18.13 x 10.13 [610 x 461 x 257]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC182412</a>	\$192.00	<a href="#">SC182412NK</a>	\$192.00	16/16	24.00 x 18.13 x 12.13 [610 x 461 x 308]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC183004</a>	\$112.00	<a href="#">SC183004NK</a>	\$112.00	16/16	30.12 x 18.13 x 4.47 [765 x 461 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC242404</a>	\$119.00	<a href="#">SC242404NK</a>	\$119.00	14/14	24.12 x 24.12 x 4.49 [613 x 613 x 114]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A

Notes: Dimensions in inches [millimeters]  
 Not UL listed.  
 A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

Continued on next page

# NEMA 1 Screw Cover Wall-Mount



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Continued from previous page

NEMA 1 Screw Cover Wall-Mount							
Painted				Body/Door Steel Gauge	Enclosure SizeHxWxD	Knockout Pattern	
With Knockouts	Price	Without Knockouts	Price			Width Side	Height Side
<a href="#">SC242406</a>	\$138.00	<a href="#">SC242406NK</a>	\$138.00	14/14	24.12 x 24.12 x 6.49 [613 x 613 x 165]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC242408</a>	\$153.00	<a href="#">SC242408NK</a>	\$153.00	14/14	24.00 x 24.15 x 8.15 [610 x 613 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC242410</a>	\$217.00	<a href="#">SC242410NK</a>	\$217.00	14/14	24.00 x 24.15 x 10.15 [610 x 613 x 258]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC242412</a>	\$235.00	<a href="#">SC242412NK</a>	\$235.00	14/14	24.00 x 24.15 x 12.15 [610 x 613 x 309]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243006</a>	\$166.00	<a href="#">SC243006NK</a>	\$166.00	14/14	30.00 x 24.15 x 6.15 [762 x 613 x 156]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243008</a>	\$218.00	<a href="#">SC243008NK</a>	\$218.00	14/14	30.00 x 24.15 x 8.15 [762 x 613 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243010</a>	\$257.00	<a href="#">SC243010NK</a>	\$257.00	14/14	30.00 x 24.15 x 10.15 [762 x 613 x 258]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243012</a>	\$288.00	<a href="#">SC243012NK</a>	\$288.00	14/14	30.00 x 24.15 x 12.15 [762 x 613 x 309]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243608</a>	\$212.00	<a href="#">SC243608NK</a>	\$212.00	14/14	36.00 x 24.15 x 8.15 [914 x 613 x 207]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243610</a>	\$293.00	<a href="#">SC243610NK</a>	\$293.00	14/14	36.00 x 24.15 x 10.15 [914 x 613 x 258]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
<a href="#">SC243612</a>	\$315.00	<a href="#">SC243612NK</a>	\$315.00	14/14	36.00 x 24.15 x 12.15 [914 x 613 x 309]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303008NK</a>	\$283.00	12/12	30.00 x 30.19 x 8.19 [762 x 767 x 208]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303010NK</a>	\$335.00	12/12	30.00 x 30.19 x 10.19 [762 x 767 x 259]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303012NK</a>	\$368.00	12/12	30.00 x 30.19 x 12.19 [762 x 767 x 310]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303608NK</a>	\$324.00	12/12	36.00 x 30.19 x 8.19 [914 x 767 x 208]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303610NK</a>	\$335.00	12/12	36.00 x 30.19 x 10.19 [914 x 767 x 259]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC303612NK</a>	\$378.00	12/12	36.00 x 30.19 x 12.19 [914 x 767 x 310]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC363608NK</a>	\$307.00	12/12	36.00 x 36.19 x 8.19 [914 x 919 x 208]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC363610NK</a>	\$340.00	12/12	36.00 x 36.19 x 10.19 [914 x 919 x 259]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A
—	—	<a href="#">SC363612NK</a>	\$437.00	12/12	36.00 x 36.19 x 12.19 [914 x 919 x 310]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A

Notes: Dimensions in inches [millimeters]  
 Not UL listed.  
 A WGNDKT must be ordered with each SC enclosure to meet the CSA standard.

# NEMA 1 Screw Cover Wall-Mount



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Grounding Kit		
Part Number	Description	Price
WGNDKT	Grounding Kit	\$2.75
Note: Field grounding kit includes necessary parts to properly ground enclosure..		

## Dimensions

