

Stride SE2 Series Managed Industrial Ethernet Switches



RoHS Compliant

Stride SE2 Series Managed Models				
Part Number	Price	Ethernet Ports	Fiber Ports	Input Power (max)
SE2-SW8M	\$429.00	8	—	8.1 W
SE2-SW8M-2P	\$645.00	6	2 GbE SFP*	9.1 W
SE2-SW8M-2C1	\$539.00		2 SC	8.1 W
SE2-SW8M-2T1	\$539.00		2 ST	
SE2-SW16M	\$829.00	16	—	18W
SE2-SW18MG-2P	\$1,249.00	16, 2 GbE combo	2 GbE SFP combo*	

**Optional SFP modules sold separately.*

Features

- Modbus TCP management capability
- EtherNet/IP management capability
- Wide temp range
- DIN-rail mount with optional panel mount accessory
- Metal housing
- 12, 24 VDC redundant input
- Gigabit Ethernet (GbE) models
- Haz Loc
- 5-year warranty

Panel Mounting Brackets

Stride SE2 series DIN-rail mounted switches can be panel mounted with the addition of the optional panel mounting brackets SE2-PM1 or SE2-PM3.



SE2-Series Panel Mounting Brackets		
Part Number	Price	For use with switch model
SE2-PM1	\$15.00	SE2-SW5Ux, SE2-SW8U-x, and SE2-MCx
SE2-PM3	\$20.00	SE2-SWPx, SE2-SW8UG-T, SE2-SW10UG-2P-T, SE2-SW16U-T, SE2-SW18U-2G-T and all SE2 managed switches