

Seifert Fan Hoods



Features

- Protects fan and exhaust vents from environmental hazards.
- Screw-less mounting and removal of the hood.
- Easy to clean.
- Mounting screws torque: 40 lb-in / 4.5 Nm.
- cULus Recognized File E498756.
- IP56



Stainless Steel Hood

- 304 stainless steel
- Blue Food Safe Gasket
- UL Type 1,2,3,3X,3R,3RX,3S,3SX,5,12,12K and 13



| Seifert Stainless Steel Fan Hood | | | | |
|----------------------------------|----------|------------------------------------|------------------------------------|---------------------|
| Part Number | Price | Max Cutout Size | Max Covered Area | Drawing Link |
| 400000020 | \$130.00 | 3.62 x 3.62 [91.95 x 91.95] | 4.19 x 4.19 [106.43 x 106.43] | PDF |
| 400010020 | \$144.00 | 4.92 x 4.92 [124.97 x 124.97] | 5.91 x 5.91 [150.11 x 150.11] | PDF |
| 400020020 | \$176.00 | 6.97 x 6.97 [177.04 x 177.04] | 8.03 x 8.03 [203.96 x 203.96] | PDF |
| 400030020 | \$206.00 | 8.78 x 8.78 [223.01 x 223.01] | 9.84 x 9.84 [249.94 x 249.94] | PDF |
| 400040020 | \$229.00 | 11.46 x 11.46 [291.08 x 291.08] | 12.80 x 12.80 [325.12 x 325.12] | PDF |

NOTE: Dimensions listed as inches [millimeters]

Carbon Steel Hood

- Carbon steel, powder coated RAL 7035 light gray
- UL Type 1,2,5,12,12K and 13



| Seifert Carbon Steel Fan Hood | | | | |
|-------------------------------|----------|------------------------------------|------------------------------------|---------------------|
| Part Number | Price | Max Cutout Size | Max Covered Area | Drawing Link |
| 400000020 | \$88.00 | 3.62 x 3.62 [91.95 x 91.95] | 4.19 x 4.19 [106.43 x 106.43] | PDF |
| 400010020 | \$103.00 | 4.92 x 4.92 [124.97 x 124.97] | 5.91 x 5.91 [150.11 x 150.11] | PDF |
| 400020020 | \$128.00 | 6.97 x 6.97 [177.04 x 177.04] | 8.03 x 8.03 [203.96 x 203.96] | PDF |
| 400030020 | \$144.00 | 8.78 x 8.78 [223.01 x 223.01] | 9.84 x 9.84 [249.94 x 249.94] | PDF |
| 400040020 | \$168.00 | 11.46 x 11.46 [291.08 x 291.08] | 12.80 x 12.80 [325.12 x 325.12] | PDF |

NOTE: Dimensions listed as inches [millimeters]