

## Features

- Protects fan and exhaust vents from environmental hazards.
- Screw-less mounting and removal of the hood.
- Easy to clean.
- Mounting screws torque: 40 lb-in / 4.5 Nm.
- cULus Recognized File E498756.
- IP56



## Stainless Steel Hood

- 304 stainless steel
- Blue Food Safe Gasket
- UL Type 1,2,3,3X,3R,3RX,3S,3SX,5,12,12K and 13



Seifert Stainless Steel Fan Hood				
Part Number	Price	Max Cutout Size	Max Covered Area	Drawing Link
<a href="#">400000020</a>	\$130.00	3.62 x 3.62 [91.95 x 91.95]	4.19 x 4.19 [106.43 x 106.43]	<a href="#">PDF</a>
<a href="#">400010020</a>	\$144.00	4.92 x 4.92 [124.97 x 124.97]	5.91 x 5.91 [150.11 x 150.11]	<a href="#">PDF</a>
<a href="#">400020020</a>	\$176.00	6.97 x 6.97 [177.04 x 177.04]	8.03 x 8.03 [203.96 x 203.96]	<a href="#">PDF</a>
<a href="#">400030020</a>	\$206.00	8.78 x 8.78 [223.01 x 223.01]	9.84 x 9.84 [249.94 x 249.94]	<a href="#">PDF</a>
<a href="#">400040020</a>	\$229.00	11.46 x 11.46 [291.08 x 291.08]	12.80 x 12.80 [325.12 x 325.12]	<a href="#">PDF</a>

NOTE: Dimensions listed as inches [millimeters]

## Carbon Steel Hood

- Carbon steel, powder coated RAL 7035 light gray
- UL Type 1,2,5,12,12K and 13



Seifert Carbon Steel Fan Hood				
Part Number	Price	Max Cutout Size	Max Covered Area	Drawing Link
<a href="#">400000020</a>	\$88.00	3.62 x 3.62 [91.95 x 91.95]	4.19 x 4.19 [106.43 x 106.43]	<a href="#">PDF</a>
<a href="#">400010020</a>	\$103.00	4.92 x 4.92 [124.97 x 124.97]	5.91 x 5.91 [150.11 x 150.11]	<a href="#">PDF</a>
<a href="#">400020020</a>	\$128.00	6.97 x 6.97 [177.04 x 177.04]	8.03 x 8.03 [203.96 x 203.96]	<a href="#">PDF</a>
<a href="#">400030020</a>	\$144.00	8.78 x 8.78 [223.01 x 223.01]	9.84 x 9.84 [249.94 x 249.94]	<a href="#">PDF</a>
<a href="#">400040020</a>	\$168.00	11.46 x 11.46 [291.08 x 291.08]	12.80 x 12.80 [325.12 x 325.12]	<a href="#">PDF</a>

NOTE: Dimensions listed as inches [millimeters]