



Remote Access Solution

Add-on Subscriptions

These subscriptions provide added services to your STRIDE SiteLink remote access. These are not needed for the basic function of the VPN remote access, but can be added to enhance the value of the platform to you and your customers.

All subscriptions are available at www.StrideSiteLink.com. Log into your account for all subscription purchases, upgrades, and cancellations.

All subscriptions can be purchased on a recurring monthly or annual basis. Annual purchases receive a free month of subscription.

STRIDE SiteLink Add-on Subscriptions			
Part #	Price (per month)	Description	Features
SE-SL001	\$60.00	Service Level Agreement (SLA)	99.6% availability, 4-hour max consecutive downtime per router
SE-SL010	\$15.00	Cloud Logging, Standard Data logging enabled at 1,000 data samples per hour per router	Unlimited cloud storage for up to 7 years with active subscription, unlimited real time and user configurable dashboards, unlimited data reports, unlimited data tags, Modbus protocol support Data logging traffic does not affect monthly data usage (5 GB free or Data Top-up subscriptions).
SE-SL011	\$35.00	Cloud Logging, Professional Data logging enabled at 5,000 data samples per hour per router	
SE-SL012	\$85.00	Cloud Logging, High Resolution Data logging enabled at 20,000 data samples per hour per router	
SE-SL030	\$35.00	Data Top-up, 5GB	Additional monthly data traffic by 5GB per company account
SE-SL031	\$95.00	Data Top-up, 15GB	Additional monthly data traffic by 15GB per company account
SE-SL032	\$190.00	Data Top-up, 50GB	Additional monthly data traffic by 50GB per company account



WARNING: Data is only stored for as long as you maintain your paid subscription. ALL data will be lost if your subscription lapses. Data for a specific device will be lost if a subscription is removed from that device. Data is also only stored for a maximum of 7 years. If data older than 7 years is important, please archive your data locally before the 7-year limit is reached.