


**Southwire™**

TOOLS &amp; EQUIPMENT

# Wire Cutters/Pliers Strippers/Shears

## Overview

Southwire's pliers and cutters are made from American forged steel and assembled with hot rivet technology. These tools are built to withstand the wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.



Wire Cutters/Pliers/Strippers/Shears					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
<a href="#"><u>S1020SOLUS</u></a>	Southwire multi-purpose cutting and stripping tool, beveled cutting edges, 22-10 AWG capacity.	6in	1	0.31	\$12.50
<a href="#"><u>DCPA8D-US</u></a>	Southwire diagonal cutters, 8.0in (203mm) overall length, induction hardened beveled cutting edges, 15-degree angled head, comfort grip handles.	8in	1	0.63	\$37.00
<a href="#"><u>CCP9D-US</u></a>	Southwire cable shears, 9.0in (229mm) overall length, induction hardened shear cutting edges, comfort grip handles.	9in	1	1.03	\$37.50
<a href="#"><u>SCP9TPCD-US</u></a>	Southwire linesmans pliers, 9.0in (229mm) overall length, induction hardened beveled cutting edges, comfort grip handles. Additional features include fish tape pulling and conduit reaming.	9in	1	1.07	\$41.50
<a href="#"><u>TCC9D-US</u></a>	Southwire crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors.	9in	1	0.96	\$33.00


[S1020SOLUS](#)

- Strips and cuts up to 10-20 AWG solid and 12-22 AWG stranded wire
- Double-dipped grip for comfortable fit
- Serrated nose holds cable for easy twisting and pulling
- Spring-loaded for self-opening action


[DCPA8D-US](#)

- Effectively cuts most hardened wire, ACSR, bolts, screws and nails
- High-leverage design provides maximum cutting power
- Angled head allows for easy work in confined spaces


[CCP9D-US](#)

- Cuts up to 4/0 AWG aluminum, 2/0 AWG copper, and 100-pair 24 AWG communications cable
- Induction hardened blades for maximum durability
- Dipped handles for comfort


[SCP9TPCD-US](#)

- High-leverage design provides maximum cutting power
- Induction hardened cutting blades ensure efficient and lasting cutting surfaces for hard and soft wire
- Features a crimper, fish tape puller and reaming head for added versatility


[TCC9D-US](#)

- Crimps insulated and non-insulated terminals and connectors
- Specially hardened wire cutter in nose
- Tapered nose for working in confined spaces


**Southwire™**

TOOLS &amp; EQUIPMENT

# Cable Shears and Pliers

## Overview

Southwire's cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges of wire and cable effortless.

Cable Shears and Pliers					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
<b><u>MP61</u></b>	Southwire multi-purpose crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors.	9in	1	0.49	\$26.00


**MP61**

## Features

- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
- Crimps: insulated and non-insulated terminals/connectors
- Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws



# Nutdriver Sets



## ND6N1HD Nutdriver Set

- 6 IN 1 Multi-driver with 3/16", 1/4", 5/16", 3/8", 7/16", 9/16" nut drivers.
- Heavy Duty steel shanks with bolsters for wrench assisted turning
- Comfort grip handle provides extra comfort and maximum torque
- Color coded ends for quick identification of sizes
- Chrome plated finish for corrosion resistance
- Hollow shafts for screw shank clearance

ND6N1HD

Nut Drivers and Set				
Part Number	Description	Pcs/ Pkg	Weight (lbs)	Price
ND6N1HD	Southwire multi-bit reversible shaft nutdriver, 4 pieces, imperial, cushion grip handle, 1.4in (36mm) shaft length.	4	1	\$21.50


**Southwire™**

TOOLS &amp; EQUIPMENT

# Fish Tape

## Overview

Southwire's SIMpull™ fish tape makes pulling wire or cable through a filled or empty conduit up to 2 inches in diameter easily. The low friction design allows these fish tapes to easily glide through the conduit without binding at turns, joints, or couplings. Spiral extruded polymer reduces the amount of effort required to push or pull the fish tape through EMT, IMC, Rigid or PVC conduit and as an added bonus polymer fish tapes will not rust. Do not confuse these polymer tapes with a fiberglass tape. A polymer fish tape offers greater flexibility than fiberglass fish tapes. These fish tapes will not break when folded or leave uncomfortable splinters. With the swiveling flexible metal leader and the polymer non-conductive tape makes the job SIMpull.

## Features

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape.
- Swiveling flexible metal leader easily glides through bends
- Low friction material reduces binding at joints, couplings, or 90-degree bends
- Two lengths 75 or 125 feet
- 580 lbs. tensile strength
- 4.5mm diameter tape
- Weighs less than a steel tape



**FTSP45-75FML**



**FTSP45-125FML**

Fish Tape				
Part Number	Description	Pcs/ Pkg	Weight (lbs)	Price
<b><u>FTSP45-75FML</u></b>	Southwire SIMpull fish tape, 75ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	2.77	\$69.00
<b><u>FTSP45-125FML</u></b>	Southwire SIMpull fish tape, 125ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	3.35	\$100.00



**Southwire™**

TOOLS & EQUIPMENT

# Misc Sets



**60010S**

## Features

- UL listed CAT IV 600V, CAT III 1000V Test Leads
- 39in test leads
- 1000V AC/DC (Max)
- 10 Amp Current (Max)
- Includes removable CAT III 600V Alligator Clips

Miscellaneous Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
<b>60010S</b>	Southwire test lead set, CAT IV 600V/CAT III 1000V, 48in length. For use with all Southwire meters except for the 10010S Analog Multimeter. Alligator clip adapters included.	1	0.31	\$17.50


**Southwire™**

TOOLS &amp; EQUIPMENT

# Tool Accessories

## EDGEFORCE™ Hawk Bill Knife


**HBKND2**

- Premium D2 Stainless Steel Holds an edge
- Curved blade for pull cuts and splicing
- Rugged metal handle
- Stonewash black oxide coated blade
- Liner lock keeps blade secure
- Comfort grip for maximum hold and comfort
- Reversible belt clip

## Folding Utility Knife


**UTILQO**

- Quick open button for easy one hand operation
- Durable metal body with comfort grip for secure hold
- Easy blade replacement
- Rugged metal handle
- Comfort grip for maximum hold and comfort
- Quick open/close button
- Lanyard hole
- Belt clip

### Accessories Selection

<b>Part Number</b>	<b>Description</b>	<b>Weight (lbs)</b>	<b>Price</b>
<b><u>HBKND2</u></b>	Southwire EDGEFORCE folding knife, hawkbill blade, 2.60in blade length, 7.24in overall length, metal body with comfort grip and pocket clip.	0.3	\$29.50
<b><u>UTILQO</u></b>	Southwire EDGEFORCE folding knife, common replaceable 2 point utility blade, 6.01in overall length, metal body with comfort grip and pocket clip.	0.4	\$13.00