

Stride Managed Industrial Ethernet Switches

Industrial Hardened Full Feature Layer 2 Switch



For detailed specifications on all models, see following pages

		SE Series	SE2 Series
Price			
		starting at \$475 (5 port)	starting at \$429 (8 port)
Full Feature Layer 2 Switch			
		✓	✓
Industrial Temperature Ranges			
	Wide Temp	-40 to +75°C	-40 to +75°C
Ethernet Connectivity			
	RJ45 Ports	up to 1000 Mbps	up to 1000 Mbps
	Fiber Optic Ports	✓	✓
	SFP Ports	✓	✓
Port Count			
		5,8,10,16	8,16,18
Industrial Protocol Management			
	Modbus TCP	Read	Full Management
	EtherNet/IP	—	Full Management
Network Redundancy			
	STP/RSTP	✓	✓
	Proprietary Fast Recovery	Real-Time Ring	AD-Ring/AD-RP
Mounting			
	DIN Rail Mount	✓	✓
	Panel Mount	Integrated	Optional accessory
Input Power			
	Redundant Power Inputs	✓	✓
	Reverse Polarity Protection	✓	✓
	Power LED	✓	✓
	Power Alarm	✓	✓
Agency Approvals			
	UL508 / 61010	✓	✓
	Haz Loc-Class 1 Div 2	✓	✓
	ATEX Zone 2	✓	—
	CE	✓	✓
Warranty			
		2 years	5 years