

Stride Managed Industrial Ethernet Switches

Industrial Hardened Full Feature Layer 2 Switch



For detailed specifications on all models, see following pages

		SE Series	SE2 Series
Price			
		starting at \$475 (5 port)	starting at \$429 (8 port)
Full Feature Layer 2 Switch			
		✓	✓
Industrial Temperature Ranges			
<i>Wide Temp</i>		-40 to +75°C	-40 to +75°C
Ethernet Connectivity			
<i>RJ45 Ports</i>		up to 1000 Mbps	up to 1000 Mbps
<i>Fiber Optic Ports</i>		✓	✓
<i>SFP Ports</i>		✓	✓
Port Count			
		5,8,10,16	8,16,18
Industrial Protocol Management			
<i>Modbus TCP</i>		Read	Full Management
<i>EtherNet/IP</i>		—	Full Management
Network Redundancy			
<i>STP/RSTP</i>		✓	✓
<i>Proprietary Fast Recovery</i>		Real-Time Ring	AD-Ring/AD-RP
Mounting			
<i>DIN Rail Mount</i>		✓	✓
<i>Panel Mount</i>		Integrated	Optional accessory
Input Power			
<i>Redundant Power Inputs</i>		✓	✓
<i>Reverse Polarity Protection</i>		✓	✓
<i>Power LED</i>		✓	✓
<i>Power Alarm</i>		✓	✓
Agency Approvals			
<i>UL508 / 61010</i>		✓	✓
<i>Haz Loc-Class 1 Div 2</i>		✓	✓
<i>ATEX Zone 2</i>		✓	—
<i>CE</i>		✓	✓
Warranty			
		2 years	5 years