

# UL/CUL/CSA Certification Numbers

UL/CUL/CSA Certification Numbers <sup>1</sup>			
Name	UL/CUL	CSA	ISO-9000
Accuamp Current Sensors, Switches, Transducers	E222847	-	-
ADC 22mm Pushbuttons and Indicating Lights ECX/GCX models	E189258	66746	-
ADC Contactors	E191059	703171	✓
ADC Foot Switches	E191072	-	-
ADC GS & DURAPULSE Drives	E198015	-	-
ADC Limit Switches	E191072	-	✓
ADC Line Reactors - GS series	E61431	-	-
ADC Line Reactors - LR series	E197592	-	-
ADC Manual Motor Controllers	E195426	-	✓
ADC Photo Sensors	E130644, E224302 E187310	-	✓
ADC LED Photo Sensor Cables	E191684	-	-
ADC Power Supplies (FA Series)	E200031	-	-
ADC Power Supplies (PS & PSE series) <sup>2</sup>	E197592, E198298, E197886	-	✓
ADC Power Supplies (PSM series)	E197592, E198298	229285	✓
ADC Power Supplies (PSS series)	E198298	-	-
ADC Power Supplies (PSB series)	E197592, E198298	249074	-
ADC Power Supplies (PSP, PSC series) <sup>3</sup>	E197592 E198298	-	✓
ADC Proximity Switches	E130644, E187310 E328811	-	✓
ADC Relays - QL and QM Series	E222847	218218	-
ADC Relays - 75, 78 and PR40 Series	E191059	244610	-
ADC Relays - 755 Series	E43641	244610	-
ADC Relays - RS Series	E44592	-	-
ADC Relays - SSR2, SSR6, SSR8 Series	E222847	244610	-
ADC Relays - HSSR8 Series	E344125	-	-
ADC Telephone Modems and Ethernet Switches	E200031	-	-
Atlas Industrial Monitors	E313546, E191072	-	-
BM Cable Ties <sup>4</sup>	E223175	-	-
Bryant Plugs	E1381	16215	-
Bryant Connectors	E3381, E3382	16215	-
Bryant Receptacles	E2258	16215	-
Bryant Cover Plates	E31999	18416	-
Bryant Manual Motor Controllers	E70402	46186	-
C-more Panels	E157382	-	-
C-more Micro Panels	E157382	-	-
Cirronet RF Modems	E235438	-	-
CLICK PLCs	E157382, E316037	-	✓
Comepi Safety Limit Switches	E189258	176294	-
Contrinex Light Curtains	E321951	-	-
Cutler-Hammer Pushbuttons	E131568	68551	-
Cutler-Hammer Contactors	E1491	353	-
DINnectors (DN-SP-xx series only)	E320462	-	-
DINnectors (all other products)	E179129	-	-
DirectLOGIC PLC hazardous locations	E200031	-	✓ (Koyo)
DirectLOGIC PLCs & I/O	E157382	-	✓ (Koyo)
DirectTouch Panels	E178572	-	✓
Dold Safety Relays	E107778	-	-
Eaton Supplementary Protectors (WMZS)	E162396	245545	-
Eaton Miniature Circuit Breakers (WMZT)	E7819, E64983	245545	-

UL/CUL/CSA Certification Numbers <sup>1</sup>			
Name	UL/CUL	CSA	ISO-9000
Edison Fuse Blocks (Class T)	E14853	47235	-
Edison Fuse Holders – CH	E14853	-	-
Edison Fuses	E19180, E162363, E162443	053787, 227483, 700489	-
Edison Power Distribution Blocks	E256146, E221592, E333541	700490 700489	-
Encore Wire Type THHN	E123774 E156879	-	-
Encore Wire Type MTW	E156879	-	-
Encore Wire Type TFFN	E156878	-	-
Ethernet Patch Cable	E148114	-	-
Ethernet Patch Cable Connector	E205572	-	-
FACTS I/O Modules	E139594 E200031	-	-
Ferraz Shawmut Fusible and Non-Fusible Disconnects	E191605 E258428	703166	-
Ferraz Shawmut Disconnects Shafts and Handles (SH400-15 = Socomec 379H1540)	E191605 E196672 E201138	703166	-
Ferraz Shawmut Disconnects Accessories (Connectors and Lugs)	E191605	703166	-
TL100 = Brumall 2/0 TP	E61509	026192_0_000 703166	-
TL200 = Brumall 3/0 TP	E61509	026192_0_000 703167	-
TL400 = Brumall 600T-2 / CMC PV2-600	E61509 E26130	030117_C_000 703166 026192_0_000	-
TL600 = Brumall 600T-2 / CMC PV2-600	E61509 E26130	030117_C_000 703166 026192_0_001	-
TL800 = CMC PV3-600	E26130	030117_C_00 703168	-
AC3= Socomec 39990701	E191127	703166	-
AC4= Socomec 39990702	E191127	703166	-
Flexible Cord, Types SJE00W/SE00W	E46194	224650	-
Flexible Cord, Type W	E308664	236844	-
Fuji Molded Case Circuit Breakers: Fuji MCCB Accessories:	E90584 E93289	-	-
Fuji Motor Controls	E44592 E93289	20479	✓
Fuji Manual Motor Starters (stand-alone)	E163944	-	-
Fuji Manual Motor Starter w/ Fuji contactor	E211710	-	-
Fuji Pushbuttons	E44592	LR20479	-
Fuji Timers and Card Relays	E44592	-	✓
Fuse Blocks	E14853	47235_C_000	-
Fuses (Class CC)	E162363	700489	-
Fuses (Midget Class)	E162443	700489	-
Fuses (Class J)	E162363	700489	-
Fuses (Class RK5)	E162363	700489	-
Fuses (Class RK1)	E162363	700489	-
Fuses (Class T) Edison	E162363	53787	-
Fuses (General Purpose-Small Electronic)	E19180	227483053787_ C_000	-
Gladiator Switches Open Type (Class CC)	E339079	-	-
Gladiator Switches Industrial Control Type (Class Midget)	E222847	-	-

Continued on next page.

Footnotes on next page.

# UL/CUL/CSA Certification Numbers

UL/CUL/CSA Certification Numbers <sup>1</sup>			
Name	UL/CUL	CSA	ISO-9000
Hammond Control Transformers	E50394	003902	-
Hammond Encapsulated Transformers	E50394	003902	
Hitachi Drives	E178241	-	✓
H/W Filter Fan Kits WPF Series (PFANNENBERG PF Series)	E175229	-	-
H/W Metal Cabinet & Cutout Boxes	E6924	66078	-
H/W Metal Industrial Control Panels (Non- disconnect)	E64791	66078	-
H/W Metal Industrial Control Panels (Disconnect)	E64791	66078	-
H/W Metal Junction & Pull Boxes	E23553	66078	-
H/W Metal Wireway & Fittings	E32576	66078	-
H/W Non-Metal Enclosures	E64791	222873	-
Host Products	E185989	-	-
I-Flex Flexible Liquid-Tight Tubing (NMPT)	E311916	-	-
IronHorse Motors (T-Frame, TC-Frame)	-	200895 215302	✓
IronHorse Motors (Rolled Steel)	-	215302	-
IronHorse Motors (DC)	-	247070	-
Koyo Timers	E186879	-	✓
Koyo Encoders	E189395	-	✓
Koyo Proximity Switches	E186879	-	✓
Marathon Motors	E49747	37479 002025	-
MCCB (molded case circuit breakers)	E7819 E64983	43556	-
MCCB Field Installed Accessories	E64983	-	-
Nitra Cylinder Switches	E328811	-	-
Non-Fused Disconnects	E226699	-	-
Optimate Panels	E182843	-	-
Productivity3000 PAC and I/O <sup>5</sup>	E157382 E200031	-	-
ProSense Pressure Sensors	E320431	-	-
ProSense QPS Pressure Switch	E157382	-	-
ProSense Temperature Sensors	E324411	-	-
Signal Conditioners: FC Series	E200031	-	-
Signal Conditioners: Universal	E314521	-	-
Solo Process Controllers	E311366	-	-
Stratus Air Conditioners	SA33404	-	-
Stride Ethernet Switches	E200031	-	-
Stellar SR22 Compact Soft Starters	E333109	-	-
Stellar SR22 Soft Starter Accessory Cooling Fans	E89936 E132139 E77551	-	-
Stellar SR33 Basic Soft Starters	E333109	-	-
Stellar SR44 Full-Featured Soft Starters	E333109	-	-
SureServo Servo Systems - Drives	E198015	-	-
SureServo Servo Systems - Motors	E245050	-	-

UL/CUL/CSA Certification Numbers <sup>1</sup>			
Name	UL/CUL	CSA	ISO-9000
Werma Signaltechnik	E164155	-	✓
Wire Duct	E123572	-	-
ZipLinks: FACTS Communication Adapters and all Cables <sup>6</sup>	E200031	-	-
ZipLinks: FACTS Relay Modules	E157382	-	-
ZipLinks: FACTS Replacement Relays	E141060	-	-
ZipLinks: Non-FACTS Cables <sup>7</sup>	E179771	80671	-
ZipLinks: Non-FACTS Connectors <sup>7</sup>	E197592	-	-
ZipPort Junction Blocks	E328610	-	-
ZipPort Multi-Wire	E342543	-	-
ZipPort Panel Interface Connectors	E329932	-	-

Other Registrations and Certifications	
Name/Description	Designation
ITAR Part 122 - Registration of Manufacturers and Exporters, registered with Office of Defense Trade Controls	22CFR Section122

## Footnotes

<sup>1</sup>For the latest agency approvals information please see our Website:

<http://www.automationdirect.com/static/specs/agencyapprovals.pdf>

<sup>2</sup>PSxx-050D and PS24-500D are not UL/cUL 1604 listed.

<sup>3</sup>PSP05-020S, PSP12-024S and PSP24-240S are not UL 60950 recognized.

<sup>4</sup>Except for the following parts, which are not UL approved: BM-N8912, BM-N1012, BM-R1576, BM-R2076, BM-R3076, all BM-Txxxxx, all cable mounts and hand tools.

<sup>5</sup>P3-16TD3P, P3-HSI and P3-HSO modules are not UL1604 E200031 recognized.

<sup>6</sup>The cables are listed in E200031 Vol. 5 Sec. 1; Titled: Unlisted Components Report. Included in this section are ZL-CMA15 and ZL-CMA15L as well. A copy of this section is available from ADC upon request.

<sup>7</sup>The manufacturer of these devices is no longer in business. Please verify listing status with UL directly at Multiple Listings Customer Service (1-877-854-3577 or [mls@us.ul.com](mailto:mls@us.ul.com)). For new projects please use ZipLinks manufactured by FACTS Engineering.