



# SC91 Series




**1/4" NPT**  
**Brass Forged Body**  
**2-Way Direct Acting**  
**Normally Open**



Materials	Seals:	FKM, EPDM, Nitrile
	Orifice:	Stainless Steel
Electrical	Standard Housing:	DIN 43650 Form B
	Optional Housings:	18" Leads
	Standard Voltages:	24, 120, 240AC 60Hz; 50Hz available; 12, 24 DC; Contact GC Valves Customer Service for Additional Voltages.
	Voltage Tolerance:	±10% of applicable voltage
	Coil Class:	F
Operating Temperature	Ambient (Nominal):	32°F to 125°F
Mounting	Position:	Any
Approvals*	Agencies:	cURus, CE

\*Not Available for all variations

## Dimensions








# SC912-1/4" NPT, Forged Brass, Normally Open



## Valve Selection List

Normally Open



Pipe Size	Orifice Size	Cv	Operating Pressure Differential (PSI)				Max. Fluid Temp. °F	Seal Material	Power Consumption		Model Code (24V/60HZ - DIN) Shown	
			Min.	Maximum		AC			DC	AC : vA		DC : Watts
				Air/Gas								
NPT	mm.			AC	DC	AC	DC			Brass Forged Body		
1/4	1.2	0.028	0	217	217	217	217	230	FKM	6.5	4	SC912YN24VEBA2
	1.6	0.049	0	145	145	145	145	230	FKM	6.5	4	SC912YN24VEBA3
	2.0	0.065	0	95	95	95	95	230	FKM	6.5	4	SC912YN24VEBA4
	2.4	0.086	0	55	55	55	55	230	FKM	6.5	4	SC912YN24VEBA5
1/4	1.2	0.028	0	217	217	217	217	295	EPDM	6.5	4	SC912YN24CEBA2
	1.6	0.049	0	145	145	145	145	295	EPDM	6.5	4	SC912YN24CEBA3
	2.0	0.065	0	95	95	95	95	295	EPDM	6.5	4	SC912YN24CEBA4
	2.4	0.086	0	55	55	55	55	295	EPDM	6.5	4	SC912YN24CEBA5
1/4	1.2	0.028	0	217	217	217	217	180	NITRILE	6.5	4	SC912YN24NEBA2
	1.6	0.049	0	145	145	145	145	180	NITRILE	6.5	4	SC912YN24NEBA3
	2.0	0.065	0	95	95	95	95	180	NITRILE	6.5	4	SC912YN24NEBA4
	2.4	0.086	0	55	55	55	55	180	NITRILE	6.5	4	SC912YN24NEBA5



# SC912-1/4" NPT, Forged Brass, Normally Open



## Part Numbering

1	2	3	4	5	6	7	8	9	10	11	12	13	14
<b>S</b>	<b>C</b>	<b>9</b>	<b>1</b>	<b>2</b>	<b>Y</b>	<b>N</b>	<b>2</b>	<b>4</b>	<b>V</b>	<b>E</b>	<b>B</b>	<b>A</b>	<b>5</b>
Series		Stations	Operating Mode	Housing	Coil	Voltage		Seal Material	Body Material	Pipe Size	Orifice Size		
C9 Direct Acting NPT Threads		1	2: 2Way N.O.	Y: DIN G: Leads	N: F Class	02: 120/60 04: 240/60 24: 24/60 15: 12 VDC 16: 24 VDC		V: FKM C: EPDM N: Nitrile	E: Brass	B: 1/4"	A2: 1.2mm A3: 1.6mm A4: 2.0mm <b>A5: 2.4mm</b>		

## Coil Data

AC Coil Family	
Voltage Code	Coil Number
YN02	C944
GN02	C944L
YN04	C802
GN04	C802L
YN24	C987
GN24	C987L

DC Coil Family	
Voltage Code	Coil Number
YN15	C999
GN15	C999L
YN16	C926
GN16	C926L

## Kit Data

Operator	
Seal	Part Number
V	KSC9202VDA5
C	KSC9202CDA5
N	KSC9202NDA5